






DNI = DO NOT INSTALL




 <b>TEXAS INSTRUMENTS</b>		
Title <b>DAC5668/88/89 EVB</b>		
Size <b>B</b>	Document Number	Rev <b>D</b>
Date: Wednesday, December 23, 2009 Sheet 1 of 7		



J5 - JUMPER PINS 1 & 2  
JUMPER PINS 5 & 6  
JUMPER PINS 10 & 11  
JUMPER PINS 16 & 17  
JUMPER PINS 20 & 21




DNI = DO NOT INSTALL



NOTE 1

NOTE 1: For TRF3703-17 configuration

R47, R53, R66, R59 = 124 ohm  
R97, R106, R114, R115 = 453 ohm  
R48, R54, R67, R60 = 499 ohm  
C114, C116, C117, C118 = 10uF (installed)




NOTE 1


**TEXAS INSTRUMENTS**




Title		<b>DAC5668/88/89 EVM</b>	
Size	Document Number	Rev	
<b>B</b>		<b>D</b>	
Date:	Wednesday, December 23, 2009	Sheet	3 of 7


DNI = DO NOT INSTALL





Title				
<b><i>DAC5668/88/89 EVM</i></b>				
Size	Document Number			Rev
<b>B</b>				<b>D</b>
Date:	Wednesday, December 23, 2009		Sheet	4 of 7






**TEXAS INSTRUMENTS**


Title		<b>DAC5668/88/89 EVM</b>	
Size <b>B</b>	Document Number		Rev <b>D</b>
Date:	Wednesday, December 23, 2009	Sheet	6 of 7



# MECHANICAL PARTS

# FOR J24

- x\_SCREW1  
SCREW PANHEAD 4-40 x 3/8  
x\_STANDOFF1  
STANDOFF ALUM HEX 4-40 x .500
- x\_SCREW2  
SCREW PANHEAD 4-40 x 3/8  
x\_STANDOFF2  
STANDOFF ALUM HEX 4-40 x .500
- x\_SCREW3  
SCREW PANHEAD 4-40 x 3/8  
x\_STANDOFF3  
STANDOFF ALUM HEX 4-40 x .500
- x\_SCREW4  
SCREW PANHEAD 4-40 x 3/8  
x\_STANDOFF4  
STANDOFF ALUM HEX 4-40 x .500
- x\_SCREW5  
SCREW PANHEAD 4-40 x 3/8  
x\_SCREW6  
SCREW PANHEAD 4-40 x 3/8



**TEXAS INSTRUMENTS**

Title

**DAC5668/88/89 EVM**

Size **B** Document Number

Date: Wednesday, December 23, 2009 Sheet 7 of 7

Rev **D**