



Note:

1. Input capacitance of Vbus should not exceed 10uF.
2. LT1121-3.3 is 3.3V voltage regulator.
3. DS1233A is reset IC with manual reset button feature.
4. 2N3904 sets TP40 at 3.0 voltage after reset.
5. 22pF caps are used to bypass high frequency and for edge rate control (optional)