




TIDC-HYBRID-RF-PLC



TIDC-HYBRID-RF-PLC




TIDC-HYBRID-RF-PLC



TIDC-HYBRID-RF-PLC


ART FILM - soldmask_top



TIDC-HYBRID-RF-PLC

ART FILM - soldmask_top

ART FILM - soldmask_bottom




TIDC-HYBRID-RF-PLC

ART FILM - soldmask_bottom

DESIGN CROSS SECTION CHART


TOTAL THICKNESS 0.8 MM



L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.73 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
◦	0.2	PLATED	231
⊙	0.2	PLATED	25
.	0.4	PLATED	19
△	1.501	NON-PLATED	4