

## 带有自动方向感测的 2 位双向电压电平转换器

查询样品: **TXB0302**

### 特性

- 完全对称电源电压  
A 端口上 **0.9V 至 3.6V** 和 **0.9V 至 3.6V**
- **V<sub>CC</sub>** 隔离特性—如果任何一个 **V<sub>CC</sub>** 输入在接地 (**GND**) 上, 所有输出在高阻抗状态
- 以 **V<sub>CCA</sub>** 为基准的输出使能 (**OE**) 输入电路
- 低功耗, 最大值 **5μA I<sub>CC</sub>**
- **I<sub>off</sub>** 支持部分断电模式运行
- 锁断性能超过 **100mA** (符合 **JESD 78 Class II** 规范的要求)
- 静电放电 (**ESD**) 保护性能超过 **JESD 22** 规范要求
  - **4000V** 人体模型 (**A114-A**)
  - **1000V** 充电器件模型 (**C101**)

### 说明

这个 2 位非反向转换器使用两个独立的可配置电源轨。A 端口被设计用于跟踪 **V<sub>CCA</sub>**。 **V<sub>CCA</sub>** 接受从 0.9V 至 3.6V 间的任一电源电压值。B 端口设计用于跟踪 **V<sub>CCB</sub>**。 **V<sub>CCB</sub>** 接受从 0.9V 至 3.6V 间的任一电源电压值。这可实现 1V, 1.2V, 1.5V, 1.8V, 2.5V 和 3.3V 电压节点间的低压双向转换。对于 **TXB0302**, 当输出使能端 (**OE**) 输入为低电平时, 所有输出均被置于高阻抗状态。为了确保加电或断电期间的高阻抗状态, **OE** 应该通过一个下拉电阻器接在 **GND** 上; 此电阻器的最小值由驱动器电流供源能力决定。 **TXB0302** 被设计用于实现 **V<sub>CCA</sub>** 对 **OE** 输入电路供电。该器件完全符合使用 **I<sub>关闭</sub>** 的部分断电应用的规范要求。 **I<sub>关闭</sub>** 电路禁用输出, 从而可防止其断电时破坏性电流从该器件回流。

**DQM 封装**  
(顶视图)



- 不需要在逻辑 I/O 的两侧都安装上拉电阻器。
- 如果需要上拉电阻器或者下拉电阻器的话, 电阻器的值必须超过 20kΩ。
- 20kΩ 是建议的安全值, 如果用户能够接受更高 **V<sub>ol</sub>** 或者更低 **V<sub>oh</sub>** 的话, 也允许使用电阻值更小的上拉或者下拉电阻器, 粗略的估算值为 **V<sub>ol</sub>=V<sub>ccout</sub> x 1.5k/(1.5k+R<sub>pu</sub>)**, 而 **V<sub>oh</sub>=V<sub>ccout</sub> x R<sub>dw</sub>/(1.5k+R<sub>dw</sub>)**。
- 如果需要上拉电阻器, 请参考 **TXS0102** 或者与 **TI** 联系。
- 更多信息, 请参考应用注释 (文献号: **SCEA043**)。

### 订购信息<sup>(1)</sup>

T <sub>A</sub>	封装 <sup>(2)</sup>	可订购部件号	正面标记
-40°C 至 85°C	DQM – 微型四方扁平无引线 (MicroQFN)	TXB0302DQMR	77A

(1) 要获得最新的封装和订货信息, 请参阅本文档末尾的封装选项附录, 或者登录 **TI** 的网站 [www.ti.com](http://www.ti.com)。

(2) 封装图样、热数据和符号可登录 [www.ti.com/packaging](http://www.ti.com/packaging) 获取。



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

# TXB0302

ZHCS822B – MARCH 2012 – REVISED OCTOBER 2012

[www.ti.com.cn](http://www.ti.com.cn)


These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## PIN DESCRIPTION

PIN NO.	NAME	FUNCTION
DQM	TXB0302	
1	VCCA	A-port supply voltage $0.9\text{ V} \leq V_{CCA} \leq 3.6\text{ V}$
2	A1	Input/output 1. Referenced to $V_{CCA}$ .
3	A2	Input/output 2. Referenced to $V_{CCA}$ .
4	GND	Ground
5	OE	3-state output-mode enable. Pull OE (TXB0302) low to place all outputs in 3-state mode.
6	B2	Input/output 2. Referenced to $V_{CCB}$ .
7	B1	Input/output 1. Referenced to $V_{CCB}$ .
8	VCCB	B-port supply voltage $0.9\text{ V} \leq V_{CCB} \leq 3.6\text{ V}$ .

## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
$V_{CCA}$	Supply voltage range		–0.5	4.6	V
$V_{CCB}$			–0.5	4.6	V
$V_I$	Input voltage range	A port	–0.5	4.6	V
		B port	–0.5	6.5	V
$V_O$	Voltage range applied to any output in the high-impedance or power-off state	A port	–0.5	4.6	V
		B port	–0.5	6.5	V
$V_O$	Voltage range applied to any output in the high or low state <sup>(2)</sup>	A port	–0.5	$V_{CCA} + 0.5$	V
		B port	–0.5	$V_{CCB} + 0.5$	V
$I_{IK}$	Input clamp current	$V_I < 0$		–50	mA
$I_{OK}$	Output clamp current	$V_O < 0$		–50	mA
$I_O$	Continuous output current			±50	mA
	Continuous current through VCCA, VCCB, or GND			±100	mA
$T_{stg}$	Storage temperature range		–65	150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## THERMAL IMPEDANCE RATINGS<sup>(1)(2)</sup>

THERMAL METRIC		TXB0302	UNIT
		DQM	
		8 PINS	
$\theta_{JA}$	Package thermal impedance	259	°C/W

- (1) The package thermal impedance is calculated in accordance with JESD 51-7.

- (2) The package thermal impedance is calculated in accordance with JESD 51-5.

**RECOMMENDED OPERATING CONDITIONS<sup>(1)</sup>**

			VCCA	VCCB	MIN	MAX	UNIT
VCCA	Supply voltage				0.9	3.6	V
VCCB					0.9	3.6	
VIH	High-level input voltage	Data inputs	0.9 V to 3.6 V	0.9 V to 3.6 V	$V_{CCI}^{(2)} \times 0.65$	$V_{CCI}^{(2)}$	V
		OE	0.9 V to 3.6 V	0.9 V to 3.6 V	$V_{CCA} \times 0.65$	3.6	
VIL	Low-level input voltage	Data inputs	0.9 V to 3.6 V	0.9 V to 3.6 V	0	$V_{CCI}^{(2)} \times 0.35$	V
		OE	0.9 V to 3.6 V	0.9 V to 3.6 V	0	$V_{CCA} \times 0.35$	
VO	Voltage range applied to any output in the high-impedance or power-off state	A-port	0.9 V to 3.6 V	0.9 V to 3.6 V	0	3.6	V
		B-port	0.9 V to 3.6 V	0.9 V to 3.6 V	0	3.6	
$\Delta t/\Delta v$	Input transition rise or fall rate	A-port inputs	0.9 V to 3.6 V	0.9 V to 3.6 V		40	ns/V
		B-port inputs	0.9 V to 3.6 V	0.9 V to 3.6 V		40	
TA	Operating free-air temperature				–40	85	°C

(1) The A and B sides of an unused data I/O pair must be held in the same state, i.e., both at VCCI or both at GND.

(2) VCCI is the supply voltage associated with the input port.

**ELECTRICAL CHARACTERISTICS**

PARAMETER	TEST CONDITIONS	VCCA	VCCB	TA = 25°C			–40°C to 85°C		UNIT
				MIN	TYP	MAX	MIN	MAX	
VOHA	I <sub>OH</sub> = –20 µA	0.9 V to 3.6 V				0.9 × VCCA			V
VOA	I <sub>OL</sub> = 20 µA	0.9 V to 3.6 V					0.2		V
VOHB	I <sub>OH</sub> = –20 µA		0.9 V to 3.6 V			0.9 × VCCB			V
VOB	I <sub>OL</sub> = 20 µA	0.9 V to 3.6 V					0.2		V
II	OE	VI = VCCI or GND	0.9 V to 3.6 V	0.9 V to 3.6 V		±1		±2	µA
Ioff	A port	VI or VO = 0 to 3.6 V	0 V	0 V to 3.6 V		±1		±2	µA
	B port	VI or VO = 0 to 3.6 V	0 V	0 V to 3.6 V		±1		±2	
IOZ	A or B port	OE = GND	0.9 V to 3.6 V	0.9 V to 3.6 V		±1		±2	µA
ICCA	VI = VCCI or GND, IO = 0	0.9 V to 3.6 V	0.9 V to 3.6 V					5	µA
ICCB	VI = VCCI or GND, IO = 0	0.9 V to 3.6 V	0.9 V to 3.6 V					5	µA
ICCA + ICCB	VI = VCCI or GND, IO = 0	0.9 V to 3.6 V	0.9 V to 3.6 V					10	µA
ICCA	VI = VCCI or GND, IO = 0, OE = GND	0.9 V to 3.6 V	0.9 V to 3.6 V					5	µA
ICCA	VI = VCCI or GND, IO = 0, OE = GND	0.9 V to 3.6 V	0.9 V to 3.6 V					5	µA
Ci	OE	0.9 V to 3.6 V	0.9 V to 3.6 V		3				pF
Cio	A port	0.9 V to 3.6 V	0.9 V to 3.6 V		9				pF
	B port				12				

**TIMING REQUIREMENTS**

		VCCA	VCCB	MIN	MAX	UNIT
Data rate	C <sub>L</sub> = 15 pF	0.9 to 3.6 V	0.9 to 3.6 V		40	Mbps
	C <sub>L</sub> = 15 pF	1.2 to 3.6 V	1.2 to 3.6 V		100	Mbps
	C <sub>L</sub> = 15 pF	1.8 to 3.6 V	1.8 to 3.6 V		140	Mbps
	C <sub>L</sub> = 30 pF	0.9 to 3.6 V	0.9 to 3.6 V		40	Mbps
	C <sub>L</sub> = 30 pF	1.2 to 3.6 V	1.2 to 3.6 V		90	Mbps
	C <sub>L</sub> = 30 pF	1.8 to 3.6 V	1.8 to 3.6 V		120	Mbps
	C <sub>L</sub> = 50 pF	1.2 to 3.6 V	1.2 to 3.6 V		70	Mbps
	C <sub>L</sub> = 50 pF	1.8 to 3.6 V	1.8 to 3.6 V		100	Mbps

## SWITCHING CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)


PARAMETER	FROM (INPUT)	TO (OUTPUT)		VCCA	VCCB	MIN	TYP T <sub>A</sub> = 25°C	MAX	UNIT
t <sub>pd</sub>	A	B	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6		18.9	62.5	ns
	A	B	C <sub>L</sub> = 15	1.2-3.6	1.2-3.6		7.5	15.5	
	A	B	C <sub>L</sub> = 15	1.8-3.6	1.8-3.6		3.7	5.8	
	A	B	C <sub>L</sub> = 30	0.9-3.6	0.9-3.6		19.5	64.5	
	A	B	C <sub>L</sub> = 30	1.2-3.6	1.2-3.6		7.8	16.1	
	A	B	C <sub>L</sub> = 30	1.8-3.6	1.8-3.6		3.8	6.1	
	A	B	C <sub>L</sub> = 50	1.2-3.6	1.2-3.6		8	16.8	
	A	B	C <sub>L</sub> = 50	1.8-3.6	1.8-3.6		4	6.5	ns
	B	A	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6		18.9	62.6	
	B	A	C <sub>L</sub> = 15	1.2-3.6	1.2-3.6		7.5	15.4	
	B	A	C <sub>L</sub> = 15	1.8-3.6	1.8-3.6		3.7	5.8	
	B	A	C <sub>L</sub> = 30	0.9-3.6	0.9-3.6		19.5	64.5	
	B	A	C <sub>L</sub> = 30	1.2-3.6	1.2-3.6		7.8	16.1	
	B	A	C <sub>L</sub> = 30	1.8-3.6	1.8-3.6		3.8	5.2	
	B	A	C <sub>L</sub> = 50	1.2-3.6	1.2-3.6		8	16.9	
	B	A	C <sub>L</sub> = 50	1.8-3.6	1.8-3.6		4	6.6	
t <sub>en</sub>	OE	A	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6			504	ns
		B	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6			356	
t <sub>dis</sub>	OE	A	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6			200	ns
		B	C <sub>L</sub> = 15	0.9-3.6	0.9-3.6			200	ns
t <sub>rB</sub> , t <sub>fB</sub>	B-port rise and fall times		C <sub>L</sub> = 15	0.9-3.6	0.9-3.6		2.95		ns
t <sub>s</sub> , t <sub>f</sub>	A-port rise and fall times		C <sub>L</sub> = 15	0.9-3.6	0.9-3.6		3.1		ns
t <sub>SK(O)</sub>	Channel-to-channel skew		C <sub>L</sub> = 15	0.9-3.6	0.9-3.6			0.5	ns

## OPERATING CHARACTERISTICS

 T<sub>A</sub> = 25°C

PARAMETER		TEST CONDITIONS	VCCA, VCCB 0.9 V to 3.6 V	UNIT
			TYP	
C <sub>pdA</sub>	A-port input, B-port output	C <sub>L</sub> = 0, f = 10 MHz, t <sub>r</sub> = t <sub>f</sub> = 1 ns, OE = V <sub>CCA</sub> (outputs enabled)	40	pF
	B-port input, A-port output		40	
C <sub>pdB</sub>	A-port input, B-port output		40	pF
	B-port input, A-port output		40	
C <sub>pdA</sub>	A-port input, B-port output	C <sub>L</sub> = 0, f = 10 MHz, t <sub>r</sub> = t <sub>f</sub> = 1 ns, OE = GND (outputs disabled)	0.01	pF
	B-port input, A-port output		0.01	
C <sub>pdB</sub>	A-port input, B-port output		0.01	pF
	B-port input, A-port output		0.01	





- (1)  $V_T$  is the input threshold voltage of the TXB0302 (typical  $V_{CCI}/2$ ).
- (2)  $V_D$  is the supply voltage of the external driver.

**Figure 2. Typical  $I_{IN}$  vs  $V_{IN}$  Curve**

## Power Up

There is no requirement for the power sequence. During operation, TXB0302 can work at both  $V_{CCA} \leq V_{CCB}$  and  $V_{CCA} \geq V_{CCB}$ . During power-up sequencing, any power supply can be ramped up first. The TXB0302 has circuitry that disables all output ports when either  $V_{CC}$  is switched off ( $V_{CCA/B} = 0$  V).

## Enable and Disable

The TXB0302 has an OE input that is used to disable the device by setting OE = low, which places all I/Os in the high-impedance (Hi-Z) state. The disable time ( $t_{dis}$ ) indicates the delay between when OE goes low and when the outputs actually get disabled (Hi-Z). The enable time ( $t_{en}$ ) indicates the amount of time the user must allow for the one-shot circuitry to become operational after OE is taken high.

## Pullup or Pulldown Resistor on I/O Lines


The TXB0302 is designed to drive capacitive loads of up to 50 pF. The output drivers of the TXB0302 have low dc drive strength. If pullup or pulldown resistors are connected externally to the data I/Os, their values must be kept higher than 20 k $\Omega$  to ensure that they do not contend with the output drivers of the TXB0302. but if the receiver is integrated with the smaller pull down or pull up resistor, below formula can be used for estimation to evaluate the  $V_{oh}$  and  $V_{ol}$ .

$$V_{ol} = V_{CCout} \times \frac{1.5k\Omega}{1.5k\Omega + R_{pu}} \quad (1)$$


$$V_{oh} = V_{CCout} \times \frac{R_{pd}}{1.5k\Omega + R_{pd}} \quad (2)$$

For the same reason, the TXB0302 should not be used in applications such as I<sup>2</sup>C or 1-Wire where an open-drain driver is connected on the bidirectional data I/O. For these applications, use a device from the TI TXS01xx series of level translators.

## PARAMETER MEASUREMENT INFORMATION




LOAD CIRCUIT FOR MAX DATA RATE,  
PULSE DURATION PROPAGATION  
DELAY OUTPUT RISE AND FALL TIME  
MEASUREMENT




LOAD CIRCUIT FOR  
ENABLE/DISABLE  
TIME MEASUREMENT

TEST	S1
$t_{PZL}/t_{PLZ}$	$2 \times V_{CCO}$
$t_{PHZ}/t_{PHZ}$	Open



VOLTAGE WAVEFORMS  
PROPAGATION DELAY TIMES



VOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES

- A.  $C_L$  includes probe and jig capacitance.
- B. All input pulses are supplied by generators having the following characteristics: PRR 10 MHz,  $Z_O = 50 \Omega$ ,  $dv/dt \geq 1$  V/ns.
- C. The outputs are measured one at a time, with one transition per measurement.
- D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
- E.  $V_{CCI}$  is the  $V_{CC}$  associated with the input port.
- F.  $V_{CCO}$  is the  $V_{CC}$  associated with the output port.
- G. All parameters and waveforms are not applicable to all devices.

**Figure 3. Load Circuits and Voltage Waveforms**

**REVISION HISTORY**

---

<b>Changes from Original (March 2012) to Revision A</b>	<b>Page</b>
---------------------------------------------------------	-------------

---

<b>Changes from Revision A (May 2012) to Revision B</b>	<b>Page</b>
---------------------------------------------------------	-------------

---

- Added Application Information Section ..... [5](#)
-



## PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
<a href="#">TXB0302DQMR</a>	Active	Production	X2SON (DQM)   8	3000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	77A
TXB0302DQMR.B	Active	Production	X2SON (DQM)   8	3000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	77A
TXB0302DQMRG4	Active	Production	X2SON (DQM)   8	3000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	77A
TXB0302DQMRG4.B	Active	Production	X2SON (DQM)   8	3000   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	77A

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TXB0302DQMR	X2SON	DQM	8	3000	180.0	9.5	1.4	2.0	0.5	4.0	8.0	Q1
TXB0302DQMRG4	X2SON	DQM	8	3000	180.0	9.5	1.4	2.0	0.5	4.0	8.0	Q1

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TXB0302DQMR	X2SON	DQM	8	3000	184.0	184.0	19.0
TXB0302DQMRG4	X2SON	DQM	8	3000	184.0	184.0	19.0

DQM (R-PX2SON-N8)

PLASTIC SMALL OUTLINE NO-LEAD




4210302/A 06/2009

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. SON (Small Outline No-Lead) package configuration.




DQM (R-PX2SON-N8)

PLASTIC SMALL OUTLINE NO-LEAD

Example Board Layout



Example Stencil Design  
0.1mm Thick Stencil  
(Note C)



Solder Mask Details

4218746/A 07/13

- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
  - D. Customers should contact their board fabrication site for recommended solder mask tolerances.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月