

**TIDA-01237 REV E2 Bill of Materials**

Item #	Designator	Quantity	Part Name	PartNumber	Manufacturer	Description	PackageReference
1	PCB1	1		TIDA-01237	Any	Printed Circuit Board	
2	C1	1		C1608X5R1A106M080AC	TDK	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0603	0603
3	C2	1		EMVE500ADA470MF80G	Chem-Con	CAP, AL, 47 µF, 50 V, +/- 20%, SMD	F80
4	C3	1		C3225X7R1H106M250AC	TDK	CAP, CERM, 10 µF, 50 V, +/- 20%, X7R, 1210	1210
5	C4	1		C0603C103J5RACTU	Kemet	CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0603	0603
6	C5, C7, C10, C11, C15, C16, C17, C18, C19, C20, C21, C22, C23, C24, C25, C26, C27, C28, C29, C30, C31, C32, C33, C34	24		C0603C153J3GACTU	Kemet	CAP, CERM, 0.015 µF, 25 V, +/- 5%, COG/NP0, 0603	0603
7	C6, C9	2		0603YC104JAT2A	AVX	CAP, CERM, 0.1 µF, 16 V, +/- 5%, X7R, 0603	0603
8	C8	1		06035C104KAT2A	AVX	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
9	C12, C13	2		C1608X7R1E104K080AA	TDK	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	0603
10	C14	1		C1608X7R1C105K080AC	TDK	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
11	D1	1		B0540WS-7	Diodes Inc.	Diode, Schottky, 40 V, 0.5 A, SOD-323	SOD-323
12	D2, D3, D4, D18, D19, D20, D21	7		150060VS75000	Wurth Elektronik	LED, Green, SMD	LED_0603
13	D5	1		SDMK0340L-7-F	Diodes Inc.	Diode, Schottky, 40 V, 0.03 A, SOD-323	SOD-323
14	D6, D7, D8, D9, D10, D11, D12, D13, D14, D15, D16, D17	12		BAS40TW-7-F	Diodes Inc.	Diode, Schottky, 40 V, 0.2 A, AEC-Q101, SOT-363	SOT-363
15	H1, H2	2		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
16	J1	1		282856-2	TE Connectivity	Terminal Block, 5 mm, 2-pole, Tin, TH	TH, 2-Leads, Body 10x10mm, Pitch 5mm
17	J2, J3	2		SSW-110-01-T-S	Samtec	Receptacle, 2.54mm, 10x1, Tin, TH	Receptacle, 2.54mm, 10x1, TH
18	J4, J5, J6	3		90120-0122	Molex	Header, 100mil, 2x1, Tin, TH	Header 2x1
19	J7	1		PPPC042LFBN-RC	Sullins Connector Solutions	Connector, Receptacle, 100mil, 4x2, Gold plated, TH	4x2 Header Receptacle
20	J8	1		PBC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Gold, TH	PBC03SAAN
21	J9	1		800-10-005-10-001000	Mill-Max	Header, 100mil, 5x1, TH	Header, 5x1, 100mil, TH
22	J10	1		76308-204LF	FCI	Receptacle, 100mil, 4x1, Gold, TH	4x1 Receptacle
23	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
24	Q1	1		BC857C-7-F	Diodes Inc.	Transistor, PNP, 45 V, 0.1 A, SOT-23	SOT-23
25	Q2	1		2N7002	Fairchild Semiconductor	MOSFET, N-CH, 60 V, 115 A, SOT-23	SOT-23
26	R1	1		5106	Keystone	RES, 0, 1%, 0.5 W, 0805	0805
27	R2, R6, R7, R10, R12, R13, R15	7		CRCW060310K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
28	R3	1		ERJ-2RKF49R9X	Panasonic	RES, 49.9, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
29	R4	1		CRCW040268R0JNED	Vishay-Dale	RES, 68, 5%, 0.063 W, 0402	0402
30	R5	1		CRCW0402604RFKED	Vishay-Dale	RES, 604, 1%, 0.063 W, 0402	0402
31	R8, R9, R11, R14, R16, R17, R18, R19, R20, R21, R22, R23, R24, R25, R26, R27	16		CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
32	R28, R33	2		CRCW0603909RFKEA	Vishay-Dale	RES, 909, 1%, 0.1 W, 0603	0603
33	R29, R34	2		CRCW0603604RFKEA	Vishay-Dale	RES, 604, 1%, 0.1 W, 0603	0603
34	R30	1		CRCW0603922RFKEA	Vishay-Dale	RES, 392, 1%, 0.1 W, 0603	0603
35	R31	1		CRCW0603511RFKEA	Vishay-Dale	RES, 511, 1%, 0.1 W, 0603	0603
36	R32	1		CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
37	R35	1		CRCW0603309RFKEA	Vishay-Dale	RES, 309, 1%, 0.1 W, 0603	0603
38	R36	1		CRCW06031K21FKEA	Vishay-Dale	RES, 1.21 k, 1%, 0.1 W, 0603	0603
39	R37	1		CRCW06035K36FKEA	Vishay-Dale	RES, 5.36 k, 1%, 0.1 W, 0603	0603
40	R38	1		CRCW06034K64FKEA	Vishay-Dale	RES, 4.64 k, 1%, 0.1 W, 0603	0603
41	R39	1		CRCW06031K96FKEA	Vishay-Dale	RES, 1.96 k, 1%, 0.1 W, 0603	0603
42	R40, R41	2		RC0603JR-0710KL	Yageo America	RES, 10 k, 5%, 0.1 W, 0603	0603
43	S1, S2, S3, S4, S5, S6, S7, S8, S9, S10, S11, S12, S13, S14, S15, S16, S17, S18, S19, S20, S21, S22, S23, S24, S25, S26, S27, S28, S29, S30, S31, S32, S33, S34, S35, S36, S37, S38	38		4-1437565-1	TE Connectivity	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	SW, SPST 6x6 mm
44	U1	1		TPS7B6733QPWRQ1	Texas Instruments	450-mA High-Voltage Ultra-Low IQ Low-Dropout Regulator, PWP0020D	PWP0020D
45	U2	1		TIC12400DCPQ1	Texas Instruments	Multiple Switch Detection Interface (MSDI) device, DCP0038A	DCP0038A
46	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2018, Texas Instruments Incorporated