

Filename: Pro5366.tmp
 Variant: 001
 Generated: 7/18/2017 11:40:15 AM
 TID #: TIDA-01335



TIDA-01335 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C3	2	1800pF	GRM155R72A182KA01D	MuRata	CAP, CERM, 1800 pF, 100 V, +/- 10%, X7R, 0402	0402
2	C2	1	0.018uF	C0603C183K1RACTU	Kemet	CAP, CERM, 0.018 uF, 100 V, +/- 10%, X7R, 0603	0603
3	C4, C5	2	0.22uF	GRM155R60J224KE01D	MuRata	CAP, CERM, 0.22 uF, 6.3 V, +/- 10%, X5R, 0402	0402
4	C6, C8	2	2700pF	GRM155R72A272KA01D	MuRata	CAP, CERM, 2700 pF, 100 V, +/- 10%, X7R, 0402	0402
5	C7	1	0.027uF	C0603C273K1RACTU	Kemet	CAP, CERM, 0.027 uF, 100 V, +/- 10%, X7R, 0603	0603
6	C9	1	2.2uF	GRM155B31A225ME95	MuRata	CAP, CERM, 2.2 uF, 10 V, +/- 20%, B, 0402	0402
7	C10	1	1uF	CGA4J3X7S2A105K125AB	TDK	CAP, CERM, 1 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0805	0805
8	C11, C13	2	150pF	GRM1555C1H151JA01D	MuRata	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
9	C15	1	0.47uF	GRM155R60J474KE19D	MuRata	CAP, CERM, 0.47 uF, 6.3 V, +/- 10%, X5R, 0402	0402
10	C16, C17	2	0.1uF	C1005X5R0J104K	TDK	CAP, CERM, 0.1uF, 6.3V, +/-10%, X5R, 0402	0402
11	C18	1	4.7uF	C1005X5R0J475M050BC	TDK	CAP, CERM, 4.7 uF, 6.3 V, +/- 20%, X5R, 0402	0402
12	D1, D2	2	40V	ZHCS350TA	Diodes Inc.	Diode, Schottky, 40 V, 0.35 A, SOD-523	SOD-523
13	D3	1	Yellow	LY L29K-J1K2-26-Z	OSRAM	LED, Yellow, SMD	LED, 1.3x0.65x0.8mm
14	D5	1	Green	LG L29K-G2J1-24-Z	OSRAM	LED, Green, SMD	1.7x0.65x0.8mm
15	J2	1		09 0431 212 04	Binder-Connector	M12 Socket, 4Pos, TH	M12 Conn D12x14.3
16	J3	1		850-10-004-40-001000	Mill-Max	Header, 50mil, 4x1, Gold, R/A, SMT	Header, 50mil, R/A, SMT
17	R1, R3, R7, R11	4	4.12k	RG1608P-4121-B-T5	Susumu Co Ltd	RES, 4.12 k, 0.1%, 0.1 W, 0603	0603
18	R2	1	3.24k	PFC-W1206R-12-3241-B	TT Electronics/IRC	RES, 3.24 k, 0.1%, 0.333 W, 1206	1206
19	R5, R6, R8	3	47	CRCW040247R0JNED	Vishay-Dale	RES, 47, 5%, 0.063 W, 0402	0402
20	R13, R14	2	820	CRCW0402820RJNED	Vishay-Dale	RES, 820, 5%, 0.063 W, 0402	0402
21	R15	1	47k	CRCW040247K0JNED	Vishay-Dale	RES, 47 k, 5%, 0.063 W, 0402	0402
22	R16	1	4.7k	CRCW04024K70JNED	Vishay-Dale	RES, 4.7 k, 5%, 0.063 W, 0402	0402
23	RT1	1	100 ohm	PTS120601B100RP100	Vishay/Beyschlag	Temperature Sensor, 100 ohm, 1%, 1206	1206
24	S2	1		SKRKAEE010	Alps	Switch, Push Button, SMD	2.9x2x3.9mm SMD
25	U1	1		ADS1220IRVA	Texas Instruments	Low-Power, Low-Noise, 24-Bit Analog-to-Digital Converter for Small Signal Sensors, RVA0016A	RVA0016A
26	U2	1		TIOL111	Texas Instruments	IO-Link Device Transceiver with Integrated Surge Protection, TIOL111 (WSON-10)	TIOL111
27	U3	1		MSP430FR5738IRGE	Texas Instruments	24 MHz Mixed Signal Microcontroller, 1024 B SRAM and 17 GPIOs, -40 to 85 degC, RGE0024G	RGE0024G
28	C14	0	2200pF	GRM155R70J222KA01D	MuRata	CAP, CERM, 2200 pF, 6.3 V, +/- 10%, X7R, 0402	0402
29	R9	0	300	RG1608P-301-B-T5	Susumu Co Ltd	RES, 300, 0.1%, 0.1 W, 0603	0603

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated