

# SN54SC2T74-SEP Single-Event Effects (SEE) Radiation Report



## ABSTRACT

The purpose of this study is to characterize the single-event-effects (SEE) performance due to heavy-ion irradiation of the SN54SC2T74-SEP. SEE performance was verified at minimum (1.2V) and maximum (5.5V) operating conditions. Heavy-ions with an  $LET_{EFF}$  of 43MeV-cm<sup>2</sup>/ mg were used to irradiate three production devices with a fluence of  $1 \times 10^7$  ions / cm<sup>2</sup>. The results demonstrate that the SN54SC2T74-SEP is SEL-free up to  $LET_{EFF} = 43\text{MeV-cm}^2 / \text{mg}$  as 125°C. SET performance for minimum and maximum operating voltages saw no excursions  $\geq |1\%|$ , as shown and discussed in this report.

## Table of Contents

<b>1 Overview</b> .....	2
<b>2 Single-Event Effects (SEE)</b> .....	3
<b>3 Test Device and Test Board Information</b> .....	4
<b>4 Irradiation Facility and Setup</b> .....	6
<b>5 Results</b> .....	7
5.1 SEL Results.....	7
5.2 Single-Event Transients (SET).....	9
5.3 Event Rate Calculations.....	10
<b>6 Summary</b> .....	11
<b>7 References</b> .....	12

## Trademarks

National Instruments™ is a trademark of National Instruments.

Tektronix® is a registered trademark of Tektronix, Inc.

All trademarks are the property of their respective owners.

## 1 Overview

The SN54SC2T74-SEP is a radiation-tolerant, 1.2V to 5.5V dual D-type flip-flop with integrated translation. The input is designed with a lower threshold circuit to support up translation for lower voltage CMOS inputs (for example, 1.2V input to 1.8V output or 1.8V input to 3.3V output). In addition, the 5V tolerant input pins enable down translation (for example, 3.3V to 2.5V output).

For more information, see the SN54SC2T74-SEP [product page](#).

**Table 1-1. Overview Information**

Description	Device Information
TI Part Number	SN54SC2T74-SEP
MLS Number	SN54SC2T74MPWTSEP
Device Function	Radiation-tolerant, 1.2V to 5.5V, dual D-type flip-flop with integrated translation
Technology	LBC9
Exposure Facility	Radiation Effects Facility, Cyclotron Institute, Texas A&M University
Heavy Ion Fluence per Run	$1 \times 10^7$ ions / cm <sup>2</sup>
Irradiation Temperature	25°C (for SET testing) and 125°C (for SEL testing)

## 2 Single-Event Effects (SEE)

The primary single-event effect (SEE) event of interest in the SN54SC2T74-SEP is the destructive single-event latch-up. From a risk or impact perspective, the occurrence of an SEL is potentially the most destructive SEE event and the biggest concern for space applications. In mixed technologies such as the Linear BiCMOS (LBC9) process used for SN54SC2T74-SEP, the CMOS circuitry introduces a potential SEL susceptibility. SEL can occur if excess current injection caused by the passage of an energetic ion is high enough to trigger the formation of a parasitic cross-coupled PNP and NPN bipolar structure (formed between the p-substrate and n-well and n+ and p+ contacts). The parasitic bipolar structure initiated by a single-event creates a high-conductance path (inducing a steady-state current that is typically orders-of-magnitude higher than the normal operating current) between power and ground that persists (is latched) until power is removed or until the device is destroyed by the high-current state. The process modifications applied for SEL-mitigation were sufficient, as the SN54SC2T74-SEP exhibited no SEL with heavy-ions up to an  $LET_{EFF}$  of  $43 \text{ MeV-cm}^2 / \text{mg}$  at a fluence of  $1 \times 10^7 \text{ ions / cm}^2$  and a chip temperature of  $125^\circ\text{C}$ .




Figure 2-1. Functional Block Diagram of the SN54SC2T74-SEP

### 3 Test Device and Test Board Information

The SN54SC2T74-SEP is a packaged 14-pin, TSSOP plastic package shown in the pinout diagram in [Figure 3-1](#). [Figure 3-2](#) shows the device with the package cap decapped to reveal the die for heavy ion testing. [Figure 3-3](#) shows the evaluation board used for radiation testing. [Figure 3-4](#) shows the bias diagram used for Single-Event Latch-up (SEL) testing. [Figure 3-5](#) shows the bias diagram used for Single-Event Transient (SET) testing.




Figure 3-1. SN54SC2T74-SEP Pinout Diagram




Figure 3-2. Photo of SN54SC2T74-SEP Package Decapped



Figure 3-3. SN54SC2T74-SEP Evaluation Board (Top View)




Figure 3-4. SN54SC2T74-SEP SEL Bias Diagram




Figure 3-5. SN54SC2T74-SEP SET Bias Diagram



Figure 3-6. SN54SC2T74-SEP Thermal Image for SEL

## 4 Irradiation Facility and Setup

The heavy-ion species used for the SEE studies on this product were provided and delivered by the Texas A&M University (TAMU) Cyclotron Radiation Effects Facility using a superconducting cyclotron and an advanced electron cyclotron resonance (ECR) ion source. At the fluxes used, the ion beams had good flux stability and high irradiation uniformity over a one inch diameter circular cross-sectional area for the in-air station. Uniformity is achieved by magnetic defocusing. The flux of the beam is regulated over a broad range spanning several orders of magnitude. For the majority of these studies, ion flux of  $1 \times 10^5$  ions /  $\text{cm}^2\text{-s}$  were used to provide heavy-ion fluences of approximately  $1 \times 10^7$  ions /  $\text{cm}^2$ . Ion uniformity for these experiments was between 95% and 98%.

Figure 4-1 shows one of the three SN54SC2T74-SEP test board used for experiments at the TAMU facility. The in-air gap between the device and the ion beam port window was maintained at 40mm for all runs.




Figure 4-1. SN54SC2T74-SEP Evaluation Board at the TAMU Facility

## 5 Results


### 5.1 SEL Results

During SEL characterization, the device was heated using forced hot air, maintaining device temperature at 125°C. A FLIR (FLIR ONE Pro LT) thermal camera was used to validate die temperature to make sure the device was accurately heated (see [SN54SC2T74-SEP Thermal Image for SEL.](#)) The species used for SEL testing was a Silver (<sup>109</sup>Ag) ion at 15MeV / μ with an angle-of-incidence of 0° for an LET<sub>EFF</sub> of 43MeV-cm<sup>2</sup>/ mg. A fluence of approximately 1 × 10<sup>7</sup> ions / cm<sup>2</sup> was used for the runs.


The three devices were powered up and exposed to the heavy-ions using the maximum recommended supply voltage of 5.5V using a National Instruments™ PXI Chassis PXIe-4139 and a 5V, 1MHz square wave input using a Tektronix® AFG3102 function generator. The run duration to achieve this fluence was approximately 90 seconds. As listed in [Table 5-1](#), no SEL events were observed during the nine runs, indicating that the SN54SC2T74-SEP is SEL-free. [Figure 5-1](#), [Figure 5-2](#), and [Figure 5-3](#) show the plots of current versus time for runs one, four, and seven, respectively.

**Table 5-1. Summary of SN54SC2T74-SEP SEL Test Conditions and Results**


Run Number	Unit Number	Distance (mm)	Temperature (°C)	Ion	Angle	Flux (ions × cm <sup>2</sup> / mg)	Fluence (Number of ions)	LET <sub>EFF</sub> (MeV × cm <sup>2</sup> /mg)	Did an SEL event occur?
1	1	40	124	Ag	0°	1.00E+05	1.00E+07	43	No
2	1	40	124	Ag	0°	1.00E+05	1.00E+07	43	No
3	1	40	124	Ag	0°	1.00E+05	1.00E+07	43	No
4	2	40	123	Ag	0°	1.00E+05	1.00E+07	43	No
5	2	40	123	Ag	0°	1.00E+05	1.00E+07	43	No
6	2	40	123	Ag	0°	1.00E+05	1.00E+07	43	No
7	3	40	124	Ag	0°	1.00E+05	1.00E+07	43	No
8	3	40	124	Ag	0°	1.00E+05	1.00E+07	43	No
9	3	40	124	Ag	0°	1.00E+05	1.00E+07	43	No



**Figure 5-1. Current versus Time for Run 1 of the SN54SC2T74-SEP at T = 125°C**



**Figure 5-2. Current versus Time for Run 4 of the SN54SC2T74-SEP at T = 125°C**



**Figure 5-3. Current versus Time for Run 7 of the SN54SC2T74-SEP at T = 125°C**

No SEL events were observed, indicating that the SN54SC2T74-SEP is SEL-immune at  $LET_{EFF} = 43 \text{ MeV}\cdot\text{cm}^2 / \text{mg}$  and  $T = 125^\circ\text{C}$ . Using the MFTF method shown in [Single-Event Effects \(SEE\) Confidence Internal Calculations](#), the upper-bound cross-section (using a 95% confidence level) is calculated as:

$$\sigma_{SEL} \leq 1.23 \times 10^{-7} \text{ cm}^2 / \text{device for } LET_{EFF} = 43 \text{ MeV}\cdot\text{cm}^2 / \text{mg and } T = 125^\circ\text{C} \quad (1)$$



## 5.2 Single-Event Transients (SET)

SETs are defined as heavy-ion-induced transient upsets on output pin 1Q of the SN54SC2T74-SEP. SET testing was performed at room temperature (no external temperature control applied). The species used for the SET testing was  $^{109}\text{Ag}$  for a  $\text{LET}_{\text{EFF}} = 48\text{MeV} \times \text{cm}^2 / \text{mg}$ . Flux of approximately  $10^5$  ions /  $\text{cm}^2 \times \text{s}$  and a fluence of approximately  $10^7$  ions /  $\text{cm}^2$  were used for the SET runs.

Three units were tested across multiple input conditions to determine the worst-case setup for SETs. The unit was tested with  $V_{\text{CC}}$  of 1.2V, 1.8V, and 5.5V and window trigger of  $\pm 1\%$ ,  $\pm 5\%$ ,  $\pm 10\%$ , and  $\pm 20\%$ . All combinations of  $V_{\text{CC}}$  and window triggers showed no transient upsets, as listed in [Table 5-2](#)

To capture SETs, one NI PXI-5110 scope card was used to continuously monitor the output voltage on pin 1Q. The NI scope was programmed to a sample rate of 100M samples per second (S / s) and recorded 10k samples, with a 20% pretrigger reference, in case of an event (trigger). Under heavy-ions, the SN54SC2T74-SEP did not exhibit any transient upsets

**Table 5-2. Summary of SN54SC2T74-SEP SET Test Condition and Results**

Run Number	Unit Number	Ion	$\text{LET}_{\text{EFF}}$ (MeV $\times$ $\text{cm}^2/\text{mg}$ )	FLUX (ions $\times$ $\text{cm}^2/\text{mg}$ )	Fluence (Number ions)	Window Trigger	SET Upsets
21	1	$^{109}\text{Ag}$	48	$1.05 \times 10^5$	$9.98 \times 10^6$	20%	0
22	1	$^{109}\text{Ag}$	48	$1.07 \times 10^5$	$1.00 \times 10^7$	20%	0
23	1	$^{109}\text{Ag}$	48	$1.05 \times 10^5$	$1.00 \times 10^7$	20%	0
24	1	$^{109}\text{Ag}$	48	$1.08 \times 10^5$	$9.95 \times 10^6$	10%	0
25	2	$^{109}\text{Ag}$	48	$1.06 \times 10^5$	$1.00 \times 10^7$	20%	0
26	2	$^{109}\text{Ag}$	48	$1.04 \times 10^5$	$1.00 \times 10^7$	20%	0
27	2	$^{109}\text{Ag}$	48	$1.01 \times 10^5$	$1.00 \times 10^7$	20%	0
28	2	$^{109}\text{Ag}$	48	$1.18 \times 10^5$	$9.96 \times 10^6$	20%	0
29	2	$^{109}\text{Ag}$	48	$1.14 \times 10^5$	$9.98 \times 10^6$	20%	0
30	2	$^{109}\text{Ag}$	48	$1.19 \times 10^5$	$1.00 \times 10^7$	20%	0
31	3	$^{109}\text{Ag}$	48	$1.23 \times 10^5$	$9.95 \times 10^6$	20%	0
32	3	$^{109}\text{Ag}$	48	$1.22 \times 10^5$	$9.98 \times 10^6$	20%	0
33	3	$^{109}\text{Ag}$	48	$1.23 \times 10^5$	$9.95 \times 10^6$	20%	0
34	3	$^{109}\text{Ag}$	48	$1.27 \times 10^5$	$1.00 \times 10^7$	20%	0
35	3	$^{109}\text{Ag}$	48	$1.23 \times 10^5$	$1.00 \times 10^7$	20%	0
36	3	$^{109}\text{Ag}$	48	$1.17 \times 10^5$	$1.00 \times 10^7$	20%	0
37	3	$^{109}\text{Ag}$	48	$1.16 \times 10^5$	$9.98 \times 10^6$	5%	0
38	3	$^{109}\text{Ag}$	48	$1.18 \times 10^5$	$9.96 \times 10^6$	1%	0
40	3	$^{109}\text{Ag}$	48	$1.10 \times 10^5$	$9.94 \times 10^6$	1%	0

### 5.3 Event Rate Calculations

Event rates were calculated for LEO (ISS) and GEO environments by combining CREME96 orbital integral flux estimations and simplified SEE cross-sections according to methods shown in [Heavy Ion Orbital Environment Single-Event Effects Estimations](#). A minimum shielding configuration of 100mils (2.54mm) of aluminum, and *worst-week* solar activity is assumed. (This is similar to a 99% upper bound for the environment.) Using the 95% upper-bounds for the SEL and the SET, the event rate calculation for the SEL and the SET is listed in [Table 5-3](#) and [Table 5-4](#), respectively. Note that this number is for reference since no SEL or SET events were observed.

**Table 5-3. SEL Event Rate Calculations for Worst-Week LEO and GEO Orbits**

Orbit Type	Onset LET <sub>EFF</sub> (MeV-cm <sup>2</sup> / mg)	CREME96 Integral FLUX (per day / cm <sup>2</sup> )	σSAT (cm <sup>2</sup> )	Event Rate (per day)	Event Rate (FIT)	MTBE (Years)
LEO (ISS)	48	6.40 × 10 <sup>-4</sup>	1.23 × 10 <sup>-7</sup>	7.87 × 10 <sup>-11</sup>	3.28 × 10 <sup>-3</sup>	3.48 × 10 <sup>7</sup>
GEO		2.17 × 10 <sup>-3</sup>		2.67 × 10 <sup>-10</sup>	1.11 × 10 <sup>-2</sup>	1.03 × 10 <sup>7</sup>

**Table 5-4. SET Event Rate Calculations for Worst-Week LEO and GEO Orbits**

Orbit Type	Onset LET <sub>EFF</sub> (MeV-cm <sup>2</sup> / mg)	CREME96 Integral FLUX (per day / cm <sup>2</sup> )	σSAT (cm <sup>2</sup> )	Event Rate (per day)	Event Rate (FIT)	MTBE (Years)
LEO (ISS)	48	6.40 × 10 <sup>-4</sup>	1.94 × 10 <sup>-8</sup>	1.24 × 10 <sup>-11</sup>	5.16 × 10 <sup>-4</sup>	2.21 × 10 <sup>8</sup>
GEO		2.17 × 10 <sup>-3</sup>		4.20 × 10 <sup>-11</sup>	1.75 × 10 <sup>-3</sup>	6.52 × 10 <sup>7</sup>

MTBE is the mean-time-between-events in years at the given event rates. These rates clearly demonstrate the SEE robustness of the SN54SC2T74-SEP in two harshly conservative space environments. Customers using the SN54SC2T74-SEP must only use the above estimations as a rough guide and TI recommends performing event rate calculations based on specific mission orbital and shielding parameters to determine if the product satisfies the reliability requirements for the specific mission.

## 6 Summary

The purpose of this study was to characterize the effects of heavy-ion irradiation on the single-event latch-up (SEL) performance of the SN54SC2T74-SEP radiation-tolerant, 1.2V to 5.5V dual D-type flip-flop with integrated translation. SEE performance was verified at minimum (1.2V) and maximum (5.5V) operating conditions. Heavy-ions with an  $LET_{EFF}$  of 43MeV-cm<sup>2</sup>/ mg were used to irradiate three production devices with a fluence of  $1 \times 10^7$  ions / cm<sup>2</sup>. The results demonstrate that the SN54SC2T74-SEP is SEL-free up to  $LET_{EFF} = 43\text{MeV-cm}^2/\text{mg}$  as 125°C. SET performance for minimum and maximum operating voltages saw no excursions  $\geq |1\%|$ , as shown and discussed in this report.

## 7 References

1. M. Shoga and D. Binder, "Theory of Single Event Latchup in Complementary Metal-Oxide Semiconductor Integrated Circuits", *IEEE Trans. Nucl. Sci.*, Vol. 33(6), Dec. 1986, pp. 1714-1717.
2. G. Bruguier and J. M. Palau, "Single particle-induced latchup", *IEEE Trans. Nucl. Sci.*, Vol. 43(2), Mar. 1996, pp. 522-532.
3. Texas A&M University, [Texas A&M University Cyclotron Institute Radiation Effects Facility](#), webpage.
4. James F. Ziegler, [The Stopping and Range of Ions in Matter \(SRIM\)](#), webpage.
5. D. Kececioglu, "Reliability and Life Testing Handbook", Vol. 1, PTR Prentice Hall, New Jersey, 1993, pp. 186-193.
6. Vanderbilt University, [ISDE CRÈME-MC](#), webpage.
7. A. J. Tylka, J. H. Adams, P. R. Boberg, et al., "CREME96: A Revision of the Cosmic Ray Effects on Micro-Electronics Code", *IEEE Trans. on Nucl. Sci.*, Vol. 44(6), Dec. 1997, pp. 2150-2160.
8. A. J. Tylka, W. F. Dietrich, and P. R. Boberg, "Probability distributions of high-energy solar-heavy-ion fluxes from IMP-8: 1973-1996", *IEEE Trans. on Nucl. Sci.*, Vol. 44(6), Dec. 1997, pp. 2140-2149.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2024, Texas Instruments Incorporated