


LMH32401RGTEVM Evaluation Module



This user's guide describes the characteristics, operation, and use of the LMH32401RGTEVM. This evaluation module (EVM) is an evaluation and development kit for evaluating the LMH32401RGTEVM device, a programmable-gain, single-ended input to differential output transimpedance amplifier for light detection and ranging (LIDAR) applications and laser distance measurement systems. A complete circuit description as well as schematic diagram and bill of materials are included in this document.

Throughout this document, the abbreviation *EVM* and the term *evaluation module* are synonymous with the LMH32401RGTEVM.

The following related documentation is available through the Texas Instruments web site at www.ti.com.

Related Documentation

Device	Literature Number
LMH32401 data sheet	SBOS965

Contents

1	Introduction	2
2	Power Connections	3
3	Input and Output Connections	3
4	Optional EVM Configuration for Photodiode Input	4
5	Board Layout	5
6	Schematic and Bill of Materials	7

List of Figures

1	Top Layer	5
2	Ground Layer	5
3	Power Layer	5
4	Bottom Layer	5
5	LMH32401RGTEVM Schematic	7

List of Tables

1	LMH32401RGTEVM Specifications	2
2	EVM Bottom-Side Diode Trace Connections	4
3	Bill of Materials	8

Trademarks

All trademarks are the property of their respective owners.

1 Introduction

The LMH32401RGTEVM is an evaluation module (EVM) for the LMH32401IRGT differential output transimpedance amplifier. The EVM features a transformer to convert the output to a $50\text{-}\Omega$ single-ended connection for easy measurement with standard test equipment, and the option to convert to fully-differential DC-coupled signals. The input is $50\text{-}\Omega$ matched and configured by default to receive a voltage input that is converted to a current through a $2\text{-k}\Omega$ resistor, but can be reconfigured to receive a true current input with optional photodiode bias connections on the back of the board. The EVM also includes easy-to-use jumpers to control the device gain, input bias current cancellation, and shutdown functions.

1.1 Features

- Configured for single-ended voltage input and output with $50\text{-}\Omega$ matched SMA connections
- Includes options to connect a current input source with bias connections for edge mounting photodiodes
- Optional DC-coupled differential output configuration
- Jumpers included for easy control of gain, bias current cancellation, and power-down
- Designed for single 3.3-V supply operation

1.2 EVM Specifications

Table 1 lists the typical performance specifications for the LMH32401RGTEVM.

Table 1. LMH32401RGTEVM Specifications

Specification	Typical Value Range
Single-supply voltage range (VEE = ground)	3 V to 3.45 V
Quiescent current	29 mA
Output voltage swing (VCC = 3.3 V, 100- Ω load)	5 V _{PP}
Linear output current (VCC = 3.3 V, 25- Ω load)	26.6 mA

2 Power Connections

The LMH32401RGTEVM is equipped with a wire socket to easily connect power. The positive supply input is labeled VDD and ground is labeled GND.

3 Input and Output Connections

The LMH32401RGTEVM is equipped with SMA connectors for easy connection of signal generators and analysis equipment. As shipped, the EVM is configured for a single-ended input and output, both with $50\text{-}\Omega$ termination. The differential output of the amplifier is converted to a single-ended output through transformer T1 on the board. OUT+ is the output connector for single-ended output signals, and is terminated to $50\text{-}\Omega$ single-ended. To use the EVM with a DC-coupled differential output, remove resistor R7 and transformer T1, and short the connections across the removed transformer input and outputs. When converting to differential, the output resistors may need to be modified to achieve a desired impedance match. For more details and instructions on how to reconfigure the EVM, see the applications section, schematics, and layouts in the [LMH32401 500-MHz, Programmable Gain, Differential Output Transimpedance Amplifier](#) data sheet.

3.1 Gain Control

The amplifier gain can be adjusted using the GAIN jumper on the board to switch between the $2\text{-k}\Omega$ and $20\text{-k}\Omega$ gain settings. By default, the EVM has R1 populated with a $2\text{-k}\Omega$ resistor, which creates an effective voltage gain of 1 V/V and 10 V/V, respectively, for the two different gain settings.

3.2 Input DC Current Cancellation

The LMH32401 device features an input DC current cancellation circuit that is designed to remove any DC current that is present from a typical current input device such as a photodiode. This feature can be enabled or disabled using the IDC_EN jumper on the board. By default, the DC current cancellation circuit is enabled.

3.3 Enable Function

The LMH32401 device includes an optional disable function to put the device in a low-power mode when it is not being used. The EVM ships with jumper EN that can be used to easily enable and disable the device. By default, the board ships with the device enabled.

3.4 Optional VOCM Pin Connection

The common-mode voltage of the differential outputs of the amplifier can be controlled using the VOCM test point or optional SMA connector. If left unconnected, the amplifier output common mode will default to 1.1 V. By default, the transformer on the EVM will AC couple the output of the device and remove the effect of the output common-mode voltage. To match the board to a device that requires DC outputs with a specified common mode (such as an analog to digital converter) the transformer must be removed.

3.5 Option VOD Connection

The LMH32401 device also features a differential output offset pin that controls the DC differential offset of the two outputs. The EVM features a test point VOD as well as an optional through-hole SMA connector footprint to drive this pin. If left floating, the DC output differential voltage defaults to 510 mV. This feature is designed to compensate for unipolar input signals to achieve the maximum dynamic range of the differential outputs. For more information see the [LMH32401 500-MHz, Programmable Gain, Differential Output Transimpedance Amplifier](#) data sheet.

4 Optional EVM Configuration for Photodiode Input

The LMH32401RGTEVM features an optional configuration to accept a photodiode input in a typical TO style package. By removing the IN SMA connector, R4, and C11, and shorting C10 and R1, the trace from IN is shorted to the input of the device. Along with traces A, B, and C on the bottom of the board, the input trace can be used to connect a common three-terminal photodiode in a TO package. The photodiode can be mounted over the edge of the board where the cathode can be connected to the input of the amplifier and the case and anode connections can be soldered to any of the three traces on the bottom of the board. The A, B, and C traces can then be configured to connect to either ground or the BIAS test point where an external bias voltage can be applied. [Table 2](#) shows a list of the resistor connections that can be shorted to connect the traces to bias or ground. By default, the EVM has trace A connected to the bias test point and trace B connected to ground.


Table 2. EVM Bottom-Side Diode Trace Connections⁽¹⁾

Trace	Short to Connect to Bias	Short to Connect to Ground
A	R9	R8
B	R13	R11
C	R15	R14

⁽¹⁾ Each trace should only be shorted to either bias or ground. Do not short the traces to both bias and ground simultaneously or a power-supply short could occur.

5 Board Layout

Figure 1 to Figure 4 illustrate the board layers in top-to-bottom order.






Figure 3. Power Layer




Figure 4. Bottom Layer

6 Schematic and Bill of Materials

This section provides the schematic and bill of materials (BOM) for the LMH32401RGTEVM.

6.1 Schematic

Figure 5 shows the EVM schematic.




Figure 5. LMH32401RGTEVM Schematic

6.2 Bill of Materials

Table 3 lists the EVM BOM.

Table 3. Bill of Materials

Item #	Designator	Qty	Value	Part Number	Manufacturer	Description	Package Reference
2	C1	1	2.2 μ F	GCM31CR71H225KA55L	MuRata	CAP, CERM, 2.2 μ F, 50 V, \pm 10%, X7R, AEC-Q200 Grade 1, 1206	1206
3	C2, C4, C10	3	1 μ F	GRM155R6YA105KE11D	MuRata	CAP, CERM, 1 μ F, 35 V, \pm 10%, X5R, 0402	402
4	C3, C5	2	100 pF	CC0201JRNPO8BN101	Yageo	CAP, CERM, 100 pF, 25 V, \pm 5%, C0G/NP0, 0201	201
5	C6, C7	2	0.033 μ F	CC0402KRX7R8BB333	Yageo	CAP, CERM, 0.033 μ F, 25 V, \pm 10%, X7R, 0402	402
6	C8	1	1 μ F	C2012X7S2A105K125AB	TDK	CAP, CERM, 1 μ F, 100 V, \pm 10%, X7S, 0805	805
7	C9	1	0.01 μ F	C0603C103K2RACTU	Kemet	CAP, CERM, 0.01 μ F, 200 V, \pm 10%, X7R, 0603	603
8	C11	1	1 pF	GJM0335C1E1R0WB01D	MuRata	CAP, CERM, 1 pF, 25 V, \pm 5%, C0G/NP0, 0201	201
9	C12	1	1 pF	GJM1555C1H1R0BB01D	MuRata	CAP, CERM, 1 pF, 50 V, \pm 10%, C0G/NP0, 0402	402
10	C13, C14, C15, C16, C17	5	0.1 μ F	06033C104KAT2A	AVX	CAP, CERM, 0.1 μ F, 25 V, \pm 10%, X7R, 0603	603
11	C19	1	0.01 μ F	GCM155R71H103KA55D	MuRata	CAP, CERM, 0.01 μ F, 50 V, \pm 10%, C0G/NP0, 0402	402
12	EN, GAIN, IDC_EN	3		PBC03SAAN	Sullins Connector Solutions	Header, 100 mil, 3 x 1, Gold, TH	PBC03SAAN
13	GND, VDD	2		575-4	Keystone	Standard Banana Jack, Uninsulated, 5.5 mm	Keystone_575-4
14	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
15	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5" L #4-40 Nylon	Standoff
16	IN, OUT-, OUT+	3		142-0701-851	Cinch Connectivity	Connector, End launch SMA, 50 Ω , SMT	SMA End Launch
17	L1	1	1000 Ω	MPZ2012S102AT000	TDK	Ferrite Bead, 1000 Ω @ 100 MHz, 1.5 A, 0805	805
18	R1	1	2.00 k Ω	CRCW02012K00FKED	Vishay-Dale	RES, 2.00 k, 1%, 0.05 W, 0201	201
19	R3, R6	2	24.9	CRCW040224R9FKED	Vishay-Dale	RES, 24.9, 1%, 0.063 W, 0402	402
20	R4	1	50	FC0402E50R0BTBST1	Vishay Thin Film	RES, 50, 0.1%, 0.5 W, 0402	402
21	R7	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	603
22	R9, R11	2	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	402
23	SH-EN, SH-GAIN, SH-IDC	3	1 x 2	SNT-100-BK-G	Samtec	Shunt, 100mil, Gold plated, Black	Shunt
24	T1	1	15 μ H	JA4220-ALB	Coilcraft CPS	Transformer, 15 μ H, SMT	3.81x3.81mm
25	TP1, TP2	2		5006	Keystone	Test Point, Compact, Black, TH	Black Compact Testpoint
26	TP3	1		5005	Keystone	Test Point, Compact, Red, TH	Red Compact Testpoint
27	TP4, TP5	2		5007	Keystone	Test Point, Compact, White, TH	White Compact Testpoint
28	U1	1		LMH32401RG	Texas Instruments	Programmable Gain, Differential Output Transimpedance Amplifier, RGT0016C (VQFN-16)	RGT0016C

STANDARD TERMS FOR EVALUATION MODULES

1. *Delivery:* TI delivers TI evaluation boards, kits, or modules, including any accompanying demonstration software, components, and/or documentation which may be provided together or separately (collectively, an "EVM" or "EVMs") to the User ("User") in accordance with the terms set forth herein. User's acceptance of the EVM is expressly subject to the following terms.
 - 1.1 EVMs are intended solely for product or software developers for use in a research and development setting to facilitate feasibility evaluation, experimentation, or scientific analysis of TI semiconductors products. EVMs have no direct function and are not finished products. EVMs shall not be directly or indirectly assembled as a part or subassembly in any finished product. For clarification, any software or software tools provided with the EVM ("Software") shall not be subject to the terms and conditions set forth herein but rather shall be subject to the applicable terms that accompany such Software
 - 1.2 EVMs are not intended for consumer or household use. EVMs may not be sold, sublicensed, leased, rented, loaned, assigned, or otherwise distributed for commercial purposes by Users, in whole or in part, or used in any finished product or production system.
- 2 *Limited Warranty and Related Remedies/Disclaimers:*
 - 2.1 These terms do not apply to Software. The warranty, if any, for Software is covered in the applicable Software License Agreement.
 - 2.2 TI warrants that the TI EVM will conform to TI's published specifications for ninety (90) days after the date TI delivers such EVM to User. Notwithstanding the foregoing, TI shall not be liable for a nonconforming EVM if (a) the nonconformity was caused by neglect, misuse or mistreatment by an entity other than TI, including improper installation or testing, or for any EVMs that have been altered or modified in any way by an entity other than TI, (b) the nonconformity resulted from User's design, specifications or instructions for such EVMs or improper system design, or (c) User has not paid on time. Testing and other quality control techniques are used to the extent TI deems necessary. TI does not test all parameters of each EVM. User's claims against TI under this Section 2 are void if User fails to notify TI of any apparent defects in the EVMs within ten (10) business days after delivery, or of any hidden defects with ten (10) business days after the defect has been detected.
 - 2.3 TI's sole liability shall be at its option to repair or replace EVMs that fail to conform to the warranty set forth above, or credit User's account for such EVM. TI's liability under this warranty shall be limited to EVMs that are returned during the warranty period to the address designated by TI and that are determined by TI not to conform to such warranty. If TI elects to repair or replace such EVM, TI shall have a reasonable time to repair such EVM or provide replacements. Repaired EVMs shall be warranted for the remainder of the original warranty period. Replaced EVMs shall be warranted for a new full ninety (90) day warranty period.

WARNING

Evaluation Kits are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems.

User shall operate the Evaluation Kit within TI's recommended guidelines and any applicable legal or environmental requirements as well as reasonable and customary safeguards. Failure to set up and/or operate the Evaluation Kit within TI's recommended guidelines may result in personal injury or death or property damage. Proper set up entails following TI's instructions for electrical ratings of interface circuits such as input, output and electrical loads.

NOTE:

EXPOSURE TO ELECTROSTATIC DISCHARGE (ESD) MAY CAUSE DEGRADATION OR FAILURE OF THE EVALUATION KIT; TI RECOMMENDS STORAGE OF THE EVALUATION KIT IN A PROTECTIVE ESD BAG.

3 Regulatory Notices:

3.1 United States

3.1.1 Notice applicable to EVMs not FCC-Approved:

FCC NOTICE: This kit is designed to allow product developers to evaluate electronic components, circuitry, or software associated with the kit to determine whether to incorporate such items in a finished product and software developers to write software applications for use with the end product. This kit is not a finished product and when assembled may not be resold or otherwise marketed unless all required FCC equipment authorizations are first obtained. Operation is subject to the condition that this product not cause harmful interference to licensed radio stations and that this product accept harmful interference. Unless the assembled kit is designed to operate under part 15, part 18 or part 95 of this chapter, the operator of the kit must operate under the authority of an FCC license holder or must secure an experimental authorization under part 5 of this chapter.

3.1.2 For EVMs annotated as FCC – FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant:

CAUTION

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

3.2 Canada

3.2.1 For EVMs issued with an Industry Canada Certificate of Conformance to RSS-210 or RSS-247

Concerning EVMs Including Radio Transmitters:

This device complies with Industry Canada license-exempt RSSs. Operation is subject to the following two conditions:

(1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concernant les EVMs avec appareils radio:

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes: (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concerning EVMs Including Detachable Antennas:

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication. This radio transmitter has been approved by Industry Canada to operate with the antenna types listed in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante. Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur

3.3 Japan

3.3.1 *Notice for EVMs delivered in Japan:* Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_01.page 日本国内に輸入される評価用キット、ボードについては、次のところをご覧ください。
http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_01.page

3.3.2 *Notice for Users of EVMs Considered "Radio Frequency Products" in Japan:* EVMs entering Japan may not be certified by TI as conforming to Technical Regulations of Radio Law of Japan.

If User uses EVMs in Japan, not certified to Technical Regulations of Radio Law of Japan, User is required to follow the instructions set forth by Radio Law of Japan, which includes, but is not limited to, the instructions below with respect to EVMs (which for the avoidance of doubt are stated strictly for convenience and should be verified by User):

1. Use EVMs in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
2. Use EVMs only after User obtains the license of Test Radio Station as provided in Radio Law of Japan with respect to EVMs, or
3. Use of EVMs only after User obtains the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to EVMs. Also, do not transfer EVMs, unless User gives the same notice above to the transferee. Please note that if User does not follow the instructions above, User will be subject to penalties of Radio Law of Japan.

【無線電波を送信する製品の開発キットをお使いになる際の注意事項】開発キットの中には技術基準適合証明を受けていないものがあります。技術適合証明を受けていないものご使用に際しては、電波法遵守のため、以下のいずれかの措置を取っていただく必要がありますのでご注意ください。

1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用いただく。
2. 実験局の免許を取得後ご使用いただく。
3. 技術基準適合証明を取得後ご使用いただく。

なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。

上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。日本テキサス・インスツルメンツ株式会社

東京都新宿区西新宿 6 丁目 24 番 1 号

西新宿三井ビル

3.3.3 *Notice for EVMs for Power Line Communication:* Please see http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_02.page
電力線搬送波通信についての開発キットをお使いになる際の注意事項については、次のところをご覧ください。http://www.tij.co.jp/lsds/ti_ja/general/eStore/notice_02.page

3.4 European Union

3.4.1 *For EVMs subject to EU Directive 2014/30/EU (Electromagnetic Compatibility Directive):*

This is a class A product intended for use in environments other than domestic environments that are connected to a low-voltage power-supply network that supplies buildings used for domestic purposes. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

4 *EVM Use Restrictions and Warnings:*

4.1 EVMS ARE NOT FOR USE IN FUNCTIONAL SAFETY AND/OR SAFETY CRITICAL EVALUATIONS, INCLUDING BUT NOT LIMITED TO EVALUATIONS OF LIFE SUPPORT APPLICATIONS.

4.2 User must read and apply the user guide and other available documentation provided by TI regarding the EVM prior to handling or using the EVM, including without limitation any warning or restriction notices. The notices contain important safety information related to, for example, temperatures and voltages.

4.3 *Safety-Related Warnings and Restrictions:*

4.3.1 User shall operate the EVM within TI's recommended specifications and environmental considerations stated in the user guide, other available documentation provided by TI, and any other applicable requirements and employ reasonable and customary safeguards. Exceeding the specified performance ratings and specifications (including but not limited to input and output voltage, current, power, and environmental ranges) for the EVM may cause personal injury or death, or property damage. If there are questions concerning performance ratings and specifications, User should contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may also result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM user guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, even with the inputs and outputs kept within the specified allowable ranges, some circuit components may have elevated case temperatures. These components include but are not limited to linear regulators, switching transistors, pass transistors, current sense resistors, and heat sinks, which can be identified using the information in the associated documentation. When working with the EVM, please be aware that the EVM may become very warm.

4.3.2 EVMs are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems. User assumes all responsibility and liability for proper and safe handling and use of the EVM by User or its employees, affiliates, contractors or designees. User assumes all responsibility and liability to ensure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard. User assumes all responsibility and liability for any improper or unsafe handling or use of the EVM by User or its employees, affiliates, contractors or designees.

4.4 User assumes all responsibility and liability to determine whether the EVM is subject to any applicable international, federal, state, or local laws and regulations related to User's handling and use of the EVM and, if applicable, User assumes all responsibility and liability for compliance in all respects with such laws and regulations. User assumes all responsibility and liability for proper disposal and recycling of the EVM consistent with all applicable international, federal, state, and local requirements.

5. *Accuracy of Information:* To the extent TI provides information on the availability and function of EVMs, TI attempts to be as accurate as possible. However, TI does not warrant the accuracy of EVM descriptions, EVM availability or other information on its websites as accurate, complete, reliable, current, or error-free.

6. *Disclaimers:*

6.1 EXCEPT AS SET FORTH ABOVE, EVMS AND ANY MATERIALS PROVIDED WITH THE EVM (INCLUDING, BUT NOT LIMITED TO, REFERENCE DESIGNS AND THE DESIGN OF THE EVM ITSELF) ARE PROVIDED "AS IS" AND "WITH ALL FAULTS." TI DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, REGARDING SUCH ITEMS, INCLUDING BUT NOT LIMITED TO ANY EPIDEMIC FAILURE WARRANTY OR IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF ANY THIRD PARTY PATENTS, COPYRIGHTS, TRADE SECRETS OR OTHER INTELLECTUAL PROPERTY RIGHTS.

6.2 EXCEPT FOR THE LIMITED RIGHT TO USE THE EVM SET FORTH HEREIN, NOTHING IN THESE TERMS SHALL BE CONSTRUED AS GRANTING OR CONFERRING ANY RIGHTS BY LICENSE, PATENT, OR ANY OTHER INDUSTRIAL OR INTELLECTUAL PROPERTY RIGHT OF TI, ITS SUPPLIERS/LICENSENSORS OR ANY OTHER THIRD PARTY, TO USE THE EVM IN ANY FINISHED END-USER OR READY-TO-USE FINAL PRODUCT, OR FOR ANY INVENTION, DISCOVERY OR IMPROVEMENT, REGARDLESS OF WHEN MADE, CONCEIVED OR ACQUIRED.

7. *USER'S INDEMNITY OBLIGATIONS AND REPRESENTATIONS.* USER WILL DEFEND, INDEMNIFY AND HOLD TI, ITS LICENSORS AND THEIR REPRESENTATIVES HARMLESS FROM AND AGAINST ANY AND ALL CLAIMS, DAMAGES, LOSSES, EXPENSES, COSTS AND LIABILITIES (COLLECTIVELY, "CLAIMS") ARISING OUT OF OR IN CONNECTION WITH ANY HANDLING OR USE OF THE EVM THAT IS NOT IN ACCORDANCE WITH THESE TERMS. THIS OBLIGATION SHALL APPLY WHETHER CLAIMS ARISE UNDER STATUTE, REGULATION, OR THE LAW OF TORT, CONTRACT OR ANY OTHER LEGAL THEORY, AND EVEN IF THE EVM FAILS TO PERFORM AS DESCRIBED OR EXPECTED.

8. *Limitations on Damages and Liability:*

8.1 *General Limitations.* IN NO EVENT SHALL TI BE LIABLE FOR ANY SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL, OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THESE TERMS OR THE USE OF THE EVMS, REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. EXCLUDED DAMAGES INCLUDE, BUT ARE NOT LIMITED TO, COST OF REMOVAL OR REINSTALLATION, ANCILLARY COSTS TO THE PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES, RETESTING, OUTSIDE COMPUTER TIME, LABOR COSTS, LOSS OF GOODWILL, LOSS OF PROFITS, LOSS OF SAVINGS, LOSS OF USE, LOSS OF DATA, OR BUSINESS INTERRUPTION. NO CLAIM, SUIT OR ACTION SHALL BE BROUGHT AGAINST TI MORE THAN TWELVE (12) MONTHS AFTER THE EVENT THAT GAVE RISE TO THE CAUSE OF ACTION HAS OCCURRED.

8.2 *Specific Limitations.* IN NO EVENT SHALL TI'S AGGREGATE LIABILITY FROM ANY USE OF AN EVM PROVIDED HEREUNDER, INCLUDING FROM ANY WARRANTY, INDEMNITY OR OTHER OBLIGATION ARISING OUT OF OR IN CONNECTION WITH THESE TERMS, EXCEED THE TOTAL AMOUNT PAID TO TI BY USER FOR THE PARTICULAR EVM(S) AT ISSUE DURING THE PRIOR TWELVE (12) MONTHS WITH RESPECT TO WHICH LOSSES OR DAMAGES ARE CLAIMED. THE EXISTENCE OF MORE THAN ONE CLAIM SHALL NOT ENLARGE OR EXTEND THIS LIMIT.

9. *Return Policy.* Except as otherwise provided, TI does not offer any refunds, returns, or exchanges. Furthermore, no return of EVM(s) will be accepted if the package has been opened and no return of the EVM(s) will be accepted if they are damaged or otherwise not in a resalable condition. If User feels it has been incorrectly charged for the EVM(s) it ordered or that delivery violates the applicable order, User should contact TI. All refunds will be made in full within thirty (30) working days from the return of the components(s), excluding any postage or packaging costs.

10. *Governing Law:* These terms and conditions shall be governed by and interpreted in accordance with the laws of the State of Texas, without reference to conflict-of-laws principles. User agrees that non-exclusive jurisdiction for any dispute arising out of or relating to these terms and conditions lies within courts located in the State of Texas and consents to venue in Dallas County, Texas. Notwithstanding the foregoing, any judgment may be enforced in any United States or foreign court, and TI may seek injunctive relief in any United States or foreign court.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025