


# TPA3244EVM

## Quick-Start Guide

→ Start Here



[ti.com/tool/tpa3244evm](https://ti.com/tool/tpa3244evm)

 TEXAS INSTRUMENTS

## Evaluation Kit Contents


- TPA3244 device
- PCB and external components to evaluate at full power
- RCA input jacks
- Banana output connectors
- No heatsink required

### Not included:


- Power supply: up to 31.5V, 12A for max power
- Speakers
- High-Resolution Audio Source

## Supported Output Configurations


See full User's Guide online for more information.



4-Channels—single-ended (SE)




2-Channels—bridge-tied load (BTL)



1-Channel—parallel bridge-tied load (PBTL)

## Getting Started

1. Ensure the RESET switch (S1) is in the RESET position.
2. Connect the power supply to the EVM using the PVDD and GND terminals.
3. Connect the first speaker to the output terminals OUTA and OUTB.
4. Connect the second speaker to the output terminals OUTC and OUTD.
5. Connect a high-resolution audio source to INA (J3) and INC (J18) for single-ended operation, which are default RCA input terminals.
6. Apply power (14V-31.5V) and move the RESET switch (S1) to the NORMAL position.



## Indicator Descriptions

3.3V – indicates the 3.3V rail used for GPIO control is active

12V – indicates the 12V rail used for amplifier gate drive is active

CLP\_OTWz – indicates when clipping or over-temperature warning occur

FAULTz – indicates when a fault condition occurs (requires toggling reset to clear fault)

FAULTz	CLP_OTWz	Possible Faults
ON	ON	OTW, OTE, UVP, OLP
ON	OFF	UVP, OLP
OFF	ON	OTW (solid), Early Clipping (flickering)
OFF	OFF	No Fault

OTW - Over-temperature warning (> 125°C)

OTE - Over-temperature error / shutdown (> 150°C)

UVP - Under-voltage protection

OLP - Over-load or over-current protection

## Default Jumper Configuration

Jumper	Default	Comment	Jumper	Default	Comment
J29	IN	PVDD to 15V BUCK	J24	IN	OUTC CAP SHUNT
J31	IN	15V BUCK to 12V TERM	J25	IN	OUTD CAP SHUNT
J32	IN	12V LDO to 12V TERM	J26	2 to 3	INC SELECT
J33	IN	3.3V LDO to 3.3V TERM	J27	2 to 3	IND SELECT
J21	OUT	CSTART SE	J7	OUT	PBTL SELECT INC
J16	3 to 4	MASTER MODE	J8	OUT	PBTL SELECT IND
J5	2 to 3	M1-BTL	J10	OUT	INA/B DIFF INPUT
J6	2 to 3	M2-BTL	J12	OUT	INC/D DIFF INPUT
J22	IN	OUTA CAP SHUNT	J4	1 to 2	INA/B SE INPUT
J23	IN	OUTB CAP SHUNT	J19	1 to 2	INC/D SE INPUT



## TPA32xx Product Family

Device	TPA3244	TPA3245	TPA3250	TPA3251	TPA3255
Max Power to BTL/ Ch (W)	110	145	130	220	315
Max Power to PBTL (W)	160	230	190	355	605
Min Supported BTL Load ( $\Omega$ )	4	3	4	3	4
Power Stage Supply Max (V)	31.5	31.5	38	38	53.5
Thermal Pad Location	Bottom	Top	Bottom	Top	Top
Package	44HTSSOP <sup>2</sup>	44HTSSOP <sup>1</sup>	44HTSSOP <sup>2</sup>	44HTSSOP <sup>1</sup>	44HTSSOP <sup>1</sup>
Dimensions	6.1 x 14mm				

<sup>1</sup>Pad-Up, pin-compatible package

<sup>2</sup>Pad-Down, pin-compatible package

Power numbers taken at 10% THD+N

## More Information

### TPA3244 Product Webpage

- TPA3244 Datasheet
- Complete TPA3244EVM User's Guide
- Schematics and layout

### High-Power Audio Portal

- New Products
- Technical Documents
- Support and Training
- Product Selection Tool

Available on: [ti.com/tpa3244](https://ti.com/tpa3244) Available on: [ti.com/highpoweraudio](https://ti.com/highpoweraudio)



**Engage in the  
Audio Amplifiers Support Forum**  
Search for solutions, get help and share  
knowledge with fellow engineers

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated