

## PMP23333 REV -1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
PCBA1	1		PMP23241A		PMP23241A	N/A
C1	1	1000uF	EMXB250ARA102MLH0S	United Chemi-Con	CAP, Al Electrolytic, 1000uF, 25V, +/-20%, 0.1ohm ESR @ 100kHz, 1.12Arms @ 100kHz, SMT	16mm Diam.; 17mm Height
C2, C3, C4	3	10uF	GCM32ER71E106KA57K	Murata	CAP, CERM, 10uF, 25V, X7R, 10%, 1210	1210
C5	1	0.1uF	CGA3E2X7R1E104K080AA	TDK	CAP, CERM, 0.1uF, 25V, X7R, 10%, 0603	0603
C6	1	10pF	CGA2B2C0G1H100D050BA	TDK	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402
C7, C8, C9, C10, C11	5	22uF	CL32B226KOJVPNE	Samsung Electro-Mechanics	CAP, CERM, 22 µF, 16 V,+/- 10%, X7R, AEC-Q200 Grade 1, 1210	1210
C12, C14	2	2.2uF	CL31B225KBHVPNE	Samsung	CAP, CERM, 2.2uF, 50V, X7R, 10%, 1206	1206
C13, C15	2	0.22uF	CGA3E3X7R1H224K080AB	TDK	CAP, CERM, 0.22 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C16	1	1uF	CGA3E1X7R1C105K080AC	TDK	CAP, CERM, 1 µF, 16 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C17	1	0.22uF	GCM188R71E224KA55D	MuRata	CAP, CERM, 0.22 uF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
D1	1	45V	V3FL45HM3/H	Vishay	Diode, Schottky, 45V, 3A, DO-219AB (SMF)	DO-219AB (SMF)
D2, D3	2	30V	RB510VM-30FHTE-17	Rohm	Diode, Schottky, 30V, 100mA, SOD-323F	SOD-323F
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
J1	1		6091	Keystone	Standard Banana Jack, Insulated, Red	6091
J2, J3	2		6092	Keystone	Standard Banana Jack, Insulated, Black	6092
J4	1		108-0907-001	Cinch Connectivity	BANANA JACK, 15A, Insulated, Nylon, Yellow	940x438x438mil
L1	1	4.7uH	XAL1510-472MEB	Coilcraft	Inductor, Shielded, Composite, 4.7 uH, 29 A, 0.00335 ohm, SMD	15.4 x 11 x 16.4mm
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch
Q1	1	40V	PMBT3906,235	Nexperia	Transistor, NPN, 40V, 200mA, SOT-23-3	SOT-23-3
R1	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R2, R3	2	0	RMCF0603ZT0R00	Stackpole Electronics Inc	RES, 0, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R4, R12	2	0	RMCF0402ZT0R00	Stackpole	RMCF/RMCP Series General Purpose Thick Film Standard Power and High Power Chip Resistor	0402 (1005 metric)
R5	1	100k	CRCW0402100KFED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R6	1	4.99k	CRCW04024K99FKED	Vishay-Dale	RES, 4.99 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R9	1	40.2k	CRCW040240K2FKED	Vishay-Dale	RES, 40.2 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R10	1	14.3k	CRCW040214K3FKED	Vishay-Dale	RES, 14.3 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R11, R16, R17	3	100k	RMCF0402FT100K	Stackpole Electronics Inc	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R15	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
TP1	1		5010	Keystone Electronics	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP2, TP3, TP12	3		5011	Keystone Electronics	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
TP5	1	GND	5011	Keystone Electronics	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
TP6	1		5014	Keystone Electronics	Test Point, Multipurpose, Yellow, TH	Yellow Multipurpose Testpoint
TP7, TP8, TP10, TP11	4		5012	Keystone Electronics	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
U1	1		LM61495RPHR	Texas Instruments	LM61495RPHR, RPH0016A (VQFN-HR-16)	RPH0016A
C18	0	100pF	CGA2B2C0G1H101J050BA	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402
Q2, Q3	0	40V	PMBT3906,235	Nexperia	Transistor, NPN, 40V, 200mA, SOT-23-3	SOT-23-3
R7	0	12.1k	CRCW040212K1FKED	Vishay-Dale	RES, 12.1 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R8	0	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R13, R14	0	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R18	0	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R19	0	0	RMCF0402ZT0R00	Stackpole	RMCF/RMCP Series General Purpose Thick Film Standard Power and High Power Chip Resistor	0402 (1005 metric)
R20	0	9.76k	CRCW04029K76FKED	Vishay-Dale	RES, 9.76 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
TP4	0	Vcntl_1	5012	Keystone Electronics	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
TP9	0	Vcntl_2	5012	Keystone Electronics	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2023, Texas Instruments Incorporated