

TIDA-00365 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C2	2	100pF	88004087505	Würth Elektronik	CAP, AL, 100 pF, 100 V, +/- 20%, 0.2 ohm, TH	010x125mm
2	C3, C4, C5, C40	4	3.3uF	C3216X7S2A335M160AB	TDK	CAP, CERM, 3.3 uF, 100 V, +/- 20%, X7S, 1206, 190	1206_190
3	C6, C7	2	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0805	0805
4	C8, C9, C14, C15	4	2200pF	06031C222JA12A	AVX	CAP, CERM, 2200 pF, 100 V, +/- 5%, X7R, 0603	0603
5	C10, C12	2	1uF	C2012X7S2A105K125AB	TDK	CAP, CERM, 1 uF, 100 V, +/- 10%, X7S, 0805	0805
6	C11, C13	2	0.01uF	06031C103KA72A	AVX	CAP, CERM, 0.01 uF, 100 V, +/- 10%, X7R, 0603	0603
7	C16, C46	2	0.01uF	885012205031	Würth Elektronik	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0402	0402
8	C17, C19	2	1uF	885012108017	Würth Elektronik	CAP, CERM, 1 uF, 16 V, +/- 20%, X5R, 0603	0603
9	C18, C36, C39, C44, C48	5	0.1uF	C1005X7R1E104M050BB	TDK	CAP, CERM, 0.1 uF, 25 V, +/- 20%, X7R, 0402	0402
10	C20	1	4700pF	GRM156R72A472KA01D	MuRata	CAP, CERM, 4700 pF, 100 V, +/- 10%, X7R, 0402	0402
11	C21, C22, C23	3	100pF	885012205055	Würth Elektronik	CAP, CERM, 100 pF, 50 V, +/- 10%, X7R, 0402	0402
12	C26, C27, C28, C29, C30, C31, C32, C33, C45, C47, C51	11	100pF	CC0402KRXR9BB101	Yageo America	CAP, CERM, 100 pF, 50 V, +/- 10%, X7R, 0402	0402
13	C34	1	3300pF	GRM188R72A332KA01D	MuRata	CAP, CERM, 3300 pF, 100 V, +/- 10%, X7R, 0603	0603
14	C35	1	0.1uF	GRM188R72A104KA35D	MuRata	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0603	0603
15	C37, C38	2	4.7uF	GRM188R61E475KE11D	MuRata	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X5R, 0603	0603
16	C41, C42, C43	3	1uF	C1608X5R1C105K	TDK	CAP, CERM, 1 uF, 16 V, +/- 10%, X5R, 0603	0603
17	C49	1	1000pF	885012205044	Würth Elektronik	CAP, CERM, 1000 pF, 25 V, +/- 10%, X7R, 0402	0402
18	C50	1	0.1uF	885012205044	Würth Elektronik	CAP, CERM, 1000 pF, 25 V, +/- 10%, X7R, 0402	0402
19	D1, D2, D5, D6, D9	5	100V	BAS316, 115	NXP Semiconductor	Diode, Ultrafast, 100 V, 0.25 A, SOD-323	SOD-323
20	D3, D4	2	91V	MMS25270BT1G	ON Semiconductor	Diode, Zener, 91 V, 500 mW, SOD-123	SOD-123
21	D7, D8, D13	3	Red	150060RS75000	Würth Elektronik	LED, Red, SMD	LED 0603
22	D10, D11	2	Green	150060GS75000	Würth Elektronik	LED, Green, SMD	LED 0603
23	D12	1	3.9V	BZT52C3V9T-7	Diodes Inc.	Diode, Zener, 3.9 V, 300 mW, SOD-523	SOD-523
24	D14	1	75V	BAV99W-7-F	Diodes Inc.	Diode, Switching, 75 V, 0.15 A, SOT-323	SOT-323
25	FID1, FID2, FID3, FID4, FID5, FID6	6		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
26	H1, H2, H3, H4	4		1514409	Farnell	Will add component to BOM. Useful for cables, nuts, etc. not in libraries	Screw, M3, 6mm, Nylon
27	H5	1		691351500003	Würth Elektronik	TERM BLOCK PLUG 3POS 5.08MM	
28	H6, H7, H8, H9	4		1902C	Standoff	Will add component to BOM. Useful for cables, nuts, etc. not in libraries	Hexagon Spacer
29	H10	1		691352510002	Würth Elektronik	TERM BLOCK PLUG 2POS 5.08MM	
30	J1, J4	2		61030421121	Würth Elektronik	Header, 2.54mm, 2x2, Gold, SMT	Header, 2.54mm, 2x2, Gold, SMT
31	J2	1		61031221121	Würth Elektronik	Header, 2.54mm, 6x2, Gold, SMT	Header, 2.54mm, 6x2, Gold, TH
32	J3	1		691311500103	Würth Elektronik	Header (Shrouded), 5.08mm, 3x1, Tin, TH	Header (Shrouded), 5.08mm, 3x1, TH
33	J5	1		691311500002	Würth Elektronik	Header (Shrouded), 5.08mm, 2x1, Tin, TH	Header (Shrouded), 5.08mm, 2x1, TH
34	L1	1	100uH	74404041101	Würth Elektronik	Inductor, Wirewound, Ferrite, 100 uH, 0.35 A, 1.697 ohm, SMD	3.7x4mm
35	L2	1	10uH	74479887310	Würth Elektronik	Inductor, Shielded Drum Core, Metal Composite, 10 uH, 0.35 A, 0.7 ohm, SMD	2.5x1x2mm
36	Q1, Q2, Q3, Q4	4	100V	CSD19534Q5A	Texas Instruments	MOSFET, N-CH, 100 V, 10 A, SON 5x6mm	SON 5x6mm
37	R1	1	0.01	CRA2512-FZ-R010ELF	Bourns	RES, 0.01, 1%, 3 W, 2512	2512
38	R2, R3, R8, R9	4	47	CRCW060347R0JNEA	Vishay-Dale	RES, 47, 5%, 0.1 W, 0603	0603
39	R4, R5, R10, R11	4	2.7	CRCW080527R0JNEA	Vishay-Dale	RES, 2.7, 5%, 0.125 W, 0805	0805
40	R6, R7	2	3.0	CRCW060330R0JNEA	Vishay-Dale	RES, 3.0, 5%, 0.1 W, 0603	0603
41	R12, R13, R43	3	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, 0603	0603
42	R14, R15	2	1.50k	CRCW04021K50FKED	Vishay-Dale	RES, 1.50 k, 1%, 0.063 W, 0402	0402
43	R17	1	23.2k	CRCW040223K2FKED	Vishay-Dale	RES, 23.2 k, 1%, 0.063 W, 0402	0402
44	R18, R19	2	180k	CRCW0402180KJNEA	Vishay-Dale	RES, 180 k, 5%, 0.063 W, 0402	0402
45	R20	1	16.5k	CRCW040216K5FKED	Vishay-Dale	RES, 16.5 k, 1%, 0.063 W, 0402	0402
46	R21, R22	2	10k	CRCW040210K0JNEA	Vishay-Dale	RES, 10 k, 5%, 0.063 W, 0402	0402
47	R25, R26, R27, R28, R65, R66	6	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
48	R29, R30, R33, R34, R35, R36, R37, R38	8	22	CRCW040222R0JNEA	Vishay-Dale	RES, 22, 5%, 0.063 W, 0402	0402
49	R31, R32	2	3.32k	CRCW04023K32FKED	Vishay-Dale	RES, 3.32 k, 1%, 0.063 W, 0402	0402
50	R39, R40, R56	3	1.2k	CRCW04021K20JNEA	Vishay-Dale	RES, 1.2 k, 5%, 0.063 W, 0402	0402
51	R41	1	3.0	CRCW040230R0JNEA	Vishay-Dale	RES, 3.0, 5%, 0.063 W, 0402	0402
52	R42, R48, R50, R55, R57, R58, R62, R63	8	51k	CRCW040251K0JNEA	Vishay-Dale	RES, 51 k, 5%, 0.063 W, 0402	0402
53	R44	1	20.0k	CRCW040220K0FKED	Vishay-Dale	RES, 20.0 k, 1%, 0.063 W, 0402	0402
54	R45	1	9.1k	CRCW04029K10JNEA	Vishay-Dale	RES, 9.1 k, 5%, 0.063 W, 0402	0402
55	R46, R47	2	200k	CRCW0402200KJNEA	Vishay-Dale	RES, 200 k, 5%, 0.063 W, 0402	0402
56	R48	1	2.26k	CRCW04022K26FKED	Vishay-Dale	RES, 2.26 k, 1%, 0.063 W, 0402	0402
57	R51	1	7.5k	CRCW04027K50JNEA	Vishay-Dale	RES, 7.5 k, 5%, 0.063 W, 0402	0402
58	R52	1	475	CRCW0402475R0FKED	Vishay-Dale	RES, 475, 1%, 0.063 W, 0402	0402
59	R53	1	820	CRCW0402820R0JNEA	Vishay-Dale	RES, 820, 5%, 0.063 W, 0402	0402
60	R54	1	806	CRCW0402806R0FKED	Vishay-Dale	RES, 806, 1%, 0.063 W, 0402	0402
61	R59	1	100k	CRCW0402100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.063 W, 0402	0402
62	R60	1	3.24k	CRCW04023K24FKED	Vishay-Dale	RES, 3.24 k, 1%, 0.063 W, 0402	0402
63	R61	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
64	R64	1	1.8k	CRCW04021K80JNEA	Vishay-Dale	RES, 1.8 k, 5%, 0.063 W, 0402	0402
65	R67	1	1.8k	CRCW04021K80JNEA	Vishay-Dale	RES, 1.8 k, 5%, 0.063 W, 0402	0402
66	R68	1	487k	CRCW0402487KFKED	Vishay-Dale	RES, 487 k, 1%, 0.063 W, 0402	0402
67	R69	1	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
68	R70	1	100	CRCW0402100R0JNEA	Vishay-Dale	RES, 100, 5%, 0.063 W, 0402	0402
69	R71	1	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
70	R72	1	3.09k	CRCW04023K09FKED	Vishay-Dale	RES, 3.09 k, 1%, 0.063 W, 0402	0402
71	SW1	1		TL1015AF1600G	E-Switch	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	Switch, 4.4x2x2.9 mm
72	TP1	1		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
73	U1	1		SM72295MAXNOPB	Texas Instruments	Photovoltaic Full Bridge Driver, DW0028A	DW0028A
74	U2	1		ATL431BQDB2R	Texas Instruments	2.5V Low Iq Adjustable Precision Shunt Regulator, DBZ0003A	DBZ0003A
75	U3	1		LM5018MRXNOPB	Texas Instruments	100V, 300mA Constant On-Time Synchronous Buck Regulator, DDA0008B	DDA0008B
76	U4	1		LM317LIPK	Texas Instruments	3-Terminal Adjustable Regulator, PK0003A	PK0003A
77	U5	1		SN74LVC1G175DCKR	Texas Instruments	SINGLE D-TYPE FLIP-FLOP WITH ASYNCHRONOUS CLEAR, DCK0006A	DCK0006A
78	U6	1		LM2901VOD	Texas Instruments	Quad Comparator, D0014A	D0014A
79	U7	1		LMT89DCKR	Texas Instruments	2.4V, 10uA, SC70, DSBGA Temperature Sensor, DCK0005A	DCK0005A
80	U8	1		TL431QDB2T	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 125 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Bi)	DBZ0003A
81	C24, C25	0	0.01uF	885012205031	Würth Elektronik	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0402	0402
82	C5	0	180 V	DM1M185S1-F	Diodes Inc.	Diode, Schottky, 180 V, 0.2 A, SOT-26	SOT-26
83	R16	0		CRCW040200Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
84	R23	0	24k	CRCW040224K0JNEA	Vishay-Dale	RES, 24 k, 5%, 0.063 W, 0402	0402
85	R24	0	33.2k	CRCW040233K2FKED	Vishay-Dale	RES, 33.2 k, 1%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2016, Texas Instruments Incorporated