

- 1

2

3

4

5

6
- 1) USB Differential Pairs - 90 Ohm


(A) XDS_D_P and XDS_D_N

(B) USB_D_P (GPIO41) and USB_D_N (GPIO23)
- 2) ADC PGA Differential pair Impedance Matching - 90 Ohm

(A) HSEC_PGAx_IN_P pins should match with HSEC_PGAx_IN_N, where x is between 1-3

(B) MCU_PGAx_IN_P pins should match with MCU_PGAx_IN_N, where x is between 1-3





Revision History				
Rev	ECN #	Approved Date	Approved by	Notes
E1	N/A	Sept 13, 2023	PL	Initial Draft
A	N/A	Jan 29, 2024	PL	Added Test Point for 5V0 and 3V3 Dampening resistor tuned per characterization Switched U1 from PBK to PDT package Minor changes to silkscreen and GND pour Adjustments to analog signal routing



Power to the MCU is either supported by the USB-C on the left or through the HSEC

Orderable: TMDSCNCD28P55X	Designed for: Public Release	Mod. Date: 1/31/2024
TID #: N/A	Project Title: F28P55x controlCARD	
Number: MCU132	Rev: A	Sheet Title:
SVN Rev: Version control disabled	Assembly Variant: 001	Sheet: 1 of 10
Drawn By: Peter Luong	File: MCU132A_CoverSheet.SchDoc	Size: B
Engineer: Peter Luong	Contact: http://www.ti.com/support	

Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.



A

B

C

D


A

B


C

D


JTAG and Reset



20 MHz External Crystal



Boot Mode Switch




Boot Mode Selection Chart


(S2: UP is '1', DOWN is '0')




Mode #	GPIO24	GPIO32	Boot Mode
00	0	0	Boot from Parallel GPIO
01	0	1	Boot from SCI / Wait Mode
02	1	0	Boot from CAN (MCAN-NONFD)
03	1	1	Boot from Flash (USB)

System Supervisory Circuitry




LEDs





The F28P55x controlCARD uses the internal VREG to generate the 1.2V voltage rail for VDD.


For custom boards using external VREG mode, recommend to use dual-output DC-DC (e.g., TPS62441) to generate both 3.3V and 1.2V supplies.




Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Orderable: TMDSCNCD28P55X	Designed for: Public Release	Mod. Date: 1/24/2024
TID #: N/A	Project Title: F28P55x controlCARD	
Number: MCU132	Rev: A	Sheet Title:
SVN Rev: Version control disabled	Assembly Variant: 001	Sheet: 5 of 10
Drawn By: Peter Luong	File: MCU132A_ADC.SchDoc	Size: B
Engineer: Peter Luong	Contact: http://www.ti.com/support	

USB Type-C Connector - Communication Peripheral to MCU



USB Type-C CC Controller and Power Switch






Switch Truth Table

MCU_GPIO70 STATUS	DESCRIPTION	USB_MODE
1 (HIGH)	UB_CC1 & USB_CC2 are pulled up	Host mode (DFP)
0 (LOW)	UB_CC1 & USB_CC2 are strongly pulled down	Device mode (UFP)


LED D8 will turn on to indicate that the C2000 device is in Host Mode (DFP).


NOTE: USB VBUS_5V0, PFLT & EPEN do not have a specific mux position in this device.

In this controlCARD, a standard GPIO is used to detect changes to these signals.



Switch Truth Table		
HSEC_5V0 > 4V	ISO_Pout_5V0 > HSEC_5V0	POWER_SWITCH_OUT
Yes	X	HSEC_5V0
No	No	HSEC_5V0
No	Yes	ISO_Pout_5V0





Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Orderable: TMDSCNCD28P55X	Designed for: Public Release	Mod. Date: 10/9/2023
TID #: N/A	Project Title: F28P55x controlCARD	
Number: MCU132	Rev: A	Sheet Title:
SVN Rev: Version control disabled	Assembly Variant: 001	Sheet: 8 of 10
Drawn By: Peter Luong	File: MCU132A_XDS110_MCU.SchDoc	Size: B
Engineer: Peter Luong	Contact: http://www.ti.com/support	

A

B

C

D


A

B

C


D

NOTE: Because the JTAG signals are isolated, cJTAG is not supported on this controlCARD.



S4 - JTAG Emulation & UART Switch

POS 1 ON: Use XDS110 emulator that is on the cCARD
POS 1 OFF: Boot from FLASH/peripheral (see boot mode switch) OR use emulator on baseboard
POS 2 ON: GPIOs 28 & 29 will be connected to the USB-to-UART adapter on the XDS110 emulator
POS 2 OFF: GPIOs 28 & 29 are disconnected from the USB-to-UART adapter on the XDS110 emulator and connected to the HSEC connector pins





PCB Number: MCU132
PCB Rev: A

PCB
LOGO
Texas Instruments



PCB
LOGO
FCC disclaimer

PCB
LOGO
WEEE logo

LBL1
PCB Label
THT-14-423-10
Size: 0.65" x 0.20 "

ZZ1
Label Assembly Note
This Assembly Note is for PCB labels only

ZZ2
Assembly Note
These assemblies are ESD sensitive, ESD precautions shall be observed.

ZZ3
Assembly Note
These assemblies must be clean and free from flux and all contaminants. Use of no clean flux is not acceptable.

ZZ4
Assembly Note
These assemblies must comply with workmanship standards IPC-A-610 Class 2, unless otherwise specified.

ZZ5
Assembly Note
Clip off KEY pin 9 of J1 connector header

Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Orderable: TMDSCNCD28P55X		Designed for: Public Release	Mod. Date: 10/10/2023
TID #: N/A		Project Title: F28P55x controlCARD	
Number: MCU132	Rev: A	Sheet Title:	
SVN Rev: Version control disabled		Assembly Variant: 001	Sheet: 10 of 10
Drawn By: Peter Luong		File: MCU132A_Hardware.SchDoc	Size: B
Engineer: Peter Luong		Contact: http://www.ti.com/support	