

PMP30290 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C8, C11, C23	4	1000pF	1812GC102KA1	AVX	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1812	1812
C2, C3, C9, C10, C16	5	1000pF	C1608X7R2A102K080AA	TDK	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0603	0603
C4, C5, C6, C7	4	0.01uF	C0603C103K1RACTU	Kemet	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X7R, 0603	0603
C12, C13	2	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
C14, C24	2	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	0805
C15	1	22uF	EMVH101ADA220MJA0G	Chemi-Con	CAP, AL, 22 µF, 100 V, +/- 20%, 0.55 ohm, SMD	JA0
C17, C18, C19	3	100uF	C1210C107M8PACTU	Wurth Elektronik	CAP, CERM, 100 µF, 10 V, +/- 20%, X5R, 1210	1210
C20, C26, C29	3	1uF	885012206052	Wurth Elektronik	CAP, CERM, 1 µF, 16 V, +/- 10%, X7R, 0603	0603
C21, C31	2	0.1uF	885012206046	Wurth Elektronik	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0603	0603
C22	1	22uF	12103D226MAT2A	AVX	CAP, CERM, 22 µF, 25 V, +/- 20%, X5R, 1210	1210
C25	1	470pF	GRM1885C1H471JA01D	MuRata	CAP, CERM, 470 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C27	1	0.47uF	GRM188R71C474KA88D	MuRata	CAP, CERM, 0.47 µF, 16 V, +/- 10%, X7R, 0603	0603
C28	1	0.068uF	GRM188R71H683KA93D	MuRata	CAP, CERM, 0.068 µF, 50 V, +/- 10%, X7R, 0603	0603
C30	1	220pF	GRM1885C1H221JA01D	MuRata	CAP, CERM, 220 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
D1	1	100V	B1100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 1 A, SMA	SMA
D2, D3, D4, D5, D7, D8, D9, D10	8	MBR1H100S	MBR1H100SFT3G	ON Semiconductor	Diode, Schottky, 100 V, 1 A, SOD-123FL	SOD-123FL
D6	1	58V	SMAJ58A-13-F	Diodes Inc.	Diode, TVS, Uni, 58 V, SMA	SMA
D11, D13	2	15V	MMSZ5245BS-7-F	Diodes Inc.	Diode, Zener, 15 V, 200 mW, SOD-323	SOD-323
D12, D17	2	MBR0530T1G	MBR0530T1G	ON Semiconductor	Diode, Schottky, 30 V, 0.5 A, SOD-123	SOD-123
D14	1	DNP	PDS360-13	Diodes Inc.	Diode, Schottky, 60 V, 3 A, PowerDI5	PowerDI5
D15	1	MURA120T3G	MURA120T3G	ON Semiconductor	Diode, Ultrafast, 200 V, 1 A, SMA	SMA
D16	1	MMSD4148T1G	MMSD4148T1G	ON Semiconductor	Diode, Switching, 100 V, 0.2 A, SOD-123	SOD-123
D18	1	BAT54S-7-F	BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
J1, J2	2		1-406541-1	AMP	RJ-45, Right Angle, No LED, tab up	16.26x14.54x15.75
J3, J4	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
L1, L2, L3, L4	4	220 ohm	MPZ1608S221A	TDK	Ferrite Bead, 220 ohm @ 100 MHz, 2.2 A, 0603	0603
L5	1	10uH	LPS4018-103MRB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 10 µH, 1.25 A, 0.18 ohm, SMD	LPS4018
Q1	1	CSD17578Q3A	CSD17578Q3A	Texas Instruments	MOSFET, N-CH, 30 V, 14 A, DNH0008A (VSONP-8)	DNH0008A
Q2	1	FDC86244	FDC86244	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 2.3 A, SuperSOT-6	SuperSOT-6
R1, R2, R3, R4, R5, R6	6	75.0	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0, 1%, 0.1 W, 0603	0603
R7, R10, R11	3	10	CRCW080510R0JNEA	Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R8	1	39k	CRCW080539K0JNEA	Vishay-Dale	RES, 39 k, 5%, 0.125 W, 0805	0805
R9	1	10.0	CRCW201010R0FKEF	Vishay-Dale	RES, 10.0, 1%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R12	1	49.9	RC0603FR-0749R9L	Yageo America	RES, 49.9, 1%, 0.1 W, 0603	0603
R13, R19	2	10.0k	RC0603FR-0710KL	Yageo America	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R14	1	24.3k	RC0603FR-0724K3L	Yageo America	RES, 24.3 k, 1%, 0.1 W, 0603	0603
R15	1	681	RC0603FR-07681RL	Yageo America	RES, 681, 1%, 0.1 W, 0603	0603
R16	1	24.9k	RC0603FR-0724K9L	Yageo America	RES, 24.9 k, 1%, 0.1 W, 0603	0603
R17	1	2.21k	RC0603FR-072K21L	Yageo America	RES, 2.21 k, 1%, 0.1 W, 0603	0603
R18	1	0.15	ERJ-8BSFR15V	Panasonic	RES, 0.15, 1%, 0.5 W, 1206	1206
R20	1	100k	RC0603FR-07100KL	Yageo America	RES, 100 k, 1%, 0.1 W, 0603	0603
R21	1	90.9	RC0603FR-0790R9L	Yageo America	RES, 90.9, 1%, 0.1 W, 0603	0603
R22	1	22.1k	RC0603FR-0722K1L	Yageo America	RES, 22.1 k, 1%, 0.1 W, 0603	0603
R23	1	332	RC0603FR-07332RL	Yageo America	RES, 332, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R24	1	9.09k	RC0603FR-079K09L	Yageo America	RES, 9.09 k, 1%, 0.1 W, 0603	0603
R25	1	34.0k	RC0603FR-0734KL	Yageo America	RES, 34.0 k, 1%, 0.1 W, 0603	0603
R26	1	3.65k	RC0603FR-073K65L	Yageo America	RES, 3.65 k, 1%, 0.1 W, 0603	0603
R27	1	1.50k	RC0603FR-071K5L	Yageo America	RES, 1.50 k, 1%, 0.1 W, 0603	0603
T1	1	350uH	H2019FNLT	Pulse Engineering	Transformer, 350uH, SMT	358x236x500mil
T2	1	198uH	NA6223-AL	Coilcraft	Transformer, Flyback, 198 uH	699x500x530mil
TP1	1		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
TP2	1		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP3	1		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
U1	1	TPS23752PWP	TPS23752PWP	Texas Instruments	IEEE 802.3at PoE Interface and Green-mode DC/DC Controller, PWP0020D (TSSOP-20)	PWP0020D
U2	1	TCMT1107	TCMT1107	Vishay-Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	SOP-4
U3	1	TL431AIDBZRG4	TL431AIDBZRG4	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated