



CSD13306W 12 V N Channel NexFET™ Power MOSFET

1 Features

- Ultra Low on Resistance
- Low Q_g and Q_{gd}
- Small Footprint 1×1.5 mm
- Low Profile 0.62 mm Height
- Pb Free
- RoHS Compliant
- Halogen Free



2 Applications

- Battery Management
- Load Switch
- Battery Protection


3 Description

This 8.8 m Ω , 12 V, N-Channel device is designed to deliver the lowest on resistance and gate charge in a small 1×1.5 mm outline with excellent thermal characteristics and an ultra low profile.

Top View

 $R_{DS(on)}$ vs V_{GS} 

Gate Charge



Product Summary

$T_A = 25^\circ\text{C}$		TYPICAL VALUE		UNIT
V_{DS}	Drain-to-Source Voltage	12		V
Q_g	Gate Charge Total (4.5 V)	8.6		nC
Q_{gd}	Gate Charge Gate-to-Drain	3.0		nC
$R_{DS(on)}$	Drain-to-Source On-Resistance	$V_{GS} = 2.5$ V	12.9	m Ω
		$V_{GS} = 4.5$ V	8.8	m Ω
$V_{GS(th)}$	Voltage Threshold	1.0		V

Ordering Information⁽¹⁾

Device	Qty	Media	Package	Ship
CSD13306W	3000	7-Inch Reel	1.0 mm \times 1.5 mm Wafer Level Package	Tape and Reel
CSD13306WT	250	7-Inch Reel		

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Absolute Maximum Ratings

$T_A = 25^\circ\text{C}$		VALUE	UNIT
V_{DS}	Drain-to-Source Voltage	12	V
V_{GS}	Gate-to-Source Voltage	± 10	V
I_D	Continuous Drain Current ⁽¹⁾	3.5	A
I_{DM}	Pulsed Drain Current ⁽²⁾	44	A
P_D	Power Dissipation ⁽³⁾	1.9	W
T_{stg}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range		

(1) Device Operating at a temperature of 105°C

(2) Min Cu Typ $R_{\theta JA} = 230^\circ\text{C/W}$, Pulse width ≤ 100 μs , duty cycle $\leq 1\%$

(3) Max Cu Typ $R_{\theta JA} = 65^\circ\text{C/W}$



Table of Contents

1 Features	1	6 Device and Documentation Support.....	7
2 Applications	1	6.1 Trademarks	7
3 Description	1	6.2 Electrostatic Discharge Caution.....	7
4 Revision History.....	2	6.3 Glossary	7
5 Specifications.....	3	7 Mechanical, Packaging, and Orderable Information	8
5.1 Electrical Characteristics.....	3	7.1 CSD13306W Package Dimensions	8
5.2 Thermal Information	3	7.2 Tape and Reel Information	9
5.3 Typical MOSFET Characteristics.....	4		

4 Revision History

DATE	REVISION	NOTES
March 2015	*	Initial release.

5 Specifications

5.1 Electrical Characteristics

(T_A = 25°C unless otherwise stated)



PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
STATIC CHARACTERISTICS						
BV _{DSS}	Drain-to-Source Voltage	V _{GS} = 0 V, I _D = 250 μA	12			V
I _{DSS}	Drain-to-Source Leakage Current	V _{GS} = 0 V, V _{DS} = 9.6 V			1	μA
I _{GSS}	Gate-to-Source Leakage Current	V _{DS} = 0 V, V _{GS} = 10 V			100	nA
V _{GS(th)}	Gate-to-Source Threshold Voltage	V _{DS} = V _{GS} , I _D = 250 μA	0.7	1.0	1.3	V
R _{DS(on)}	Drain-to-Source On-Resistance	V _{GS} = 2.5 V, I _D = 1.5 A		12.9	15.5	mΩ
		V _{GS} = 4.5 V, I _D = 1.5 A		8.8	10.2	mΩ
g _{fs}	Transconductance	V _{DS} = 1.2 V, I _D =1.5 A		15		S
DYNAMIC CHARACTERISTICS						
C _{ISS}	Input Capacitance	V _{GS} = 0 V, V _{DS} = 6 V, f = 1 MHz		1050	1370	pF
C _{OSS}	Output Capacitance			324	421	pF
C _{RSS}	Reverse Transfer Capacitance			226	294	pF
R _g		V _{DS} = 6 V, I _D = 1.5 A		4.2	8.4	Ω
Q _g	Gate Charge Total (4.5V)			8.6	11.2	nC
Q _{gd}	Gate Charge Gate-to-Drain			3.0		nC
Q _{gs}	Gate Charge Gate-to-Source			1.1		nC
Q _{g(th)}	Gate Charge at V _{th}			1.2		nC
Q _{OSS}	Output Charge	V _{DS} = 6 V, V _{GS} = 0 V		3.3		nC
t _{d(on)}	Turn On Delay Time	V _{DS} = 6 V, V _{GS} = 4.5 V, I _D = 1.5 A R _G = 4 Ω		7		ns
t _r	Rise Time			11		ns
t _{d(off)}	Turn Off Delay Time			20		ns
t _f	Fall Time			8		ns
DIODE CHARACTERISTICS						
V _{SD}	Diode Forward Voltage	I _S = 1.5 A, V _{GS} = 0 V		0.7	1.0	V
Q _{rr}	Reverse Recovery Charge	V _{DS} = 6 V, I _F = 1.5 A, di/dt = 200 A/μs		14.8		nC
t _{rr}	Reverse Recovery Time			23		ns

5.2 Thermal Information

T_A = 25°C unless otherwise stated


THERMAL METRIC		MIN	TYP	MAX	UNIT
R _{θJA}	Junction-to-Ambient Thermal Resistance ⁽¹⁾		230		°C/W
	Junction-to-Ambient Thermal Resistance ⁽²⁾		65		

(1) Device mounted on FR4 material with minimum Cu mounting area

(2) Device mounted on FR4 material with 1 inch² (6.45 cm²), 2 oz. (0.071 mm thick) Cu.

Typ R_{θJA} = 65°C/W
when mounted on
1 inch² of 2 oz. Cu.

Typ R_{θJA} = 230°C/W
when mounted on
minimum pad area of
2 oz. Cu.

5.3 Typical MOSFET Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)



Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 2. Saturation Characteristics




Figure 3. Transfer Characteristics




Figure 4. Gate Charge




Figure 5. Capacitance




Figure 6. Threshold Voltage vs Temperature




Figure 7. On-State Resistance vs Gate-to-Source Voltage

Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 8. Normalized On-State Resistance vs Temperature




Figure 9. Typical Diode Forward Voltage




Figure 10. Maximum Safe Operating Area




Figure 11. Maximum Drain Current vs Temperature

6 Device and Documentation Support

6.1 Trademarks

NexFET is a trademark of Texas Instruments.
All other trademarks are the property of their respective owners.

6.2 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

6.3 Glossary


[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

7.1 CSD13306W Package Dimensions




NOTE: All dimensions are in mm (unless otherwise specified)

Pinout

POSITION	DESIGNATION
C2, B2	Source
A2	Gate
A1, B1, C1	Drain


Land Pattern Recommendation



M0158-01

NOTE: All dimensions are in mm (unless otherwise specified)

7.2 Tape and Reel Information



M0159-01

NOTE: All dimensions are in mm (unless otherwise specified)

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
CSD13306W	Active	Production	DSBGA (YZC) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	13306
CSD13306W.B	Active	Production	DSBGA (YZC) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	13306
CSD13306WT	Active	Production	DSBGA (YZC) 6	250 SMALL T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	13306
CSD13306WT.B	Active	Production	DSBGA (YZC) 6	250 SMALL T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	13306

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025