

Don't Let Bad Reference Signals Destroy the Phase Noise in Your PLL/synthesizer



Brian Wang

“You are what you eat” is a commonly heard saying that recommends the careful selection of food, given its ability to directly affect our health and well-being.

Although not an exact comparison, the concept applies if you think of your input reference signal as the food, ingested by the phase-locked loop (PLL)/synthesizer, which affects the well-being of the PLL/synthesizer, as evident in the output phase noise, shown in [Figure 1](#). In this post, I'll provide some practical examples to show you what a good input reference looks like, what damage a bad input reference can do and how to analyze a given input reference.



Figure 1. Input Reference Noise is also multiplied by the PLL

To back up a little, a PLL, when paired with a voltage-controlled oscillator (VCO), becomes a control-loop system that can lock on to a low-frequency signal (10MHz from a stable crystal oscillator) and multiply it to a much higher frequency (the [LMX2592](#) can multiply up all the way to 9.8GHz).

Example 1

[Figure 2](#) shows a single sideband phase-noise plot. The orange line is the 100MHz input reference signal, which uses a very low phase-noise crystal as the input reference. The [LMX2582](#) synthesizer in this example multiplies the 100MHz up to 5,160.96MHz. In doing so, the input reference noise scales up as well by a factor of $[20 \times \text{LOG}(5,160.96/100) = 34.25\text{dB}]$. The brown line shows the scaled-up result (adjusted mathematically). The red line is showing the output of the LMX2582 at 5160.96MHz.




Figure 2. Low phase noise 100MHz input reference and 5160.96MHz LMX2582 output

Using an input reference like the one in [Figure 2](#) shows the performance of the synthesizer, since the input reference phase noise is low enough. Note that the key region is under the loop bandwidth (~300kHz offset), since beyond this offset frequency the input reference noise is also filtered and will fall in the same manner as the red line (not shown in this example).

Also notice the huge spike at about 120Hz from the input reference. This directly impacts the output phase noise. You can already see the danger here. If noise is coupled somewhere into the input reference source at the lower offsets, it can damage the synthesizer phase noise.

Example 2

[Figure 3](#) considers another input reference, this time a 122.88MHz crystal oscillator. The output frequency is again 5,160.96MHz. This time, the input reference noise is scaled by $[20 \times \text{LOG}(5,160.96/122.88) = 32.46\text{dB}]$. Look at the phase noise portion 2kHz offset and below, and compare it to the output phase noise of [Figure 2](#); you can see that this higher input reference noise contribution directly raises the output phase noise from the synthesizer. To achieve optimal performance from the LMX2582, you also have to feed it a good-enough input reference. And knowing how the noise scales and contributes helps in the selection of an input reference signal by its fundamental phase-noise level.




Figure 3. A 122.88MHz input reference and 5160.96MHz LMX2582 output

Example 3

Figure 4 explores a further scenario. This example also uses a 122.88MHz crystal oscillator, but this time the impact in phase noise occurred from vibration. Those clumps of spikes in Figure 4 appear when you tap your finger close to the oscillator. This is a known behavior in certain crystal-based oscillators. It does damage in the same way that bad phase noise does, but you may not know about it if you just leave it there on the bench and measure. This suggests that in picking an input reference, it is important to not only know the fundamental phase noise of the device, but to also know its response to vibration, aging, temperature variation, resilience to power-supply noise and many other influences. Having this in mind can help in part selection as well as debugging an overall signal chain.




Figure 4. A noisy 122.88MHz input reference and 5160.96MHz LMX2582 output

To see how this works in an example design, check out our [9.8 GHz RF High Performance Synthesizer Operating From a Buck Converter Reference Design](#).

Reference Table

As a guideline, it is helpful to see the impact of calculated scaled input reference noise. In [Table 1](#), you can see that (as expected) if the scaled input reference phase noise is the same as the PLL phase noise (0dB in [Table 1](#)), you get a 3dB addition because you are doubling the amount of noise. Likewise, if you go further down in the phase-noise level of the input reference, you get less and less of a significant contribution in phase noise.

Table 1. Phase-noise addition from the scaled input reference phase noise

Scaled input reference phase-noise level below PLL phase noise (dB)	Phase-noise addition (dB)
0	3.01
-1	2.54
-2	2.12
-3	1.76
-4	1.46
-5	1.19
-6	0.97
-7	0.79
-8	0.64
-9	0.51
-10	0.41

With these examples, I hope I've shown how a good input reference is vital to getting optimal performance from the synthesizer. A bad input reference is not only one that has too high a phase-noise level, but one that is also more susceptible to external influences (vibration, aging, temperature, power supply). With this information, you should have a better understanding and additional ideas when designing the input reference for your synthesizer. For additional information or if you have questions, visit the [TI E2E™ Community High Performance RF Modulators, PLL and VCO forum](#).

Additional Resources

- Check out TI's entire [PLL/synthesizer portfolio](#).
- Read the technical article, "[A survival guide to scaling your PLL loop filter design.](#)"
- Start designing quickly with the [LMX2582EVM high performance, wideband frequency PLLatinum™ RF synthesizer with integrated VCO evaluation module](#).

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated