

TIDA-010940 REV E2 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB	1		TIDA-010940	Any	Printed Circuit Board	
2	C1, C3	2	1uF	GMC04X7R105K10NT	Cal-Chip Electronics	1uF ±10% 10V Ceramic Capacitor X7R 0402 (1005 Metric)	402
3	C2, C10	2	0.1uF	GRM155R71E104KE14D	MuRata	CAP. CERAM, 0.1 uF, 25 V, +/- 10%, X7R, 0402	402
4	C4, C5	2	22nF	GRM1555C1H22JA01D	MuRata	CAP. CERAM, 22 nF, 50 V, +/- 5%, COG/NP0, 0402	402
5	C6, C67	2	15nF	GRM1555C1H15JA01D	MuRata	CAP. CERAM, 15 nF, 50 V, +/- 5%, COG/NP0, 0402	402
6	C7, C8	2	100pF	0402YC101KAT2A	AVX	CAP. CERAM, 100 pF, 16 V, +/- 10%, X7R, 0402	402
7	C29, C30, C34, C38, C54	5	0.033uF	GRM188R71C333KA01D	MuRata	CAP. CERAM, 0.033 uF, 16 V, +/- 10%, X7R, 0603	603
8	C31	1	0.1uF	06035C104KAT2A	AVX	CAP. CERAM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	603
9	C53	1	4700pF	C0603C47J1GAC7867	Kemet	CAP. CERAM, 4700 pF, 100 V, +/- 5%, COG/NP0, 0603	603
10	C57	1	0.22uF	CL35B223K63MNC	Samsung Electro-Mechanics	CAP. CERAM, 0.22 uF, 16 V, +/- 10%, X7R, 0402	402
11	C62	1	0.47uF	GRM155R61C474KE01	MuRata	CAP. CERAM, 0.47 uF, 16 V, +/- 10%, X5R, 0402	402
12	C63	1	10uF	GRM155R61A106ME11D	MuRata	CAP. CERAM, 10 uF, 10 V, +/- 20%, X5R, 0402	402
13	C64	1	1uF	GRM155R61E105KE11D	MuRata	CAP. CERAM, 1 uF, 25 V, +/- 10%, X5R, 0402	402
14	C66	1	1000pF	GRM155R61A102KA01D	MuRata	CAP. CERAM, 1000 pF, 10 V, +/- 10%, X5R, 0402	402
15	C80, C81	2	0.1uF	C0603X104K3RACTU	Kemet	CAP. CERAM, 0.1 uF, 25 V, +/- 10%, X7R, 0603	603
16	C86	1	0.1uF	CGA3E28R1E104K080AA	TDK	CAP. CERAM, 0.1 uF, 25 V, +/- 10%, X8R, AEC-Q200 Grade 0, 0603	603
17	D1, D2	2	Bright Green	150808V575000	Würth Elektronik	LED, Bright Green, SMD	LED_0805
18	H1, H2	2		3.5 MM HOLE	Any	3.5 mm PCB Hole	3.5mm PCB Hole
19	J1	1		FTSH-105-01-L-DV-K	Samtec	Header(Shrouded), 1.27mm, 5x2, Gold, SMT	Header(Shrouded), 1.27mm, 5x2, SMT
20	J2	1		6.91217E+11	Würth Electronics	2 Position Wire to Board Terminal Block Horizontal with Board 0.400" (10.16mm) Through Hole	TERM_BLK_2
21	J3, J12	2		61000218321	Würth Elektronik	Header, 2.54mm, 2x1, Gold, SMT	Header, 2.54mm, 2x1, SMT
22	J4	1		M50-3630242	Harwin	Header, 1.27mm, 2x1, Gold with Tin tail, SMT	Header, 1.27mm, 2x1, SMT
23	J14	1		282841-2	TE Connectivity	Terminal Block, 2x1, 5.08mm, TH	10.16x15.2x9mm
24	J15	1		O5TVND4A150	On-Shore Technology	Terminal Block, 2.54mm, 4x1, Brass, TH	Terminal Block, 2.54mm, 4-pole, TH
25	LBL1	1		TH1-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch
26	MP1, MP2, MP3, MP4	4		SJ5076	3M	Bumper Cylindrical, Flat Top 0.315" Dia (8.00mm) Polyurethane Black	BUMPER_CYLIN
27	Q1	1	30 V	BC848CLT1G	ON Semiconductor	Transistor, NPN, 30 V, 0.1 A, SOT-23	SOT-23
28	R1	1	220k	RC0402FR-07220KL	Yageo America	RES, 220 k, 1%, 0.0625 W, 0402	402
29	R3	1		B72214S2461K101	TDK	Var MOV 460VAC/615VDC 5000A 750V Thru-Hole Radial Bulk	RADIAL
30	R4, R6, R7, R74, R81	5	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603
31	R5, R9	2	10.0k	ERJ-2RFK1002X	Panasonic	RES, 10.0 k, 1%, 0.1 W, 0402	402
32	R10, R11	2	2.20k	RC0402FR-072K2L	Yageo America	RES, 2.20 k, 1%, 0.063 W, 0402	402
33	R12, R13	2	4.7Meg	CRCW0402470JUNED	Vishay-Dale	RES, 4.7 M, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	402
34	R14	1	1.0k	CRCW04021K00JUNED	Vishay-Dale	RES, 1.0 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	402
35	R16	1	8.06k	ERA-2ARB061X	Panasonic	8.06 kohms ±0.1% 0.063W, 1/16W Chip Resistor 0402 (1005 Metric) Automotive AEC-Q200 Thin Film	402
36	R17	1	820	RC0402FR-07820RL	Yageo America	RES, 820, 1%, 0.063 W, 0402	402
37	R18, R86, R87	3	1.00k	RC0402FR-071KL	Yageo America	RES, 1.00 k, 1%, 0.0625 W, 0402	402
38	R19	1	220	ERJ-2RFK2200X	Panasonic	RES, 220, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	402
39	R20	1	820	CRCW0402820RLJUNED	Vishay-Dale	RES, 820, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	402
40	R21, R22, R23, R28, R29, R30	6	330k	TNPV1206330KBEEEN	Vishay Draloric	RES, 330 k, 0.1%, 1 W, 1206	1206
41	R24	1	470	AC0500004700JAC00	Vishay-Bccomponents	RES, 470, 5%, 5 W, AEC-Q200 Grade 0, Dia 7.5mm	Dia 7.5mm
42	R26, R27	2	0	5113	Keystone Electronics	0 Ohms Jumper Chip Resistor 0402 (1005 Metric) Metal Element	402
43	R32, R33, R34, R35	4	1.00k	RC0603FR-071KL	Yageo	RES, 1.00 k, 1%, 0.1 W, 0603	603
44	R36	1	120	RT0603DRE07120RL	Yageo America	RES, 120, 0.5%, 0.1 W, 0603	603
45	R88	1	47k	CRCW040247K0JUNED	Vishay-Dale	RES, 47 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	402
46	SW1, SW2, SW3	3		TL1105DF250Q	E-Switch	Switch Tactile N.O. SPST Round Button PC Pins 0.05A 50VDC 2.45N Thru-Hole	PTH_SW_6MM0_6M MO
47	U1	1		DRV5032ZEDBZR	Texas Instruments	Ultra-Low Power 1.65V to 5.5V Hall Effect Switch Sensor, DBZ0003A (SOT-23-3)	DBZ0003A
48	U2	1		MSPM0L22281PN	Texas Instruments	MSPM0L22281PN	LQFP80
49	U3	1		THV0140DD	Texas Instruments	500 kbps RS-485 Transceivers With ±8-kV IEC ESD Protection	SOIC8
50	U4	1		W25080JVSNIQ	Winbond	3V 8M-BIT SERIAL FLASH MEMORY WITH DUAL/QUAD SPI, SOIC-8	SOIC-8
51	U6	1		ADS131M03IPWR	Texas Instruments	3-Channel, 24-Bit, Simultaneously-Sampling, Delta-Sigma ADC, PW0020A (TSOP-20)	PW0020A
52	U7	1		TPD2E007DCKR	Texas Instruments	ESD Protection Array for AC Signal Data Interface, 2 Channels, -40 to +85 degC, 3-pin SC70 (DCK), Green (RoHS & no Sb/Br)	DCK0003A
53	U11	1		ISO6731DWR	Texas Instruments		SOIC16
54	Y1	1		FA-238 16.3840MB-K	Epson	Crystal, 16.384 MHz, 50 ppm, 10 pF, SMD	3.2x2.5mm
55	Y2	1		X1A0001410014	Epson	Crystal, 32.768 KHz, 12.5 pF, SMD	SMD, 2-Leads, Body 3.2x1.5mm
56	C9, C68	0	0.47uF	GRM155R61C474KE01	MuRata	CAP. CERAM, 0.47 uF, 16 V, +/- 10%, X5R, 0402	402
57	C84, C85	0	10pF	CGA3E2C0G1H100D080AA	TDK	CAP. CERAM, 10 pF, 50 V, +/- 5%, COG/NP0, AEC-Q200 Grade 1, 0603	603
58	D3, D5, D13	0	30V	BATS4HT1G	ON Semiconductor	Diode, Schottky, 30 V, 0.2 A, SOD-323	SOD-323
59	D4, D9	0		VSMY2853SLD01	Vishay	IR Emitter High Speed 850nm 50mW/sr 100mA 1.9V 2-Pin SMD T/R	SMT_LED_2MM30_2 MM55
60	D6, D7, D8, D10, D12, D14, D15, D16	0	70V	BAV199-TP	Micro Commercial Componen	Diode, Switching, 70 V, 0.215 A, SOT-23	SOT-23
61	FID1, FID2, FID3	0	N/A	N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
62	J5, J6	0		61300111121	Würth Elektronik	Header, 2.54 mm, 1x1, Gold, TH	Header, 2.54 mm, 1x1, TH
63	J7, J8	0		M22-2511205	Harwin	Header, 2mm, 12x1, Gold, TH	Header, 2mm, 12x1, TH
64	J10	0		MTMM-105-15-L-D-150	Samtec	Header, 2mm, 5x2, Gold, TH	Header, 2mm, 5x2, TH
65	J11	0		TMM-102-01-F-S	Samtec	Header, 2mm, 2x1, Gold, TH	Header, 2mm, 2x1, TH
66	J20	0		PTT-103-01-L-S	Samtec	Header, 2mm, 3x1, Gold, TH	Header, 2mm, 3x1, TH
67	R2	0	100k	RG1005P-104-B-T5	Susumu Co Ltd	RES, 100 k, 0.1%, 0.063 W, 0402	402
68	R15	0	0uΩ	CR0402-10W-000T	Venkel	0 Ohms Jumper 0.1W, 1/10W Chip Resistor 0402 (1005 Metric) - Thick Film	402
69	R25	0	0	5113	Keystone Electronics	0 Ohms Jumper Chip Resistor 0402 (1005 Metric) Metal Element	402
70	R31, R36	0	0	PMR18E2P-J000	Rohm Semiconductor	0 Ohms Jumper 1W Chip Resistor 1206 (3216 Metric) Automotive AEC-Q200, Current Sense Thick Film	1206
71	R37, R38	0	0	RC0805FR-070RL	Yageo	RES SMD 0 OHM JUMPER 1/8W 0805	805
72	R46, R54	0	100k	CRCW0603100KJNEA	Vishay-Dale	RES, 100 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603
73	R52, R55	0	4.7k	CRCW060347K0JNEA	Vishay-Dale	RES, 4.7 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	603
74	TP1	0		3154-00-15-00-00-03-0	Mill-Max	PCB Pin, 0.46 Dia, Gold, TH	PCB Pin, 0.46 Dia, TH

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated