

TIDA-010276 REV E1 Bill of Materials

| Item # | Designator | Quantity | Value | PartNumber | Manufacturer | Description | PackageReference |
|--------|---|----------|--------|---------------------|---------------------------|---|------------------------------|
| 1 | PCB1 | | | TIDA-010276 | Any | Printed Circuit Board | |
| 2 | C1, C2 | 2 | 1000uF | ECA-2AM102 | Panasonic | CAP. AL. 1000 uF, 100 V, +/- 20%, TH | D18xL35.5mm |
| 3 | C3, C4, C5, C6, C7, C8, C9, C10, C11, C12, C13, C14, C15, C16, C17, C18, C19, C20, C21, C22, C23, C24, C25, C26, C27, C28, C29, C30, C31, C32, C33, C34, C35, C36, C37, C38, C39, C40, C41, C42 | 40 | 10µF | C3225X7R2A106K250AC | TDK | 10 µF ±10% 100V Ceramic Capacitor X7R 1210 (3225 Metric) | 1210 |
| 4 | C43, C45, C49 | 3 | 4.7µF | C1608B5TC475K080AC | TDK | CAP. CERM. 4.7 uF, 16 V, +/- 10%, X6S, 0603 | 0603 |
| 5 | C44 | 1 | 1uF | GRM185R61C109KE44D | MuRata | CAP. CERM. 1 uF, 16 V, +/- 10%, X5R, 0603 | 0603 |
| 6 | C46, C48, C50 | 3 | 0.1uF | GRM155R62A104KE14D | MuRata | CAP. CERM. 0.1 uF, 100 V, +/- 10%, X5R, 0402 | 0402 |
| 7 | C47, C51, C52, C53, C54, C55, C56, C57, C58, C59, C60, C61, C62, C63, C64, C65 | 16 | 1uF | G2012X7S2A105K125AE | TDK | CAP. CERM. 1 µF, 100 V, +/- 10%, X7S, 0805 | 0805 |
| 8 | C66, C67, C68, C69, C70, C71, C72, C73, C74, C75, C76, C77, C78, C79, C80 | 15 | 0.22uF | HMK107C7224KAHTE | Taiyo Yuden | CAP. CERM. 0.22 µF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0603 | 0603 |
| 9 | C81, C82, C83 | 3 | 0.22uF | GRM155R71C224KA12D | MuRata | CAP. CERM. 0.22 uF, 16 V, +/- 10%, X7R, 0402 | 0402 |
| 10 | C84, C85, C86 | 3 | 0.1uF | GRM218R7A2104KAC4L | MuRata | CAP. CERM. 0.1 uF, 100 V, +/- 10%, X7R, 0805 | 0805 |
| 11 | C87, C89, C91 | 3 | 2.2uF | GRM188R71C222KE43 | MuRata | CAP. CERM. 2.2 uF, 16 V, +/- 10%, X7R, 0603 | 0603 |
| 12 | C88, C90, C92 | 3 | 0.1uF | GCM155R71H104KE02D | MuRata | CAP. CERM. 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402 | 0402 |
| 13 | C93, C94, C95, C96, C97, C98 | 6 | 10pF | GRM1555C1H100JA01D | MuRata | CAP. CERM. 10 pF, 50 V, +/- 5%, COG/NP0, 0402 | 0402 |
| 14 | C99, C100, C101, C102 | 4 | 1000pF | GRM1555C1H102FA01D | MuRata | CAP. CERM. 1000 pF, 50 V, +/- 1%, COG/NP0, 0402 | 0402 |
| 15 | C103, C108, C111, C116 | 4 | 10pF | GRM1885C2A100JA01D | MuRata | CAP. CERM. 10 pF, 100 V, +/- 5%, COG/NP0, 0603 | 0603 |
| 16 | C104, C105, C107, C112, C114, C117, C118, C119, C120 | 9 | 0.1uF | GRM188R72A104KA35D | MuRata | CAP. CERM. 0.1 uF, 100 V, +/- 10%, X7R, 0603 | 0603 |
| 17 | C106, C109, C110, C113, C115, C121 | 6 | 100pF | GRM1885C2A101JA01D | MuRata | CAP. CERM. 100 pF, 100 V, +/- 5%, COG/NP0, 0603 | 0603 |
| 18 | C122, C123, C124, C125, C126, C127, C128, C129, C130 | 9 | 2200pF | 8.85012E+11 | Wurth Elektronik | CAP. CERM. 2200 pF, 16 V, +/- 10%, X7R, 0603 | 0603 |
| 19 | D1 | 1 | Green | 150060GS75000 | Wurth Elektronik | LED, Green, SMD | LED_0603 |
| 20 | D2, D3, D4, D5 | 4 | 70V | 1PS79SB70, 115 | Nexperia | Diode, Schottky, 70 V, 0.07 A, SOD-523 | SOD-523 |
| 21 | D6 | 1 | Red | LTS1-C159KRK1-5A | Life-On | LED, Red, SMD | 1.8x0.8mm |
| 22 | J1 | 1 | | PE0203AAAN | Suins Connector Solutions | Header, 100mil, 2x1, Tin, TH | Header: 2 PIN 100mil, Tin |
| 23 | J2 | 1 | | 61300311121 | Wurth Elektronik | Header, 2.54 mm, 3x1, Gold, TH | Header: 2.54mm, 3x1, TH |
| 24 | J3, J4 | 2 | | SSW-110-23-F-D | Samtec | Connector, Receptacle, 100mil, 10x2, Gold plated, TH | 10x2 Receptacle |
| 25 | L1 | 1 | 22uH | 74437342220 | Wurth Elektronik | Inductor, Shielded Core, Powdered Iron, 22 uH, 1 A, 0.47 ohm, SMD | 4.4x5.1 8x4.05mm SMD |
| 26 | MP1, MP2, MP3, MP4, MP5 | 5 | | 746600430R | Wurth Electronics | Pin Screw Terminal, Power Tap M4 Surface Mount | SMT SCREW, TERM INAL, 7MM0 |
| 27 | MP6, MP7, MP8, MP9 | 4 | | 970130365 | Wurth Electronics | | SMPAER_M3 |
| 28 | R1, R2, R16, R17, R18, R19, R20, R21, R22, R23, R24, R37, R38, R39 | 14 | 0 | PMN03E-ZP-3000 | Rohm | RES, 0, 0%, 0.25 W, AEC-Q200 Grade 0, 0603 | 0603 |
| 29 | R3, R47 | 2 | 100k | CRCW0603100KJNEAC | Vishay-Dale | RES, 100 k, 5%, 0.1 W, 0603 | 0603 |
| 30 | R4, R92 | 2 | 1.0k | RC0603JR-071KL | Yageo | RES, 1.0 k, 5%, 0.1 W, 0603 | 0603 |
| 31 | R5 | 1 | 47k | RC0603JR-0747KL | Yageo | RES, 47 k, 5%, 0.1 W, 0603 | 0603 |
| 32 | R6 | 1 | 24.9k | RC0603JR-07249KL | Yageo | RES, 24.9 k, 1%, 0.1 W, 0603 | 0603 |
| 33 | R7, R8, R9, R13, R14, R15 | 6 | 3.01 | CRCW04023901FKED | Vishay-Dale | RES, 3.01, 1%, 0.063 W, AEC-Q200 Grade 0, 0402 | 0402 |
| 34 | R10, R11, R12 | 3 | 0 | RC0402JR-070RL | Yageo America | RES, 0, 5%, 0.063 W, 0402 | 0402 |
| 35 | R25, R26, R27, R28, R29, R30, R33 | 16 | 0.002 | CRF1206-FZ-R002ELF | Souris | RES, 0.002, 1%, 1 W, AEC-Q200 Grade 0, 1206 | 1206 |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2025, Texas Instruments Incorporated

DRAFT
TI Confidential – NDA Restrictions

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated