

Variant: 001
 Generated: 12/6/2021 12:00:39 PM
 TID #: N/A



TIDA-050050 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C10	2	2.2uF	GCM188R70J225KE22D	MuRata	CAP, CERM, 2.2 uF, 6.3 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
2	C2, C4, C11, C12, C14	5		GRM188Z71A106KA73D	Murata	Chip Multilayer Ceramic Capacitors for General Purpose	0603
3	C5, C13	2	1uF	EMK107B7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, 0603	0603
4	C6	1	10uF	TMK316B7106KL-TD	Taiyo Yuden	CAP, CERM, 10 uF, 25 V, +/- 10%, X7R, 1206_190	1206_190
5	C7	1	4.7uF	C2012X7R1E475K125AB	TDK	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X7R, 0805	0805
6	C8, C9, C26	3	0.1uF	C1005X7R1H104K050BB	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0402	0402
7	C15, C16	2	4.7uF	JMK107BB7475MA-T	Taiyo Yuden	CAP, CERM, 4.7 uF, 6.3 V, +/- 10%, X7R, 0603	0603
8	C17	1	22uF	C2012X7S1A226M125AC	TDK	CAP, CERM, 22 uF, 10 V, +/- 20%, X7S, 0805	0805
9	C18, C19, C20, C21, C29, C30, C32, C33, C34, C35, C36	11	0.1uF	0402YC104KAT2A	AVX	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
10	C22, C23, C24, C25, C28	5	0.01uF	520L103KT16T	AT Ceramics	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0402	0402
11	C27	1	0.047uF	CGA2B3X7R1H473K050BB	TDK	CAP, CERM, 0.047 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
12	C37, C38, C41, C42, C43, C44, C45	7	1uF	GCM188R71C105KA64J	MuRata	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
13	C39, C40, C46	3	10uF	CL10B106MQ8NRNC	Samsung Electro-Mechanics	CAP, CERM, 10 uF, 6.3 V, +/- 20%, X7R, 0603	0603
14	L1, L4	2	1000 ohm	BLM18AG102SN1D	MuRata	Ferrite Bead, 1000 ohm @ 100 MHz, 0.4 A, 0603	0603
15	L2	1	4.7uH	CBC3225T4R7MR	Taiyo Yuden	Inductor, Wirewound, 4.7 uH, 1.01 A, 0.1 ohm, SMD	3.2x2.5x2.5mm
16	L3	1	100uH	CBC3225T101MR	Taiyo Yuden	Inductor, Wirewound, 100 uH, 0.27 A, 1.4 ohm, SMD	3.2x2.5x2.5mm
17	L5	1	2.2uH	TFM201610ALMA2R2MTAA	TDK	Inductor, Shielded, Metal Composite, 2.2 uH, 1.9 A, 0.152 ohm, AEC-Q200 Grade 0, SMD	0806
18	L6, L7	2	1uH	TFM201610ALMA1R0MTAA	TDK	Inductor, Shielded, Metal Composite, 1 uH, 3.1 A, 0.06 ohm, AEC-Q200 Grade 0, SMD	0806
19	L8, L9	2	600 ohm	BLM18KG601SN1D	MuRata	Ferrite Bead, 600 ohm @ 100 MHz, 1.3 A, 0603	0603
20	L10, L11, L12, L13	4	220 ohm	BLM15AG221SN1D	MuRata	Ferrite Bead, 220 ohm @ 100 MHz, 0.45 A, 0402	0402
21	P1	1		59S1AC-40MT5-Z	Rosenberger	Connector, HF, 50 Ohm, TH	Connector, HF, TH
22	R1, R2	2	1.0k	RC0603JR-071KL	Yageo	RES, 1.0 k, 5%, 0.1 W, 0603	0603
23	R3, R6, R7, R8, R9, R13, R17, R31	8	0	RC0402JR-070RL	Yageo America	RES, 0, 5%, 0.063 W, 0402	0402
24	R14	1	49.9	RMCF0402FT49R9	Stackpole Electronics Inc	RES, 49.9, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
25	R19	1	33	CRCW040233R0JNED	Vishay-Dale	RES, 33, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
26	R21, R22, R24, R28, R30	5	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
27	R23	1	4.70k	RC0402FR-074K7L	Yageo America	RES, 4.70 k, 1%, 0.0625 W, 0402	0402
28	R25, R26	2	3.3k	CRCW04023K30JNED	Vishay-Dale	RES, 3.3 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
29	U1	1		TPS650320QRGEQ1	Texas Instruments	Automotive Camera PMIC	VQFN24
30	U2	1		DS90UB933TRTVRQ1	Texas Instruments	12-bit 100 MHz FPD-Link III Serializer for 1MP/60fps and 2MP/30fps Cameras, RTV0032A (WQFN-32)	RTV0032A
31	U3	1		OX01F10-E48Y-1D-Z	Omnivision Technologies	1/3.55" color CMOS (1340 x 1020) HDR image sensor	a-CSP48
32	Y1	1		ECS-2018-480-BN	ECS Inc.	XO, 48.000 MHz, 1.8V, SMD	2.5x0.9x2.0mm
33	C31	0	0.1uF	0402YC104KAT2A	AVX	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
34	FID1, FID2, FID3, FID4, FID5, FID6	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
35	R12	0	10.0k	RMCF0402FT10K0	Stackpole Electronics Inc	RES, 10.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
36	R29	0	10k	CRCW040210K0JNED	Vishay-Dale	RES, 10 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated