

PMP23404 REV A Bill of Materials

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
C1	1	56uF	CAP, Polymer Hybrid, 82 uF, 63 V, +/- 20%, 30 ohm, 10x10 SMD	10x10	EEHZC1J560P	Panasonic		
C2, C3	2	0.1uF	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0805	0805	C0805C104K1RACTU	Kemet		
C4, C5, C6, C7, C8, C14, C15, C16, C23, C24, C25	11	4.7uF	CAP, CERM, 4.7 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 1210	1210	GCM32DC72A475KE02L	MuRata		
C9	1	0.47uF	CAP, CERM, 0.47 uF, 100 V, +/- 10%, X7R, 0805	0805	GRM21BR72A474KA73L	MuRata		
C10	1	0.47uF	CAP, CERM, 0.47 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71C474KA55D	MuRata		
C11, C12, C13	3	2.2uF	CAP, CERM, 2.2 uF, 10 V, +/- 10%, X7R, 0603	0603	GRM188R71A225KE15D	MuRata		
C17, C18, C19, C20, C21, C22	6	0.01uF	CAP, CERM, 0.01 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7S2A103K050BB	TDK		
C26, C27, C33, C39	4	0.1uF	CAP, CERM, 0.1 uF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CGA3E2X7R1E104K080AA	TDK		
C28, C34	2	0.15uF	CAP, CERM, 0.15 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CGA3E3X7R1H154K080AB	TDK		
C29, C30, C31, C32, C35, C36, C37, C38, C38B, C38C	10	47uF	CAP, CERM, 47 uF, 6.3 V, +/- 20%, X7S, AEC-Q200 Grade 1, 1210	1210	CGA6P1X7S0J476M250AC	TDK		
C40, C41	2	33pF	CAP, CERM, 33 pF, 100 V, +/- 5%, C0G/NP0, 0603	0603	06031A330JAT2A	AVX		
C42, C42A, C42B, C42C, C42D, C42E, C42F, C42G, C42H, C42I	10	220uF	CAP, Tantalum Polymer, 220 uF, 10 V, +/- 20%, 0.025 ohm, AEC-Q200 Grade 1, 7343-31 SMD	7343-31	T598D227M010ATE025	Kemet		
C43	0	DNP	OMIT	0603				
C44, C45	2	0.22uF	CAP, CERM, 0.22 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CL10B224K08VPNC	Samsung		
C46, R22	2	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603L	CRCW06030000Z0EA	Vishay-Dale		
C47	1	4700pF	CAP, CERM, 4700 pF, 100 V, +/- 5%, X7R, 0603	0603	06031C472JAT2A	AVX		
C48, C49	2	220pF	CAP, CERM, 220 pF, 100 V, +/- 10%, X7R, 0603	0603	06031C221KAT2A	AVX		
D1, D2	2	100V	Diode, Schottky, 100 V, 0.25 A, SOD-323F	SOD-323F	BAT46WJ.115	Nexperia		
D3*	1	100V	Diode, Schottky, 100 V, 0.25 A, SOD-323F	SOD-323F	BAT46WJ.115	Nexperia	see note 2) below	
H1, H2, H3, H4	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Phillips panhead	Screw	NY PMS 440 0025 PH	B&F Fastener Supply		
H5, H6, H7, H8	4		Standoff, Hex, 0.5" L #4-40 Nylon	Standoff	1902C	Keystone		
J1	1		TEST POINT SLOTTED .118", TH	Test point, TH Slot Test point	1040	Keystone		
J2	1		Receptacle, 9.52mm, 2x1, TH	Receptacle, 9.52mm, 2x1, TH	1714971	Phoenix Contact		
J3	1		Terminal Block, 10.16mm, 2x1, Tin, R/A, TH	Terminal Block, 10.16mm, 2x1, TH	EM292902-UL	Eaton		
J4	1		Header, 100mil, 12x1, Gold, TH	12x1 Header	TSW-112-07-G-S	Samtec		
L1	1	1.2uH	Inductor, Shielded, Composite, 1.2 uH, 26.3 A, 0.0025 ohm, AEC-Q200 Grade 1, SMD	Inductor, 10x6x11.3mm	XAL1060-122MEB	Coilcraft		
L2, L3	2	1.5uH	Inductor 1.5uH 1.6mOhm 32.5A	SMD2	VCUD128T-1R5M58	Cyntec		
Q1, Q2	2		N-Channel 11A (Ta), 42A (Tc) 3.6W (Ta), 54W (Tc) Surface Mount 5-DFN (5x6) (8-SOFL)	DFN5	NVMF56H852NLWFT1G	ON Semiconductor		
Q3, Q4	2		N-Channel 80 V 24A (Ta), 160A (Tc) 3.8W (Ta), 167W (Tc) Surface Mount 5-DFN (5x6) (8-SOFL)	DFN5	NVMF56H801NLT1G	onsemi		
R1	1	1	RES, 1.00, 1%, 0.1 W, 0603	0603	RC0603FR-071RL	Yageo		
R2	1	0	RES, 0, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206	CRCW12060000Z0EA	Vishay-Dale		
R3, R4, R9, R10, R17, R18, R19, R20	8	100k	RES, 100 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW0603100KFKEA	Vishay-Dale		
R5, R6	2	6.49k	RES, 6.49 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06036K49FKEA	Vishay-Dale		
R7, R8	2	0.047uF	CAP, CERM, 0.047 uF, 50 V, +/- 10%, X7R, 0603	0603	C1608X7R1H473K080AA	TDK		
R11, R14	2	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06030000Z0EA	Vishay-Dale		
R12, R13	2	100	RES, 100, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW0603100RFKEA	Vishay-Dale		
R15, R16	0	DNP		0603				
R21	1	19.1k	RES, 19.1 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060319K1FKEA	Vishay-Dale		
R23	1	54.9k	RES, 54.9 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060354K9FKEA	Vishay-Dale		
R24, R25, R26, R27	4	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	0402	ERJ-2GE0R00X	Panasonic		
R28, R29	2	2.2	RES, 2.2, 5%, 0.125 W, AEC-Q200 Grade 0, 0805	0805	ERJ-6GEYJ2R2V	Panasonic		
SH-J1	1		Single Operation 2.54mm Pitch Open Top Jumper Socket	Single Operation 2.54mm Pitch Open Top Jumper Socket	M7582-05	Harwin		
TP1, TP2, TP3, TP4	4		Test Point, Miniature, SMT	Testpoint_Keystone_Miniature	5015	Keystone		
U1	1		Automotive 3.5-V to 65-V Dual Synchronous Buck Controller With Low IQ	VQFN40	LM5143QRHARQ1	Texas Instruments		

Notes:

1) Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated