

11/15/2016

## PMP20531 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C25	1	100pF	C0603C101J5GAC	Kemet	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	603
C5, C6, C7, C8, C20	5	1000pF	C1608X7R2A102K080AA	TDK	CAP, CERM, 1000 pF, 100 V, +/- 10%, X7R, 0603	603
C2, C4	2	0.01uF	06031C103KAT2A	AVX	CAP, CERM, 0.01 µF, 100 V, +/- 10%, X7R, 0603	603
C28	1	0.047uF	GRM188R71E473KA01D	MuRata	CAP, CERM, 0.047 µF, 25 V, +/- 10%, X7R, 0603	603
C26	1	0.015uF	GRM188R71E153KA01D	MuRata	CAP, CERM, 0.015 µF, 25 V, +/- 10%, X7R, 0603	603
C21	1	0.1uF	C1608X7R1E104K080AA	TDK	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, 0603	603
C24	1	0.22uF	GRM188R71E224KA88D	MuRata	CAP, CERM, 0.22 µF, 25 V, +/- 10%, X7R, 0603	603
C11, C14, C27	3	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	805
C19, C29	2	1uF	GRM219R71E105KA88D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0805	805
C30	0	DNP	GRM21A5C2E470JW01D	MuRata	CAP, CERM, 47 pF, 250 V, +/- 5%, C0G/NP0, 0805	805
C15, C16, C17, C18, C22	5	10uF	GRM31CR71C106KAC7L	MuRata	CAP, CERM, 10 µF, 16 V, +/- 10%, X7R, 1206	1206
C12, C13	2	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
C1, C3	2	1000pF	1812GC102KA1	AVX	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1812	1812
C9, C23	2	2200pF	C4532X7R3D222K130KA	TDK	CAP, CERM, 2200 pF, 2000 V, +/- 10%, X7R, 1812	1812
C10	1	22uF	EEE-FK2A220P	Panasonic	CAP, AL, 22uF, 100V, +/-20%, 1.3 ohm, SMD	SMT Radial F
D1	1		B1100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 1 A, SMA	SMA
D2, D3	2		HD01-T	Diodes Inc.	Diode, Switching-Bridge, 100 V, 0.8 A, MiniDIP	MiniDIP
D4	1		DFLU1200-7	Diodes Inc.	Diode, Superfast Rectifier, 200 V, 1 A, AEC-Q101, PowerDI123	PowerDI123
D5	1		B2100A-13-F	Diodes Inc.	Diode, Schottky, 100 V, 2 A, SMB	SMB
D6, D7	2		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100V, 0.2A, SOD-123	SOD-123
D8	1	5.1V	BZT52C5V1T-7	Diodes Inc.	Diode, Zener, 5.1 V, 300 mW, SOD-523	SOD-523
D9	1		BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30V, 0.2A, SOT-23	SOT-23
D10	1	58V	SMAJ58A	Diodes Inc.	Diode, TVS, Uni, 58 V, 400 W, SMA	SMA
J1, J2	2		1-406541-1	TE Connectivity	RJ-45, No LED, tab up, R/A, TH	16.26x14.54x15.75
J3, J4	2		ED555/2DS	On-Shore Technology	Terminal Block, 6A, 3.5mm Pitch, 2-Pos, TH	7.0x8.2x6.5mm
L1, L2, L3, L4	4	220 ohm	MPZ1608S221A	TDK	Ferrite Bead, 220 ohm @ 100 MHz, 2.2 A, 0603	603
L5	1	3.3uH	LPS3015-332MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 3.3 µH, 1.4 A, 0.13 ohm, SMD	LPS3015
Q1	1		FDC86244	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 2.3 A, SuperSOT-6	SuperSOT-6
R10	1	0	ERJ-3GEY0R00V	Panasonic	RES, 0 ohm, 5%, 0.1W, 0603	603
R13	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10 ohm, 5%, 0.1W, 0603	603
R1, R2, R3, R4	4	75	CRCW060375R0FKEA	Vishay-Dale	RES, 75.0 ohm, 1%, 0.1W, 0603	603
R17	1	90.9	CRCW060390R9FKEA	Vishay-Dale	RES, 90.9, 1%, 0.1 W, 0603	603
R18, R25	2	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	603
R21, R22, R24	3	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00k ohm, 1%, 0.1W, 0603	603
R11	1	3.01k	CRCW06033K01FKEA	Vishay-Dale	RES, 3.01 k, 1%, 0.1 W, 0603	603
R20	1	4.99k	CRCW06034K99FKEA	Vishay-Dale	RES, 4.99 k, 1%, 0.1 W, 0603	603
R23	1	6.49k	CRCW06036K49FKEA	Vishay-Dale	RES, 6.49 k, 1%, 0.1 W, 0603	603
R14	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0k ohm, 1%, 0.1W, 0603	603
R15, R16	2	24.9k	CRCW060324K9FKEA	Vishay-Dale	RES, 24.9 k, 1%, 0.1 W, 0603	603
R8	1	36.5k	CRCW060336K5FKEA	Vishay-Dale	RES, 36.5 k, 1%, 0.1 W, 0603	603
R9	1	59.0k	CRCW060359K0FKEA	Vishay-Dale	RES, 59.0 k, 1%, 0.1 W, 0603	603
R12	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	603
R6	1	20	CRCW080520R0JNEA	Vishay-Dale	RES, 20 ohm, 5%, 0.125W, 0805	805
R5	1	39k	CRCW080539K0JNEA	Vishay-Dale	RES, 39k ohm, 5%, 0.125W, 0805	805
R19	1	0.3	CSR1206FKR300	Stackpole Electronics Inc	RES, 0.3, 1%, 0.5 W, 1206	1206
R7	1	10	CRCW120610R0JNEA	Vishay-Dale	RES, 10, 5%, 0.25 W, 1206	1206
R26	0	DNP	CRCW120675R0JNEA	Vishay-Dale	RES, 75, 5%, 0.25 W, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
T1	1		H2019FNLT	Pulse Engineering	Transformer, 350uH, SMT	358x236x500mil
T2	1		UA8268-AL	Coilcraft	Transformer, Flyback, EP10, 30 uH, SMT	EP10, 8 pin SMD
U3	1		HMHA2801A	Fairchild Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	Mini Flat Package
U1	1		TPS23753APW	Texas Instruments	IEEE 802.3-2005 PoE Interface and Isolated Converter Controller with Enhanced ESD Ride-Through, -40 to 125 degC, 14-pin SOP (PW14), Green (RoHS & no Sb/Br)	PW0014A
U2	1		TL431AIDBVRA	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 5-pin SOT-23 (DBV), Green (RoHS & no Sb/Br)	DBV0005A

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated