

AI-Enabled, Wireless ECG Holter Monitor Reference Design for Real-Time Arrhythmia Classification



Description

The Edge-AI ready wearable biosensing Holter reference design provides an evaluation platform for TI's latest offerings in continuous monitoring of vital signs such as electrocardiography (ECG), heart rate, respiration, pace pulse, temperature, and motion. The design utilizes the AFE159RP4 for low-power, high-resolution, and highly-integrated ECG signal acquisition with up to 6 leads (4 channels) and the TMP119 for body temperature monitoring. The measured data is processed by the MSPM0 MCU with hardware acceleration for real-time arrhythmia classification, then transferred by the CC2340R5 (with Bluetooth® Low Energy 5.3 support) to a remote terminal such as a smartphone or medical monitoring system for real-time display. The full system can be powered by 2 × CR2032 batteries (3V input) or 1 × AAA battery (1.5V input).

Resources



| | |
|--|----------------|
| TIDA-010288 | Design Folder |
| AFE159RP4, MSPM0 | Product Folder |
| CC2340R5, TMP119, TPD1E01B04 | Product Folder |
| TPS62843, TPS61299 | Product Folder |

Features

- On-device AI hardware accelerator delivers immediate and precise detection of cardiac events
- Advanced, low-power features along with high-resolution recording and transmission only when necessary, enabling extended wear times
- Small, multiparameter, single-chip ECG Holter monitor design for synchronized ECG, respiration, and pace pulse detection
- Ultra-low-power 2.4G Bluetooth® Low Energy 5.3, Arm® Cortex®-M0+ processor supports wireless data transfer
- Highly efficient DC/DC converters support both 2 × CR2032 (3V, 210mAh) coin-cell batteries and 1 × AAA battery (1.5V, 500mAh)
- [SimpleLink™ Connect mobile application](#) for real-time ECG, arrhythmia classification, respiration, pace pulse, and temperature display

Applications

- [Medical sensor patches](#)
- [Electrocardiogram \(ECG\)](#)
- [Wearable fitness and activity monitor](#)



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2025, Texas Instruments Incorporated