

```
*****
*
* Model Usage Notes:
*
* A. Features have been modelled
* 1. Output Voltage Setting
* 2. Internal Fixed Soft-Start
* 3. Frequency and Operation Mode Selection
* 4. Low-side FET Zero-Crossing
* 5. Current Sense and Positive Overcurrent Protection(OCP)
* 6. Low-side FET Negative Current Limit
* 7. Power Good
* 8. Over Voltage Protection(OVP)
* 9. Under Voltage Protection(UVP)
* 10. Output Voltage Discharge
* 11. UVLO Protection
* 12. BOOT functionality
*
* B. Features have not been modelled
* 1. Operating Quiescent Current
* 2. Shutdown Current
* 3. Temperature dependent characteristics
*
* C. Application Notes
*
* 1. The parameter STEADY_STATE has been used to reach the steady state faster.
* Keep STEADY_STATE = 0 to observe startup behaviour.
* Keep STEADY_STATE = 1 and appropriate IC on Inductor and capacitor to observe for faster Steady state.
*
* 2. The parameter FASTSS_B has been used to reduce the soft start and hiccup reset time
* Keep FASTSS_B = 1 to observe the actual soft start and hiccup reset time
* Keep FASTSS_B = 0 to observe reduced soft start and hiccup reset time
*
*****
```