



* SURFACE - AIR 0 MM
L1: TOP CONDUCTOR - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.175 MM
L2: L2 PLANE - COPPER 0.035 MM

* DIELECTRIC - FR-4 1.01 MM


L3: L3 PLANE - COPPER 0.035 MM

* DIELECTRIC - FR-4 0.175 MM
L4: BOTTOM CONDUCTOR - COPPER 0.035 MM

* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART

TOTAL THICKNESS 1.5 MM



DRILL CHART: TOP to BOTTOM

ALL UNITS ARE IN MILLIMETERS

FIGURE	SIZE	PLATED	QTY
⊙	0.2	PLATED	300
.	0.4	PLATED	20
+	0.9	PLATED	4
.	0.325	NON-PLATED	1
▲	0.6	NON-PLATED	1
.	0.9	NON-PLATED	2
0	3.0x1.0	PLATED	2