

SNx4HC244 具有三态输出的八路缓冲器和线路驱动器

1 特性

- 2V 至 6V 的宽工作电压范围
- 高电流输出可驱动多达 15 个 LSTTL 负载
- 三态输出驱动总线或缓冲存储器地址寄存器
- 低功耗： I_{CC} ，80 μ A (最大值)
- t_{pd} 典型值 = 11ns
- ± 6 mA 输出驱动 (电压为 5V 时)
- 低输入电流，最大值为 1 μ A
- 对于符合 MIL-PRF-38535 标准的产品，所有参数均经过测试，除非另外注明。对于所有其他产品，生产流程不一定包含对所有参数进行的测试。

2 应用

- 服务器
- 发光二极管 (LED) 显示屏
- 网络交换机
- 电信基础设施
- 电机驱动器
- I/O 扩展器


3 说明

SNx4HC244 八路缓冲器和线路驱动器专门设计用于提高三态存储器地址驱动器、时钟驱动器以及总线导向接收器和发送器的性能和密度。SNx4HC244 器件配备两个具有独立输出使能 (\overline{OE}) 输入的 4 位缓冲器和驱动器。当 \overline{OE} 为低电平时，该器件将来自 A 输入的同相数据传递到 Y 输出。当 \overline{OE} 为高电平时，输出处于高阻态。

器件信息

| 器件型号 | 封装 ⁽¹⁾ | 封装尺寸 ⁽²⁾ | 本体尺寸 ⁽³⁾ |
|-----------|-------------------|---------------------|---------------------|
| SN54HC244 | J (CDIP, 20) | 24.38mm × 7.62mm | 24.38mm × 6.92mm |
| | W (CFP, 20) | 13.72mm × 8.13mm | 13.72mm × 6.92mm |
| | FK (LCCC, 20) | 8.89mm × 8.89mm | 8.89mm × 8.89mm |
| SN74HC244 | DB (SSOP, 20) | 7.2mm × 7.8mm | 7.2mm × 5.3mm |
| | DW (SOIC, 20) | 12.80mm × 10.3mm | 12.8mm × 7.5mm |
| | N (PDIP, 20) | 24.33mm × 9.4mm | 24.33mm × 6.35mm |
| | NS (SOP, 20) | 12.6mm × 7.8mm | 12.6mm × 5.3mm |
| | PW (TSSOP, 20) | 6.5mm × 6.4mm | 6.5mm × 4.4mm |

- (1) 如需了解更多信息，请参阅机械、封装和可订购信息。
- (2) 封装尺寸 (长 × 宽) 为标称值，并包括引脚 (如适用)。
- (3) 本体尺寸 (长 × 宽) 为标称值，不包括引脚。



逻辑图 (正逻辑)



内容

| | | | |
|--|----|-----------------------------|----|
| 1 特性 | 1 | 7.1 概述..... | 12 |
| 2 应用 | 1 | 7.2 功能方框图..... | 12 |
| 3 说明 | 1 | 7.3 特性说明..... | 12 |
| 4 引脚配置和功能 | 3 | 7.4 器件功能模式..... | 12 |
| 5 规格 | 4 | 8 应用和实施 | 13 |
| 5.1 绝对最大额定值..... | 4 | 8.1 应用信息..... | 13 |
| 5.2 ESD 等级..... | 4 | 8.2 典型应用..... | 13 |
| 5.3 建议运行条件..... | 4 | 8.3 电源相关建议..... | 14 |
| 5.4 热性能信息..... | 5 | 8.4 布局指南..... | 14 |
| 5.5 电气特性..... | 5 | 9 器件和文档支持 | 16 |
| 5.6 电气特性 - SN54HC244..... | 5 | 9.1 文档支持..... | 16 |
| 5.7 电气特性 - SN74HC244..... | 6 | 9.2 接收文档更新通知..... | 16 |
| 5.8 开关特性..... | 6 | 9.3 支持资源..... | 16 |
| 5.9 开关特性 - $C_L = 50\text{pF}$ | 8 | 9.4 商标..... | 16 |
| 5.10 开关特性 - $C_L = 150\text{pF}$ | 8 | 9.5 静电放电警告..... | 16 |
| 5.11 典型特性..... | 9 | 9.6 术语表..... | 16 |
| 6 参数测量信息 | 10 | 10 修订历史记录 | 16 |
| 7 详细说明 | 12 | 11 机械、封装和可订购信息 | 17 |

4 引脚配置和功能




图 4-1. DB、DW、J、N、NS、PW、W 封装 20 引脚 SSOP、SOIC、CDIP、PDIP、SOP、TSSOP 或 CFP 顶视图




图 4-2. FK 封装 20 引脚 LCCC 顶视图

| 引脚 | | I/O ⁽¹⁾ | 说明 |
|----|-------------------|--------------------|------|
| 编号 | 名称 | | |
| 1 | 1 \overline{OE} | I | 输出使能 |
| 2 | 1A1 | I | 输入 |
| 3 | 2Y4 | O | 输出 |
| 4 | 1A2 | I | 输入 |
| 5 | 2Y3 | O | 输出 |
| 6 | 1A3 | I | 输入 |
| 7 | 2Y2 | O | 输出 |
| 8 | 1A4 | I | 输入 |
| 9 | 2Y1 | O | 输出 |
| 10 | GND | — | 接地 |
| 11 | 2A1 | I | 输入 |
| 12 | 1Y4 | O | 输出 |
| 13 | 2A2 | I | 输入 |
| 14 | 1Y3 | O | 输出 |
| 15 | 2A3 | I | 输入 |
| 16 | 1Y2 | O | 输出 |
| 17 | 2A4 | I | 输入 |
| 18 | 1Y1 | O | 输出 |
| 19 | 2 \overline{OE} | I | 输出使能 |
| 20 | V _{CC} | — | 电源引脚 |

(1) 信号类型：I = 输入，O = 输出，I/O = 输入或输出。

5 规格

5.1 绝对最大额定值

在自然通风条件下的工作温度范围内测得 (除非另有说明) ⁽¹⁾

| | | 最小值 | 最大值 | 单位 |
|-------------------------|----------------------------|------|----------|--------------------|
| 电源电压范围, V_{CC} | | -0.5 | 7 | V |
| 输入钳位电流, I_{IK} | $V_I < 0$ 或 $V_I > V_{CC}$ | | ± 20 | mA |
| 输出钳位电流, I_{OK} | $V_O < 0$ 或 $V_O > V_{CC}$ | | ± 20 | mA |
| 持续输出电流, I_O | $V_O = 0$ 或 V_{CC} | | ± 35 | mA |
| 通过 V_{CC} 或 GND 的持续电流 | | | ± 70 | mA |
| 结温, T_J | | | 150 | $^{\circ}\text{C}$ |
| 贮存温度, T_{stg} | | -65 | 150 | $^{\circ}\text{C}$ |

(1) 应力超出绝对最大额定值下面列出的值可能会对器件造成永久损坏。这些列出的值仅仅是应力等级, 这并不表示器件在这些条件下以及在建议运行条件以外的任何其他条件下能够正常运行。长时间处于绝对最大额定条件下可能会影响器件的可靠性。

5.2 ESD 等级

| SN74HC244 | | 值 | 单位 |
|------------------|---|------------|----|
| $V_{(ESD)}$ 静电放电 | 人体放电模型 (HBM), 符合 ANSI/ESDA/JEDEC JS-001 标准 ⁽¹⁾ | ± 2000 | V |
| | 充电器件模型 (CDM), 符合 JEDEC 规范 JESD22-C101 ⁽²⁾ | ± 1000 | |

(1) JEDEC 文档 JEP155 指出: 500V HBM 时能够在标准 ESD 控制流程下安全生产。

(2) JEDEC 文档 JEP157 指出: 250V CDM 时能够在标准 ESD 控制流程下安全生产。

5.3 建议运行条件

在自然通风条件下的工作温度范围内测得 (除非另有说明) ⁽¹⁾

| | | 最小值 | 标称值 | 最大值 | 单位 |
|-----------------------|------------------------|-----------------|------|----------|--------------------|
| V_{CC} | 电源电压 | 2 | 5 | 6 | V |
| V_{IH} | 高电平输入电压 | $V_{CC} = 2V$ | | | V |
| | | $V_{CC} = 4.5V$ | 3.15 | | |
| | | $V_{CC} = 6V$ | 4.2 | | |
| V_{IL} | 低电平输入电压 | $V_{CC} = 2V$ | | 0.5 | V |
| | | $V_{CC} = 4.5V$ | | 1.35 | |
| | | $V_{CC} = 6V$ | | 1.8 | |
| V_I | 输入电压 | 0 | | V_{CC} | V |
| V_O | 输出电压 | 0 | | V_{CC} | V |
| $\Delta t / \Delta v$ | 输入转换上升和下降时间 | $V_{CC} = 2V$ | | 1000 | ns/V |
| | | $V_{CC} = 4.5V$ | | 500 | |
| | | $V_{CC} = 6V$ | | 400 | |
| C_{pd} | 每个缓冲器或驱动器的功率耗散电容 (无负载) | | 35 | | pF |
| T_A | 自然通风条件下的工作温度范围 | SN54HC244 | -55 | 125 | $^{\circ}\text{C}$ |
| | | SN74HC244 | -40 | 85 | |

(1) 器件所有的未使用输入必须保持在 V_{CC} 或 GND 以确保器件正常运行。请参阅德州仪器 (TI) 应用报告: CMOS 输入缓慢变化或悬空的影响 (SCBA004)。

5.4 热性能信息

| 热指标 | | SN74HC244 | | | | | 单位 |
|----------------------|-----------------------|-----------|-----------|----------|---------|------------|------|
| | | DW (SOIC) | DB (SSOP) | N (PDIP) | NS (SO) | PW (TSSOP) | |
| | | 20 引脚 | 20 引脚 | 20 引脚 | 20 引脚 | 20 引脚 | |
| $R_{\theta JA}$ | 结至环境热阻 ⁽¹⁾ | 109.1 | 122.7 | 84.6 | 113.4 | 131.8 | °C/W |
| $R_{\theta JC(top)}$ | 结至外壳 (顶部) 热阻 | 76 | 81.6 | 72.5 | 78.6 | 72.2 | °C/W |
| $R_{\theta JB}$ | 结至电路板热阻 | 77.6 | 77.5 | 65.3 | 78.4 | 82.8 | °C/W |
| Ψ_{JT} | 结至顶部特征参数 | 51.5 | 46.1 | 55.3 | 47.1 | 21.5 | °C/W |
| Ψ_{JB} | 结至电路板特征参数 | 77.1 | 77.1 | 65.2 | 78.1 | 82.4 | °C/W |
| $R_{\theta JC(bot)}$ | 结至外壳 (底部) 热阻 | 不适用 | 不适用 | 不适用 | 不适用 | 不适用 | °C/W |

(1) 有关新旧热指标的更多信息, 请参阅 *半导体和 IC 封装热指标应用报告*, [SPRA953](#)。

5.5 电气特性

$T_A = 25^\circ\text{C}$ (除非另有说明)

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|----------|--|--|------------------------|------------|-----------|---------------|
| V_{OH} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OH} = -20\mu\text{A}$ | $V_{CC} = 2\text{V}$ | 1.9 | 1.998 | V |
| | | | $V_{CC} = 4.5\text{V}$ | 4.4 | 4.499 | |
| | | | $V_{CC} = 6\text{V}$ | 5.9 | 5.999 | |
| | | $I_{OH} = -6\text{mA}, V_{CC} = 4.5\text{V}$ | 3.98 | 4.3 | | |
| | | $I_{OH} = -7.8\text{mA}, V_{CC} = 6\text{V}$ | 5.48 | 5.8 | | |
| V_{OL} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OL} = 20\mu\text{A}$ | $V_{CC} = 2\text{V}$ | 0.002 | 0.1 | V |
| | | | $V_{CC} = 4.5\text{V}$ | 0.001 | 0.1 | |
| | | | $V_{CC} = 6\text{V}$ | 0.001 | 0.1 | |
| | | $I_{OL} = 6\text{mA}, V_{CC} = 4.5\text{V}$ | 0.17 | 0.26 | | |
| | | $I_{OL} = 7.8\text{mA}, V_{CC} = 6\text{V}$ | 0.15 | 0.26 | | |
| I_I | $V_I = V_{CC}$ 或 0, $V_{CC} = 6\text{V}$ | | | ± 0.1 | ± 100 | nA |
| I_{OZ} | $V_O = V_{CC}$ 或 0, $V_I = V_{IH}$ 或 V_{IL} , $V_{CC} = 6\text{V}$ | | | ± 0.01 | ± 0.5 | μA |
| I_{CC} | $V_I = V_{CC}$ 或 0, $I_O = 0$, $V_{CC} = 6\text{V}$ | | | | 8 | μA |
| C_i | $V_{CC} = 2\text{V}$ 至 6V | | | 3 | 10 | pF |

5.6 电气特性 - SN54HC244

在自然通风条件下的建议运行温度范围内测得 (除非另有说明)

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|----------|--|--|------------------------|-----|------------|---------------|
| V_{OH} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OH} = -20\mu\text{A}$ | $V_{CC} = 2\text{V}$ | 1.9 | | V |
| | | | $V_{CC} = 4.5\text{V}$ | 4.4 | | |
| | | | $V_{CC} = 6\text{V}$ | 5.9 | | |
| | | $I_{OH} = -6\text{mA}, V_{CC} = 4.5\text{V}$ | 3.7 | | | |
| | | $I_{OH} = -7.8\text{mA}, V_{CC} = 6\text{V}$ | 5.2 | | | |
| V_{OL} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OL} = 20\mu\text{A}$ | $V_{CC} = 2\text{V}$ | | 0.1 | V |
| | | | $V_{CC} = 4.5\text{V}$ | | 0.1 | |
| | | | $V_{CC} = 6\text{V}$ | | 0.1 | |
| | | $I_{OL} = 6\text{mA}, V_{CC} = 4.5\text{V}$ | | 0.4 | | |
| | | $I_{OL} = 7.8\text{mA}, V_{CC} = 6\text{V}$ | | 0.4 | | |
| I_I | $V_I = V_{CC}$ 或 0, $V_{CC} = 6\text{V}$ | | | | ± 1000 | nA |
| I_{OZ} | $V_O = V_{CC}$ 或 0, $V_I = V_{IH}$ 或 V_{IL} , $V_{CC} = 6\text{V}$ | | | | ± 10 | μA |

在自然通风条件下的建议运行温度范围内测得 (除非另有说明)

| 参数 | 测试条件 | 最小值 | 典型值 | 最大值 | 单位 |
|----------|---|-----|-----|-----|---------|
| I_{CC} | $V_I = V_{CC}$ 或 0, $I_O = 0$, $V_{CC} = 6V$ | | | 160 | μA |
| C_i | $V_{CC} = 2V$ 至 $6V$ | | | 10 | pF |

5.7 电气特性 - SN74HC244

在自然通风条件下的建议运行温度范围内测得 (除非另有说明)

| 参数 | 测试条件 | 最小值 | 典型值 | 最大值 | 单位 |
|----------|---|-----------------------------------|-----------------|------------|---------|
| V_{OH} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OH} = -20\mu A$ | $V_{CC} = 2V$ | 1.9 | V |
| | | | $V_{CC} = 4.5V$ | 4.4 | |
| | | | $V_{CC} = 6V$ | 5.9 | |
| | | $I_{OH} = -6mA$, $V_{CC} = 4.5V$ | 3.84 | | |
| | | $I_{OH} = -7.8mA$, $V_{CC} = 6V$ | 5.34 | | |
| V_{OL} | $V_I = V_{IH}$ 或 V_{IL} | $I_{OL} = 20\mu A$ | $V_{CC} = 2V$ | 0.1 | V |
| | | | $V_{CC} = 4.5V$ | 0.1 | |
| | | | $V_{CC} = 6V$ | 0.1 | |
| | | $I_{OL} = 6mA$, $V_{CC} = 4.5V$ | 0.33 | | |
| | | $I_{OL} = 7.8mA$, $V_{CC} = 6V$ | 0.33 | | |
| I_I | $V_I = V_{CC}$ 或 0, $V_{CC} = 6V$ | | | ± 1000 | nA |
| I_{OZ} | $V_O = V_{CC}$ 或 0, $V_I = V_{IH}$ 或 V_{IL} , $V_{CC} = 6V$ | | | ± 5 | μA |
| I_{CC} | $V_I = V_{CC}$ 或 0, $I_O = 0$, $V_{CC} = 6V$ | | | 80 | μA |
| C_i | $V_{CC} = 2V$ 至 $6V$ | | | 10 | pF |

5.8 开关特性

$T_A = 25^\circ C$ (除非另有说明; 请参阅图 6-1)

| 参数 | 测试条件 | 最小值 | 典型值 | 最大值 | 单位 | |
|-----------|---------------------------------|-----------------|---------------|-----|-----|----|
| t_{pd} | 从 A (输入) 到 Y (输出) | $V_{CC} = 2V$ | $C_L = 50pF$ | 40 | 115 | ns |
| | | | $C_L = 150pF$ | 56 | 165 | |
| | | $V_{CC} = 4.5V$ | $C_L = 50pF$ | 13 | 23 | |
| | | | $C_L = 150pF$ | 18 | 33 | |
| | | $V_{CC} = 6V$ | $C_L = 50pF$ | 11 | 20 | |
| | | | $C_L = 150pF$ | 15 | 28 | |
| t_{en} | 从 \overline{OE} (输入) 到 Y (输出) | $V_{CC} = 2V$ | $C_L = 50pF$ | 75 | 150 | ns |
| | | | $C_L = 150pF$ | 100 | 200 | |
| | | $V_{CC} = 4.5V$ | $C_L = 50pF$ | 15 | 30 | |
| | | | $C_L = 150pF$ | 20 | 40 | |
| | | $V_{CC} = 6V$ | $C_L = 50pF$ | 13 | 26 | |
| | | | $C_L = 150pF$ | 17 | 34 | |
| t_{dis} | 从 \overline{OE} (输入) 到 Y (输出) | $V_{CC} = 2V$ | $C_L = 50pF$ | 75 | 150 | ns |
| | | $V_{CC} = 4.5V$ | $C_L = 50pF$ | 15 | 30 | |
| | | $V_{CC} = 6V$ | $C_L = 50pF$ | 13 | 26 | |

$T_A = 25^\circ\text{C}$ (除非另有说明; 请参阅图 6-1)

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|-------|----------|------------------------|----------------------|-----|-----|----|
| t_t | 到 Y (输出) | $V_{CC} = 2\text{V}$ | $C_L = 50\text{pF}$ | 28 | 60 | ns |
| | | | $C_L = 150\text{pF}$ | 45 | 210 | |
| | | $V_{CC} = 4.5\text{V}$ | $C_L = 50\text{pF}$ | 8 | 12 | |
| | | | $C_L = 150\text{pF}$ | 17 | 42 | |
| | | $V_{CC} = 6\text{V}$ | $C_L = 50\text{pF}$ | 6 | 10 | |
| | | | $C_L = 150\text{pF}$ | 13 | 36 | |

5.9 开关特性 - $C_L = 50\text{pF}$

在建议的自然通风条件下的工作温度范围内测得（除非另有说明；请参阅图 6-1）

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|-----------|---------------------------------|------------------------|-----------|-----|-----|----|
| t_{pd} | 从 A (输入) 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 170 | ns |
| | | | SN74HC244 | | 145 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 34 | |
| | | | SN74HC244 | | 29 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 29 | |
| | | | SN74HC244 | | 25 | |
| t_{en} | 从 \overline{OE} (输入) 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 225 | ns |
| | | | SN74HC244 | | 190 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 45 | |
| | | | SN74HC244 | | 38 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 38 | |
| | | | SN74HC244 | | 32 | |
| t_{dis} | 从 \overline{OE} (输入) 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 225 | ns |
| | | | SN74HC244 | | 190 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 45 | |
| | | | SN74HC244 | | 38 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 38 | |
| | | | SN74HC244 | | 32 | |
| t_t | 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 90 | ns |
| | | | SN74HC244 | | 75 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 18 | |
| | | | SN74HC244 | | 15 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 15 | |
| | | | SN74HC244 | | 13 | |

5.10 开关特性 - $C_L = 150\text{pF}$

在建议的自然通风条件下的工作温度范围内测得（除非另有说明；请参阅图 6-1）

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|----------|---------------------------------|------------------------|-----------|-----|-----|----|
| t_{pd} | 从 A (输入) 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 245 | ns |
| | | | SN74HC244 | | 210 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 49 | |
| | | | SN74HC244 | | 42 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 42 | |
| | | | SN74HC244 | | 35 | |
| t_{en} | 从 \overline{OE} (输入) 到 Y (输出) | $V_{CC} = 2\text{V}$ | SN54HC244 | | 300 | ns |
| | | | SN74HC244 | | 250 | |
| | | $V_{CC} = 4.5\text{V}$ | SN54HC244 | | 60 | |
| | | | SN74HC244 | | 50 | |
| | | $V_{CC} = 6\text{V}$ | SN54HC244 | | 51 | |
| | | | SN74HC244 | | 43 | |

在建议的自然通风条件下的工作温度范围内测得 (除非另有说明; 请参阅图 6-1)

| 参数 | 测试条件 | | 最小值 | 典型值 | 最大值 | 单位 |
|-------|----------|-----------------|-----------|-----|-----|----|
| t_t | 到 Y (输出) | $V_{CC} = 2V$ | SN54HC244 | | 315 | ns |
| | | | SN74HC244 | | 265 | |
| | | $V_{CC} = 4.5V$ | SN54HC244 | | 63 | |
| | | | SN74HC244 | | 53 | |
| | | $V_{CC} = 6V$ | SN54HC244 | | 53 | |
| | | | SN74HC244 | | 45 | |

5.11 典型特性




图 5-1. 传播延迟

6 参数测量信息




图 6-1. 负载电路




图 6-2. 传播延迟和输出转换时间




图 6-3. 输入上升和下降时间




图 6-4. 三态输出的启用和禁用时间

备注

注意：

- A. C_L 包括探头和测试夹具电容。
- B. 波形 1 用于具有内部条件的输出，使得输出为低电平，除非被输出控制禁用。波形 2 用于具有内部条件的输出，使得输出为高电平，除非被输出控制禁用。
- C. 任意选择波形之间的相位关系。所有输入脉冲均由具有以下特性的发生器提供： $PRR \leq 1\text{MHz}$ ， $Z_O = 50\ \Omega$ ， $t_r = 6\text{ns}$ ， $t_f = 6\text{ns}$ 。
- D. 一次测量一个输出，每次测量进行一次输入转换。
- E. t_{PLZ} 和 t_{PHZ} 与 t_{dis} 一样。
- F. t_{pZL} 和 t_{pZH} 与 t_{en} 一样。
- G. t_{PLH} 和 t_{PHL} 与 t_{pd} 一样。

表 6-1. 开关信息表

| 参数 | | RL | CL | S1 | S2 |
|------------------|-----------|-------------|--------------|----|----|
| t_{en} | t_{pZH} | 1k Ω | 50pF 或 150pF | 开路 | 闭合 |
| | t_{pZL} | 1k Ω | 50pF 或 150pF | 闭合 | 开路 |
| t_{dis} | t_{PHZ} | 1k Ω | 50pF | 开路 | 闭合 |
| | t_{PLZ} | 1k Ω | 50pF | 闭合 | 开路 |
| t_{pd} 或 t_t | | — | 50pF 或 150pF | 开路 | 开路 |

7 详细说明

7.1 概述

SNx4HC244 包含 8 个具有施密特触发输入和三态输出的独立高速 CMOS 缓冲器。

每个缓冲器均可执行布尔逻辑函数 $xY_n = xA_n$ ，其中 x 为存储体编号， n 为通道编号。

每个输出使能 (\overline{xOE}) 控制四个缓冲器。当 \overline{xOE} 引脚处于低电平状态时，存储体 x 中所有缓冲器的输出将被启用。当 \overline{xOE} 引脚处于高电平状态时，存储体 x 中所有缓冲器的输出将被禁用。所有被禁用的输出将置于高阻抗状态。

为了在上电或断电期间将器件置于高阻抗状态，需将两个 \overline{OE} 引脚通过一个上拉电阻连接至 V_{CC} ；电阻的最小值由驱动器的灌电流能力和 *电气特性* 表中定义的引脚漏电流决定。

7.2 功能方框图




图 7-1. 逻辑图 (正逻辑)

7.3 特性说明

7.3.1 标准 CMOS 输入

此器件包括标准 CMOS 输入。标准 CMOS 输入为高阻抗，通常建模为与输入电容并联的电阻器，如 *电气特性* 中所示。最坏情况下的电阻是根据 *绝对最大额定值* 中给出的最大输入电压和 *电气特性* 中给出的最大输入漏电流，使用欧姆定律 ($R = V \div I$) 计算得出的。

标准 CMOS 输入要求输入信号在有效逻辑状态之间快速转换，如 *建议运行条件* 表中的输入转换时间或速率所定义。不符合此规范将导致功耗过大并可能导致振荡。更多详细信息，请参阅 *CMOS 输入缓慢或悬空的影响*。

在运行期间，任何时候都不要让标准 CMOS 输入悬空。未使用的输入必须在 V_{CC} 或 GND 端接。如果系统不会一直主动驱动输入，则可以添加上拉或下拉电阻器，以在这些时间段提供有效的输入电压。电阻值将取决于多种因素；但建议使用 $10k\Omega$ 电阻器，这通常可以满足所有要求。

7.4 器件功能模式

表 7-1 列出了 SNx4HC244 的功能模式。

表 7-1. 功能表

| 输入 ⁽¹⁾ | | 输出 |
|-------------------|---|----|
| \overline{OE} | A | Y |
| L | L | L |
| L | H | H |
| H | X | Z |

(1) H = 高压电平, L = 低压电平, X = 无关, Z = 高阻抗状态

8 应用和实施


备注

以下应用部分中的信息不属于 TI 器件规格的范围，TI 不担保其准确性和完整性。TI 的客户应负责确定器件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

8.1 应用信息

SN74HC244 是一款低驱动 CMOS 器件，可用于需要考虑输出驱动或布线长度的多种总线接口类型应用。

8.2 典型应用



Copyright © 2016, Texas Instruments Incorporated

图 8-1. SN74HC244 应用原理图

8.2.1 设计要求

此器件采用 CMOS 技术并具有平衡输出驱动。注意避免总线争用，因为它可以驱动超过最大限值的电流。高驱动也会在轻负载时产生快速边缘，因此应考虑布线和负载条件以防止振铃。

8.2.2 详细设计过程

1. 建议的输入条件：

- 有关上升时间和下降时间规范，请参阅 [节 5.3](#) 表中的 $\Delta t / \Delta V$ 。
- 有关指定的高电平和低电平，请参阅 [节 5.3](#) 中的 V_{IH} 和 V_{IL} 。

2. 建议的输出条件：

- 每路输出的负载电流不应超过最大值 I_O ，且不应超过该器件通过 V_{CC} 的持续电流或 GND 总电流。这些示例位于：[节 5.1](#)。
- 输出不应被拉至高于 V_{CC} 。

8.2.3 应用曲线




图 8-2. 启用时间

8.3 电源相关建议

电源可以是 *建议运行条件* 中最小和最大电源电压额定值之间的任何电压。每个 V_{CC} 端子均应具有良好的旁路电容器，以防止功率干扰。建议为该器件使用 $0.1 \mu F$ 电容器。可以并联多个旁路电容器以抑制不同的噪声频率。 $0.1 \mu F$ 和 $1 \mu F$ 电容器通常并联使用。为了获得最佳效果，旁路电容器必须尽可能靠近电源端子安装。

8.4 布局指南

- 旁路电容器的放置
 - 靠近器件的正电源端子放置
 - 提供电气短接地返回路径
 - 使用宽布线以最大限度减小阻抗
 - 尽可能将器件、电容器和布线保持在电路板的同一面
- 信号布线几何形状
 - 8mil 至 12mil 布线宽度
 - 布线长度小于 12cm 可最大限度减轻传输线路影响
 - 避免信号布线出现 90° 角
 - 在信号布线下方使用不间断的接地平面
 - 通过接地对信号布线周围的区域进行泛洪填充
 - 对于长度超过 12cm 的布线
 - 使用阻抗受控的布线
 - 在输出端附近使用串联阻尼电阻进行源端接
 - 避免分支；对必须单独分支的信号进行缓冲

8.4.1 布局示例




图 8-3. 可改善信号完整性的布线转角示例




图 8-4. TSSOP 和类似封装的旁路电容器放置示例




图 8-5. WQFN 和类似封装的旁路电容器放置示例




图 8-6. SOT、SC70 和类似封装的旁路电容器放置示例




图 8-7. 可改善信号完整性的阻尼电阻放置示例

9 器件和文档支持

9.1 文档支持

9.1.1 相关链接

表 9-1 列出了快速访问链接。类别包括技术文档、支持和社区资源、工具和软件，以及申请样片或购买产品的快速链接。

表 9-1. 相关链接

| 器件 | 产品文件夹 | 样片与购买 | 技术文档 | 工具和软件 | 支持和社区 |
|-----------|----------------------|----------------------|----------------------|----------------------|----------------------|
| SN54HC244 | 点击此处 | 点击此处 | 点击此处 | 点击此处 | 点击此处 |
| SN74HC244 | 点击此处 | 点击此处 | 点击此处 | 点击此处 | 点击此处 |

9.2 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

9.3 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

9.4 商标

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

9.5 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

9.6 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

10 修订历史记录

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision F (May 2022) to Revision G (January 2025) Page

- 向 [器件信息表](#) 添加了封装尺寸，并根据当前标准更新了数据表的结构布局..... [1](#)
- 更新了 [特性说明](#) 并更正了 [功能方框图](#) 图像和 [器件功能模式表](#)..... [12](#)

Changes from Revision E (May 2016) to Revision F (May 2022) Page

- 提高了结温至环境温度热阻值以匹配电流函数。..... [5](#)

11 机械、封装和可订购信息

以下页面包含机械、封装和可订购信息。这些信息是指定器件可用的最新数据。数据如有变更，恕不另行通知，且不会对此文档进行修订。有关此数据表的浏览器版本，请查阅左侧的导航栏。

PACKAGING INFORMATION

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|---------------|--------------|-----------------|------|-------------|---------------------|--------------------------------------|----------------------|--------------|------------------------------------|-------------------------|
| 5962-8409601VRA | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-8409601VR A SNV54HC244J | Samples |
| 5962-8409601VSA | ACTIVE | CFP | W | 20 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-8409601VS A SNV54HC244W | Samples |
| 84096012A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 84096012A SNJ54HC 244FK | Samples |
| 8409601RA | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 8409601RA SNJ54HC244J | Samples |
| 8409601SA | ACTIVE | CFP | W | 20 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 8409601SA SNJ54HC244W | Samples |
| JM38510/65705B2A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705B2A | Samples |
| JM38510/65705BRA | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705BRA | Samples |
| JM38510/65705BSA | ACTIVE | CFP | W | 20 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705BSA | Samples |
| M38510/65705B2A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705B2A | Samples |
| M38510/65705BRA | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705BRA | Samples |
| M38510/65705BSA | ACTIVE | CFP | W | 20 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 65705BSA | Samples |
| SN54HC244J | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SN54HC244J | Samples |
| SN74HC244APWR | ACTIVE | TSSOP | PW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244A | Samples |
| SN74HC244DBR | ACTIVE | SSOP | DB | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244DWR | ACTIVE | SOIC | DW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244DWRE4 | ACTIVE | SOIC | DW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |

| Orderable Device | Status (1) | Package Type | Package Drawing | Pins | Package Qty | Eco Plan (2) | Lead finish/ Ball material (6) | MSL Peak Temp (3) | Op Temp (°C) | Device Marking (4/5) | Samples |
|-------------------|---------------|--------------|-----------------|------|-------------|---------------------|--------------------------------------|----------------------|--------------|-------------------------------|-------------------------|
| SN74HC244DWRG4 | ACTIVE | SOIC | DW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244N | ACTIVE | PDIP | N | 20 | 20 | RoHS & Green | NIPDAU | N / A for Pkg Type | -40 to 85 | SN74HC244N | Samples |
| SN74HC244NE4 | ACTIVE | PDIP | N | 20 | 20 | RoHS & Green | NIPDAU | N / A for Pkg Type | -40 to 85 | SN74HC244N | Samples |
| SN74HC244NSR | ACTIVE | SOP | NS | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244NSRG4 | ACTIVE | SOP | NS | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244PW | OBSOLETE | TSSOP | PW | 20 | | TBD | Call TI | Call TI | -40 to 85 | HC244 | |
| SN74HC244PWR | ACTIVE | TSSOP | PW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244PWRE4 | ACTIVE | TSSOP | PW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244PWRG4 | ACTIVE | TSSOP | PW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 85 | HC244 | Samples |
| SN74HC244PWT | OBSOLETE | TSSOP | PW | 20 | | TBD | Call TI | Call TI | -40 to 85 | HC244 | |
| SN74HC244QDWRG4Q1 | ACTIVE | SOIC | DW | 20 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | | HC244Q | Samples |
| SNJ54HC244FK | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 84096012A SNJ54HC 244FK | Samples |
| SNJ54HC244J | ACTIVE | CDIP | J | 20 | 20 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 8409601RA SNJ54HC244J | Samples |
| SNJ54HC244W | ACTIVE | CFP | W | 20 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 8409601SA SNJ54HC244W | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of ≤ 1000 ppm threshold. Antimony trioxide based flame retardants must also meet the ≤ 1000 ppm threshold requirement.

- (3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54HC244, SN54HC244-SP, SN74HC244 :

- Catalog : [SN74HC244](#), [SN54HC244](#)
- Automotive : [SN74HC244-Q1](#), [SN74HC244-Q1](#)
- Enhanced Product : [SN74HC244-EP](#), [SN74HC244-EP](#)
- Military : [SN54HC244](#)
- Space : [SN54HC244-SP](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

- Enhanced Product - Supports Defense, Aerospace and Medical Applications
- Military - QML certified for Military and Defense Applications
- Space - Radiation tolerant, ceramic packaging and qualified for use in Space-based application

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74HC244APWR | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74HC244APWR | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.1 | 1.6 | 8.0 | 16.0 | Q1 |
| SN74HC244DBR | SSOP | DB | 20 | 2000 | 330.0 | 16.4 | 8.2 | 7.5 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74HC244DBR | SSOP | DB | 20 | 2000 | 330.0 | 16.4 | 8.2 | 7.5 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74HC244DWR | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.9 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |
| SN74HC244DWR | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.8 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |
| SN74HC244DWRG4 | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.8 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |
| SN74HC244NSR | SOP | NS | 20 | 2000 | 330.0 | 24.4 | 8.4 | 13.0 | 2.5 | 12.0 | 24.0 | Q1 |
| SN74HC244NSR | SOP | NS | 20 | 2000 | 330.0 | 24.4 | 8.4 | 13.0 | 2.5 | 12.0 | 24.0 | Q1 |
| SN74HC244PWR | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74HC244PWR | TSSOP | PW | 20 | 2000 | 330.0 | 16.4 | 6.95 | 7.0 | 1.4 | 8.0 | 16.0 | Q1 |
| SN74HC244QDWRG4Q1 | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.8 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74HC244APWR | TSSOP | PW | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244APWR | TSSOP | PW | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244DBR | SSOP | DB | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244DBR | SSOP | DB | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244DWR | SOIC | DW | 20 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74HC244DWR | SOIC | DW | 20 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74HC244DWRG4 | SOIC | DW | 20 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74HC244NSR | SOP | NS | 20 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74HC244NSR | SOP | NS | 20 | 2000 | 367.0 | 367.0 | 45.0 |
| SN74HC244PWR | TSSOP | PW | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244PWR | TSSOP | PW | 20 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74HC244QDWRG4Q1 | SOIC | DW | 20 | 2000 | 367.0 | 367.0 | 45.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-8409601VSA | W | CFP | 20 | 25 | 506.98 | 26.16 | 6220 | NA |
| 84096012A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| 8409601SA | W | CFP | 20 | 25 | 506.98 | 26.16 | 6220 | NA |
| JM38510/65705B2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| JM38510/65705BSA | W | CFP | 20 | 25 | 506.98 | 26.16 | 6220 | NA |
| M38510/65705B2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| M38510/65705BSA | W | CFP | 20 | 25 | 506.98 | 26.16 | 6220 | NA |
| SN74HC244N | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |
| SN74HC244NE4 | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |
| SNJ54HC244FK | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| SNJ54HC244W | W | CFP | 20 | 25 | 506.98 | 26.16 | 6220 | NA |

W (R-GDFP-F20)

CERAMIC DUAL FLATPACK



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - C. This package can be hermetically sealed with a ceramic lid using glass frit.
 - D. Index point is provided on cap for terminal identification only.
 - E. Falls within Mil-Std 1835 GDFP2-F20

PW0020A



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



4220206/A 02/2017

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

EXAMPLE BOARD LAYOUT

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4220206/A 02/2017

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

DB0020A



PACKAGE OUTLINE

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



4214851/B 08/2019

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

EXAMPLE BOARD LAYOUT

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4214851/B 08/2019

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

MECHANICAL DATA

NS (R-PDSO-G**)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

J (R-GDIP-T**)

14 LEADS SHOWN

CERAMIC DUAL IN-LINE PACKAGE



| DIM \ PINS ** | 14 | 16 | 18 | 20 |
|---------------|------------------------|------------------------|------------------------|------------------------|
| A | 0.300 (7,62) BSC | 0.300 (7,62) BSC | 0.300 (7,62) BSC | 0.300 (7,62) BSC |
| B MAX | 0.785 (19,94) | .840 (21,34) | 0.960 (24,38) | 1.060 (26,92) |
| B MIN | — | — | — | — |
| C MAX | 0.300 (7,62) | 0.300 (7,62) | 0.310 (7,87) | 0.300 (7,62) |
| C MIN | 0.245 (6,22) | 0.245 (6,22) | 0.220 (5,59) | 0.245 (6,22) |



4040083/F 03/03

- NOTES:
- All linear dimensions are in inches (millimeters).
 - This drawing is subject to change without notice.
 - This package is hermetically sealed with a ceramic lid using glass frit.
 - Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
 - Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

GENERIC PACKAGE VIEW

FK 20

LCCC - 2.03 mm max height

8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4229370VA\

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- NOTES:
- A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
 - The 20 pin end lead shoulder width is a vendor option, either half or full width.

DW0020A



PACKAGE OUTLINE

SOIC - 2.65 mm max height

SOIC



4220724/A 05/2016

NOTES:

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

EXAMPLE BOARD LAYOUT

DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
版权所有 © 2025，德州仪器 (TI) 公司