

# SN54ALS541, SN74ALS540, SN74ALS541 OCTAL BUFFERS AND LINE DRIVERS WITH 3-STATE OUTPUTS

SDAS025D – APRIL 1982 – REVISED MARCH 2002

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- pnp Inputs Reduce dc Loading
- Data Flowthrough Pinout (All Inputs on Opposite Side From Outputs)

## description

These octal buffers and line drivers are designed to have the performance of the popular SN54ALS240A/SN74ALS240A series and, at the same time, offer a pinout with inputs and outputs on opposite sides of the package. This arrangement greatly facilitates printed circuit board layout.


The 3-state control gate is a 2-input NOR gate such that, if either output-enable ( $\overline{OE}_1$  or  $\overline{OE}_2$ ) input is high, all eight outputs are in the high-impedance state.

The SN74ALS540 provides inverted data. The 'ALS541 provide true data at the outputs.


The -1 versions of SN74ALS540 and SN74ALS541 are identical to the standard versions, except that the recommended maximum  $I_{OL}$  is increased to 48 mA. There is no -1 version of the SN54ALS541.

SN54ALS541 . . . J PACKAGE  
SN74ALS540 . . . DW, N, OR NS PACKAGE  
SN74ALS541 . . . DB, DW, N, OR NS PACKAGE

(TOP VIEW)



SN54ALS541 . . . FK PACKAGE  
(TOP VIEW)



  
Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

 **TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2002, Texas Instruments Incorporated  
On products compliant to MIL-PRF-38535, all parameters are tested unless otherwise noted. On all other products, production processing does not necessarily include testing of all parameters.

**SN54ALS541, SN74ALS540, SN74ALS541  
OCTAL BUFFERS AND LINE DRIVERS  
WITH 3-STATE OUTPUTS**


SDAS025D – APRIL 1982 – REVISED MARCH 2002

**ORDERING INFORMATION**

| TA             | PACKAGE <sup>†</sup> |               | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|----------------|----------------------|---------------|-----------------------|------------------|
| 0°C to 70°C    | PDIP – N             | Tube          | SN74ALS540N           | SN74ALS540N      |
|                |                      |               | SN74ALS540-1N         | SN74ALS540-1N    |
|                |                      |               | SN74ALS541N           | SN74ALS541N      |
|                |                      |               | SN74ALS541-1N         | SN74ALS541-1N    |
|                | SOIC – DW            | Tube          | SN74ALS540DW          | ALS540           |
|                |                      | Tape and reel | SN74ALS540DWR         |                  |
|                |                      | Tube          | SN74ALS540-1DW        | ALS540-1         |
|                |                      | Tube          | SN74ALS541DW          | ALS541           |
|                |                      | Tape and reel | SN74ALS541DWR         |                  |
|                |                      | Tube          | SN74ALS541-1DW        | ALS541-1         |
|                | SOP – NS             | Tape and reel | SN74ALS540NSR         | ALS540           |
|                |                      | Tape and reel | SN74ALS540-1NSR       | ALS540-1         |
|                |                      |               | SN74ALS541NSR         | ALS541           |
|                |                      |               | SN74ALS541-1NSR       | ALS541-1         |
| -55°C to 125°C | SSOP – DB            | Tape and reel | SN74ALS541DBR         | G541             |
|                |                      |               | SN74ALS541-1DBR       | G541-1           |
|                | CDIP – J             | Tube          | SNJ54ALS541J          | SNJ54ALS541J     |
|                | LCCC – FK            | Tube          | SNJ54ALS541FK         | SNJ54ALS541FK    |

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).

**logic diagrams (positive logic)**



# **SN54ALS541, SN74ALS540, SN74ALS541 OCTAL BUFFERS AND LINE DRIVERS WITH 3-STATE OUTPUTS**

SDAS025D – APRIL 1982 – REVISED MARCH 2002

**absolute maximum ratings over operating free-air temperature (unless otherwise noted)†**

|  |                |
|--|----------------|
| Supply voltage, $V_{CC}$ .....                         | 7 V            |
| Input voltage, $V_I$ .....                             | 7 V            |
| Voltage applied to a disabled 3-state output .....     | 5.5 V          |
| Package thermal impedance, $\theta_{JA}$ (see Note 1): |                |
| DB package .....                                       | 70°C/W         |
| DW package .....                                       | 58°C/W         |
| N package .....  | 69°C/W         |
| NS package .....                                       | 60°C/W         |
| Storage temperature range, $T_{STG}$ .....             | -65°C to 150°C |

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The package thermal impedance is calculated in accordance with JESD 51-7.

### **recommended operating conditions**

|                 |                                | SN54ALS541 |     |     | SN74ALS540<br>SN74ALS541 |     |     | UNIT |
|-----------------|--------------------------------|------------|-----|-----|--------------------------|-----|-----|------|
|                 |                                | MIN        | NOM | MAX | MIN                      | NOM | MAX |      |
| V <sub>CC</sub> | Supply voltage                 | 4.5        | 5   | 5.5 | 4.5                      | 5   | 5.5 | V    |
| V <sub>IH</sub> | High-level input voltage       |            | 2   |     |                          | 2   |     | V    |
| V <sub>IL</sub> | Low-level input voltage        |            |     | 0.7 |                          |     | 0.8 | V    |
| I <sub>OH</sub> | High-level output current      |            |     | -12 |                          |     | -15 | mA   |
| I <sub>OL</sub> | Low-level output current       |            |     | 12  |                          |     | 24  | mA   |
|                 |                                |            |     |     |                          |     | 48† |      |
| T <sub>A</sub>  | Operating free-air temperature | -55        |     | 125 | 0                        |     | 70  | °C   |

<sup>†</sup> Applies only to the -1 version and only if  $V_{CC}$  is between 4.75 V and 5.25 V

**SN54ALS541, SN74ALS540, SN74ALS541  
OCTAL BUFFERS AND LINE DRIVERS  
WITH 3-STATE OUTPUTS**

SDAS025D – APRIL 1982 – REVISED MARCH 2002

**electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)**

| PARAMETER                   | TEST CONDITIONS   | SN54ALS541                           |                  |      | SN74ALS540<br>SN74ALS541 |                  |      | UNIT |
|-----------------------------|---|--------------------------------------|------------------|------|--------------------------|------------------|------|------|
|                             |   | MIN                                  | TYP <sup>‡</sup> | MAX  | MIN                      | TYP <sup>‡</sup> | MAX  |      |
| V <sub>IK</sub>             | V <sub>CC</sub> = 4.5 V, I <sub>I</sub> = -18 mA            |                                      |                  | -1.2 |                          |                  | -1.2 | V    |
| V <sub>OH</sub>             | V <sub>CC</sub> = 4.5 V to 5.5 V, I <sub>OH</sub> = -0.4 mA | V <sub>CC</sub> - 2                  |                  |      | V <sub>CC</sub> - 2      |                  |      | V    |
|                             | V <sub>CC</sub> = 4.5 V                                     | I <sub>OH</sub> = -3 mA              | 2.4              | 3.2  | 2.4                      | 3.2              |      |      |
|                             |   | I <sub>OH</sub> = -12 mA             | 2                |      |                          |                  |      |      |
|                             |   | I <sub>OH</sub> = -15 mA             |                  |      |                          | 2                |      |      |
| V <sub>OL</sub>             | V <sub>CC</sub> = 4.5 V                                     | I <sub>OL</sub> = 12 mA              | 0.25             | 0.4  | 0.25                     | 0.4              |      | V    |
|                             |   | I <sub>OL</sub> = 24 mA              |                  |      | 0.35                     | 0.5              |      |      |
|                             |   | I <sub>OL</sub> = 48 mA <sup>†</sup> |                  |      | 0.35                     | 0.5              |      |      |
| I <sub>OZH</sub>            | V <sub>CC</sub> = 5.5 V, V <sub>O</sub> = 2.7 V             |                                      |                  | 20   |                          |                  | 20   | µA   |
| I <sub>OZL</sub>            | V <sub>CC</sub> = 5.5 V, V <sub>O</sub> = 0.4 V             |                                      |                  | -20  |                          |                  | -20  | µA   |
| I <sub>I</sub>              | V <sub>CC</sub> = 5.5 V, V <sub>I</sub> = 7 V               |                                      |                  | 0.1  |                          |                  | 0.1  | mA   |
| I <sub>IH</sub>             | V <sub>CC</sub> = 5.5 V, V <sub>I</sub> = 2.7 V             |                                      |                  | 20   |                          |                  | 20   | µA   |
| I <sub>IL</sub>             | V <sub>CC</sub> = 5.5 V, V <sub>I</sub> = 0.4 V             |                                      |                  | -0.2 |                          |                  | -0.1 | mA   |
| I <sub>O</sub> <sup>§</sup> | V <sub>CC</sub> = 5.5 V, V <sub>O</sub> = 2.25 V            | -20                                  | -112             | -30  | -112                     |                  |      | mA   |
| I <sub>CC</sub>             | SN74ALS540<br>V <sub>CC</sub> = 5.5 V                       | Outputs high                         |                  |      |                          | 5                | 10   | mA   |
|                             |   | Outputs low                          |                  |      |                          | 13               | 22   |      |
|                             |   | Outputs disabled                     |                  |      |                          | 11               | 19   |      |
|                             | 'ALS541<br>V <sub>CC</sub> = 5.5 V                          | Outputs high                         | 6                | 14   |                          | 6                | 14   |      |
|                             |   | Outputs low                          | 15               | 25   |                          | 15               | 25   |      |
|                             |   | Outputs disabled                     | 13.5             | 32   |                          | 13.5             | 22   |      |

<sup>†</sup> Applies only to the -1 version and only if V<sub>CC</sub> is between 4.75 V and 5.25 V

<sup>‡</sup> All typical values are at V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C.

<sup>§</sup> The output conditions have been chosen to produce a current that closely approximates one-half of the true short-circuit output current, I<sub>OS</sub>.

**switching characteristics (see Figure 1)**

| PARAMETER        | FROM<br>(INPUT) | TO<br>(OUTPUT) | V <sub>CC</sub> = 4.5 V to 5.5 V,<br>C <sub>L</sub> = 50 pF,<br>R <sub>1</sub> = 500 Ω,<br>R <sub>2</sub> = 500 Ω,<br>T <sub>A</sub> = MIN to MAX <sup>¶</sup> |     |            |     |            | UNIT |    |
|------------------|-----------------|----------------|--|-----|------------|-----|------------|------|----|
|                  |                 |                | SN54ALS541   |     | SN74ALS540 |     | SN74ALS541 |      |    |
|                  |                 |                | MIN  | MAX | MIN        | MAX | MIN        | MAX  |    |
| t <sub>PLH</sub> | A               | Y              | 4  | 17  | 2          | 12  | 4          | 14   | ns |
|                  |                 |                | 2  | 14  | 2          | 9   | 2          | 10   |    |
| t <sub>PHL</sub> | OE              | Y              | 5  | 18  | 5          | 15  | 5          | 15   | ns |
|                  |                 |                | 8  | 28  | 8          | 20  | 8          | 20   |    |
| t <sub>PZH</sub> | OE              | Y              | 1  | 12  | 1          | 10  | 1          | 10   | ns |
|                  |                 |                | 2  | 14  | 2          | 12  | 2          | 12   |    |
| t <sub>PZL</sub> |                 |                |  |     |            |     |            |      |    |

<sup>¶</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

PARAMETER MEASUREMENT INFORMATION  
SERIES 54ALS/74ALS AND 54AS/74AS DEVICES




Figure 1. Load Circuits and Voltage Waveforms

**PACKAGING INFORMATION**

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)            |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------|
| 5962-8960201RA        | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8960201RA<br>SNJ54ALS541J |
| SN54ALS541J           | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54ALS541J                    |
| SN54ALS541J.A         | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | SN54ALS541J                    |
| SN74ALS540-1N         | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS540-1N                  |
| SN74ALS540-1N.A       | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS540-1N                  |
| SN74ALS540-1NSR       | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540-1                       |
| SN74ALS540-1NSR.A     | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540-1                       |
| SN74ALS540DW          | Obsolete      | Production           | SOIC (DW)   20 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | ALS540                         |
| SN74ALS540DWR         | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540                         |
| SN74ALS540DWR.A       | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540                         |
| SN74ALS540N           | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS540N                    |
| SN74ALS540N.A         | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS540N                    |
| SN74ALS540NSR         | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540                         |
| SN74ALS540NSR.A       | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS540                         |
| SN74ALS541-1DW        | Active        | Production           | SOIC (DW)   20 | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541-1                       |
| SN74ALS541-1DW.A      | Active        | Production           | SOIC (DW)   20 | 25   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541-1                       |
| SN74ALS541-1N         | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS541-1N                  |
| SN74ALS541-1N.A       | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS541-1N                  |
| SN74ALS541-1NE4       | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS541-1N                  |
| SN74ALS541-1NSR       | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541-1                       |
| SN74ALS541-1NSR.A     | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541-1                       |
| SN74ALS541DBR         | Active        | Production           | SSOP (DB)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | G541                           |
| SN74ALS541DBR.A       | Active        | Production           | SSOP (DB)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | G541                           |
| SN74ALS541DW          | Obsolete      | Production           | SOIC (DW)   20 | -                     | -           | Call TI                              | Call TI                           | 0 to 70      | ALS541                         |
| SN74ALS541DWR         | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541                         |
| SN74ALS541DWR.A       | Active        | Production           | SOIC (DW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541                         |
| SN74ALS541N           | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS541N                    |
| SN74ALS541N.A         | Active        | Production           | PDIP (N)   20  | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | 0 to 70      | SN74ALS541N                    |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)            |
|-------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------|
| <a href="#">SN74ALS541NSR</a> | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541                         |
| SN74ALS541NSR.A               | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541                         |
| SN74ALS541NSRE4               | Active        | Production           | SOP (NS)   20  | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | 0 to 70      | ALS541                         |
| <a href="#">SNJ54ALS541J</a>  | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8960201RA<br>SNJ54ALS541J |
| SNJ54ALS541J.A                | Active        | Production           | CDIP (J)   20  | 20   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 5962-8960201RA<br>SNJ54ALS541J |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF SN54ALS541, SN74ALS541 :**


---

- Catalog : [SN74ALS541](#)


- Military : [SN54ALS541](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

**TAPE AND REEL INFORMATION**


|    |   |
|----|---|
| A0 | Dimension designed to accommodate the component width     |
| B0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74ALS540-1NSR | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74ALS540DWR   | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74ALS540NSR   | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74ALS541-1NSR | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |
| SN74ALS541DBR   | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN74ALS541DWR   | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN74ALS541NSR   | SOP          | NS              | 20   | 2000 | 330.0              | 24.4               | 8.4     | 13.0    | 2.5     | 12.0    | 24.0   | Q1            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74ALS540-1NSR | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALS540DWR   | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALS540NSR   | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALS541-1NSR | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALS541DBR   | SSOP         | DB              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| SN74ALS541DWR   | SOIC         | DW              | 20   | 2000 | 356.0       | 356.0      | 45.0        |
| SN74ALS541NSR   | SOP          | NS              | 20   | 2000 | 356.0       | 356.0      | 45.0        |

**TUBE**


\*All dimensions are nominal

| Device           | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| SN74ALS540-1N    | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS540-1N.A  | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS540N      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS540N.A    | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS541-1DW   | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74ALS541-1DW.A | DW           | SOIC         | 20   | 25  | 507    | 12.83  | 5080   | 6.6    |
| SN74ALS541-1N    | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS541-1N.A  | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS541-1NE4  | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS541N      | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| SN74ALS541N.A    | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).  
 B. This drawing is subject to change without notice.

△ Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).

△ The 20 pin end lead shoulder width is a vendor option, either half or full width.


# PACKAGE OUTLINE

DW0020A



SOIC - 2.65 mm max height

SOIC



## NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

# EXAMPLE BOARD LAYOUT


DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE  
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.


# PACKAGE OUTLINE

DB0020A



SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

# EXAMPLE BOARD LAYOUT


DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4214851/B 08/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

DB0020A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4214851/B 08/2019

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## MECHANICAL DATA

NS (R-PDSO-G\*\*)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



4040062/C 03/03

NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

J (R-GDIP-T\*\*)

14 LEADS SHOWN

CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

NOTES: A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.  
C. This package is hermetically sealed with a ceramic lid using glass frit.  
D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.  
E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025