

SN74AVC2T244 2 位单向电压电平转换器

1 特性


- 0.9V 至 3.6V 的宽运行 VCC 范围
- 低静态功耗，最大 ICC 为 6 μ A
- 输出使能特性使得用户能够禁用输出以降低功耗
- 电压为 3.0V 时，输出驱动电流为 ± 24 mA
- Ioff 支持局部断电模式运行
- 输入滞后可实现输入转换和输入上更好的开关噪声抗扰度
- 最大数据速率
 - 380Mbps (1.8V 至 3.3V 转换)
 - 200Mbps (低于 1.8V 至 3.3V 转换)
 - 200Mbps (转换至 2.5V 或 1.8V)
 - 150Mbps (转换至 1.5V)
 - 100Mbps (转换至 1.2V)
- 闩锁性能超过 100mA，符合 JESD 78 II 类规范的要求
- ESD 保护性能超过 JESD 22 规范要求
 - 5000V 人体放电模式 (A114-A)

2 应用

- 手机、智能手机、平板电脑、服务器

3 说明

这个 2 位单向转换器使用两个独立的可配置电源轨。A 端口设计用于跟踪 V_{CCA}。V_{CCA} 可支持从 0.9V 到 3.6V 范围内的任意电源电压。B 端口设计用于跟踪 V_{CCB}。V_{CCB} 支持从 0.9V 至 3.6V 范围内的任意电源电压，因此可实现 0.9V、1.2V、1.5V、1.8V、2.5V 和 3.6V 电压节点之间的低压转换。对于 SN74AVC2T244，当输出使能端 (OE) 输入为高电平时，所有输出均置于高阻抗状态。SN74AVC2T244 设计成 OE 输入电路以 V_{CCA} 为基准。该器件完全适合使用 Ioff 的局部断电应用。Ioff 电路禁用输出，从而可防止其断电时破坏性电流从该器件回流。



DQE 和 DQM 封装 8 引脚 X2SON (俯视图)



Table of Contents

1 特性	1	6.4 AC Electrical Characteristics.....	6
2 应用	1	7 Device and Documentation Support	7
3 说明	1	7.1 接收文档更新通知.....	7
4 Revision History	2	7.2 支持资源.....	7
5 Pin Configuration and Functions	3	7.3 Trademarks.....	7
6 Specifications	4	7.4 静电放电警告.....	7
6.1 Absolute Maximum Ratings.....	4	7.5 术语表.....	7
6.2 Recommended Operating Conditions.....	4	8 Mechanical, Packaging, and Orderable Information	7
6.3 Electrical Characteristics.....	5		

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision B (September 2011) to Revision C (March 2021)	Page
• 更新了整个文档的表、图和交叉参考的编号格式.....	1
• 更新了数据表标题.....	1
• 删除了订购信息表，请参阅数据表末尾的 POA.....	1

5 Pin Configuration and Functions




图 5-1. DQE and DQM Packages 8 Pin X2SON (Top View)

表 5-1. Pin Functions

PIN	FUNCTION
VCCA	Input Port DC Power Supply
VCCB	Output Port DC Power Supply
GND	Ground
An	Input Port
Bn	Output Port
OE	Output Enable

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

		MIN	MAX	UNIT
Voltage	DC Supply voltage, V_{CCA} V_{CCB}	- 0.5	4.6	V
	DC Input voltage, V_I	A_n - 0.5	4.6	V
	Control Input, V_C	\overline{OE} - 0.5	4.6	V
	DC Output voltage, V_O , $V_{CCA} = V_{CCB} = 0$ (Power Down)	B_n - 0.5	4.6	V
	(Active Mode)	B_n - 0.5	4.6	
3-State Mode	B_n - 0.5	4.6		
DC Input Diode current, I_{IK}	$V_I < GND$		- 20	mA
DC Output Diode current, I_{OK}	$V_O < GND$		- 50	mA
DC Output Source/Sink current, I_O			± 50	mA
DC Supply current per supply pin, I_{CCA} , I_{CCB}			± 100	mA
I_{GND}	DC Ground current per ground pin		± 100	mA
T_{stg}	Storage temperature range	- 65	150	$^{\circ}C$

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 Recommended Operating Conditions

		MIN	MAX	UNIT	
V_{CCA} , V_{CCB}	Positive DC Supply voltage	0.9	3.6	V	
V_I	Bus input voltage	GND	3.6	V	
V_I	Input voltage	GND	3.6	V	
V_C	Control input	\overline{OE} GND	3.6	V	
V_O	Bus output voltage	(Power Down Mode) B_n	GND	3.6	V
		(Active Mode) B_n	GND	V_{CCB}	V
		3-State Mode B_n	GND	3.6	V
T_A	Operating free-air temperature	- 40	85	$^{\circ}C$	
$\Delta t / \Delta v$	Input transition rise or fall rate V_I from 30% to 70% of V_{CC} ; $V_{CC} = 3.3 V \pm 0.3 V$	0	10	nS	

6.3 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER ^{(1) (2)}		TEST CONDITIONS	V _{CCA} (V)	V _{CCB} (V)	- 40°C to 85°C		UNIT
					MIN	MAX	
V _{IH}	Input HIGH Voltage (An, \overline{OE})		2.7 - 3.6	0.9 - 3.6	2.0	-	V
			2.3 - 2.7		1.6	-	
			1.4 - 2.3		0.65 × V _{CCA}	-	
			0.9 - 1.4		0.9 × V _{CCA}	-	
V _{IL}	Input LOW voltage (An, \overline{OE})		2.7 - 3.6	0.9 - 3.6	-	0.8	V
			2.3 - 2.7		-	0.7	
			1.4 - 2.3		-	0.35 × V _{CCA}	
			0.9 - 1.5		-	0.1 × V _{CCA}	
V _{OH}	Output HIGH voltage	I _{OH} = - 100 μA; V _I = V _H	0.9 - 3.6	0.9 - 3.6	V _{CCB} - 0.2	-	V
		I _{OH} = - 0.5 mA; V _I = V _H	0.9	0.9	0.75 × V _{CCB}	-	
		I _{OH} = - 2 mA; V _I = V _H	1.4	1.4	1.05	-	
		I _{OH} = - 6 mA; V _I = V _H	1.65	1.65	1.25	-	
			2.3	2.3	2.0	-	
		I _{OH} = - 12 mA; V _I = V _H	2.3	2.3	1.8	-	
			2.7	2.7	2.2	-	
		I _{OH} = - 18 mA; V _I = V _H	2.3	2.3	1.7	-	
	3.0	3.0	2.4	-			
	I _{OH} = - 24 mA; V _I = V _H	3.0	3.0	2.2	-		
V _{OL}	Output LOW voltage	I _{OH} = 100 μA; V _I = V _H	0.9 - 3.6	0.9 - 3.6	-	0.2	V
		I _{OH} = 0.5 mA; V _I = V _H	1.1	1.1	-	0.3	
		I _{OH} = 2 mA; V _I = V _H	1.4	1.4	-	0.35	
		I _{OH} = 6 mA; V _I = V _H	1.65	1.65	-	0.3	
			2.3	2.3	-	0.4	
		I _{OH} = 12 mA; V _I = V _H	2.7	2.7	-	0.4	
			2.3	2.3	-	0.6	
			3.0	3.0	-	0.4	
	I _{OH} = 24 mA; V _I = V _H	3.0	3.0	-	0.55		
I _I	Input Leakage Current	V _I = V _{CCA} or GND	0.9 - 3.6	0.9 - 3.6	- 1.0	1.5	μ A
I _{OFF}	Power-Off Leakage Current	OE = 0V	0	0.9 - 3.6	- 1.0	1.3	μ A
			0.9 - 3.6	0	- 1.0	1.5	
I _{CCA}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 - 3.6	0.9 - 3.6	-	3.0	μ A
I _{CCB}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 - 3.6	0.9 - 3.6	-	3.0	μ A
I _{CCA} + I _{CCB}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 - 3.6	0.9 - 3.6	-	6.0	μ A
Δ I _{CCA}	Increase in I _{CC} per Input Voltage, Other inputs at V _{CCA} or GND	V _I = V _{CCA} - 0.3 V; V _I = V _{CCA} or GND	3.6	3.6	-	5.0	μ A

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER ^{(1) (2)}		TEST CONDITIONS	V _{CCA} (V)	V _{CCB} (V)	- 40°C to 85°C		UNIT
					MIN	MAX	
ΔI_{CCB}	Increase in I _{CC} per Input Voltage, Other inputs at V _{CCA} or GND	V _I = V _{CCA} - 0.3 V; V _I = V _{CCA} or GND	3.6	3.6	-	5.0	μA
I _{oZ}	I/O Tri-State Output Leakage Current	TA = 25°C, $\overline{OE} = 0$ V	0.9 - 3.6	0.9 - 3.6	- 1.0	1.0	μA

(1) V_{CCO} is the V_{CC} associated with the output port.

(2) V_{CCI} is the V_{CC} associated with the input port.

6.4 AC Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER		V _{CCA} (V)	V _{CCB} (V)	MIN	MAX	UNIT
t _{PLH} , t _{PHL}	Propagation Delay, A _n to B _n	0.9 - 3.6	0.9 - 3.6		20	nS
		1.2 - 3.6	1.2 - 3.6		7	
		1.8 - 3.6	1.8 - 3.6		3.5	
t _{PZH} , t _{PZL}	Output Enable, \overline{OE} to B _n	0.9 - 3.6	0.9 - 3.6		23	nS
		1.2 - 3.6	1.2 - 3.6		6.5	
		1.8 - 3.6	1.8 - 3.6		4.1	
t _{PHZ} , t _{PLZ}	Output Disable, \overline{OE} to B _n	0.9 - 3.6	0.9 - 3.6		17	nS
		1.2 - 3.6	1.2 - 3.6		7	
		1.8 - 3.6	1.8 - 3.6		4.3	
t _{OSHL} , t _{OSLH}	Output to Output Skew, Time	0.9 - 3.6	0.9 - 3.6		0.15	nS
		1.2 - 3.6	1.2 - 3.6		0.15	
		1.8 - 3.6	1.8 - 3.6		0.15	

表 6-1. Capacitance

(2)	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT
C _{IN}	Control Pin Input Capacitance	V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B}	3.5	pF
C _{I/O}	I/O Pin Input capacitance	V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B}	5.0	pF
C _{PD}	Power Dissipation Capacitance	V _{CCA} = V _{CCB} = 3.3 V, V _I = 0 V or V _{CCA/B} , f = 10 MHz	33	pF

(1) Typical values are at TA = +25°C.

(2) C_{PD} is defined as the value of the IC's equivalent capacitance from which the operating current can be calculated from: I_{CC(operating)} ≈ C_{PD} × V_{CC} × f_{IN} × N_{SW} where I_{CC} = I_{CCA} + I_{CCB} and N_{SW} = total number of outputs switching.

7 Device and Documentation Support

7.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [订阅更新](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

7.2 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《[使用条款](#)》。

7.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

7.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

7.5 术语表

TI 术语表 本术语表列出并解释了术语、首字母缩略词和定义。

8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
SN74AVC2T244DQER	ACTIVE	X2SON	DQE	8	5000	RoHS & Green	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA	Samples
SN74AVC2T244DQMR	ACTIVE	X2SON	DQM	8	3000	RoHS & Green	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AVC2T244DQER	X2SON	DQE	8	5000	180.0	8.4	1.2	1.6	0.55	4.0	8.0	Q1
SN74AVC2T244DQMR	X2SON	DQM	8	3000	180.0	8.4	1.57	2.21	0.59	4.0	8.0	Q1


TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AVC2T244DQER	X2SON	DQE	8	5000	202.0	201.0	28.0
SN74AVC2T244DQMR	X2SON	DQM	8	3000	202.0	201.0	28.0

DQM (R-PX2SON-N8)



PLASTIC SMALL OUTLINE NO-LEAD



- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. SON (Small Outline No-Lead) package configuration.



- NOTES:
- All linear dimensions are in millimeters.
 - This drawing is subject to change without notice.
 - Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
 - Customers should contact their board fabrication site for recommended solder mask tolerances.



4225204/A 08/2019

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package complies to JEDEC MO-287 variation X2EAF.

EXAMPLE BOARD LAYOUT


DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 40X



SOLDER MASK DETAILS

4225204/A 08/2019

NOTES: (continued)


- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

EXAMPLE STENCIL DESIGN

DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.075 MM THICK STENCIL
SCALE: 40X

4225204/A 08/2019

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要声明和免责声明

TI 提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保或其他要求。这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 TI 的销售条款 (<https://www.ti.com.cn/zh-cn/legal/termsofsale.html>) 或 [ti.com.cn](https://www.ti.com.cn) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

邮寄地址：上海市浦东新区世纪大道 1568 号中建大厦 32 楼，邮政编码：200122

Copyright © 2021 德州仪器半导体技术（上海）有限公司