

SN55HVD233-SP 3.3V放射線耐性強化CANトランシーバ

1 特長

- QMLV (QML Class V)放射線耐性保証(RHA) MIL-PRF 38535認定済み、SMD 5962L1420901VXC
 - 単一イベント・ラッチアップ(SEL)耐性: 125°Cで86MeV-cm²/mgまで
 - 低線量率における総照射線量(TID)耐性: 50kRad (Si)
 - 軍用温度範囲(-55°C~125°C)全体で認定済み
 - 高性能8ピン・セラミック・フラット・パック(HKX)
- ISO 11898-2準拠
- バス・ピンのフォルト保護: ±16V超
- バス・ピンのESD保護: ±16kV超、HBM
- データレート: 最大1Mbps
- 広い同相電圧範囲: -7V~12V
- 高い入力インピーダンスにより120ノードが可能
- LVTTTL I/Oは5V許容
- ドライバ出力電圧の遷移時間制御による信号品質の向上
- 電力オフのノードはバスに不干涉
- 低電流のスタンバイ・モード: 200μA (標準値)
- 診断用ループバック機能
- サーマル・シャットダウン保護機能
- グリッチ・フリーのバス入力および出力による電源オンおよびオフ
 - 高い入力インピーダンスと低いV_{CC}
 - 電源サイクル中のモノシック出力

2 アプリケーション

- 航空宇宙用バックプレーン・データ・バス通信/制御
- CANopen、DeviceNet、CAN Kingdom、ISO 11783、NMEA 2000、SAE J1939などのCANバス規格

3 概要

SN55HVD233-SPは、ISO 11898規格に準拠したコントローラ・エリア・ネットワーク(CAN)シリアル通信物理層を採用する航空宇宙アプリケーションに適しています。このCANトランシーバは、最大1Mbpsの信号速度で、差動CANバスとCANコントローラの間での送受信を実行する機能を備えています。

SN55HVD233-SPは、特に厳しい放射線環境向けに設計されているため、±16Vまでのクロスワイヤ保護、過電圧保護、および接地損失保護といった機能のほか、過熱(サーマル・シャットダウン)保護機能も搭載しています。また、-7V~12Vの広い同相電圧範囲で動作します。このトランシーバは、マイクロプロセッサ、FPGA、またはASIC上のHOST CANコントローラと、衛星アプリケーションで使用される差動CANバスとの間のインターフェイスになります。


製品情報(1)

型番	グレード	パッケージ
5962L1420901VXC	QMLV RHA [50kRad]	8リードCFP [HKX] 6.48mm×6.48mm
HVD233HKX/EM ⁽²⁾	エンジニアリング・サンプル	8リードCFP [HKX] 6.48mm×6.48mm
SN55HVD233EVM-CVAL	セラミック評価ボード	

(1) 利用可能なすべてのパッケージについては、このデータシートの末尾にある注文情報を参照してください。

(2) これらのユニットは、技術的な評価のみを目的としています。標準とは異なるフローに従って処理されています。これらのユニットは、認定、量産、放射線テスト、航空での使用には適していません。これらの部品は、MILに規定されている温度範囲-55°C~125°C、または動作寿命全体にわたる性能を保証されていません。

概略回路図



Copyright © 2017, Texas Instruments Incorporated



目次

1	特長	1	9	Detailed Description	15
2	アプリケーション	1	9.1	Overview	15
3	概要	1	9.2	Functional Block Diagram	15
4	改訂履歴	2	9.3	Feature Description	15
5	概要 (続き)	3	9.4	Device Functional Modes	19
6	Pin Configuration and Functions	3	10	Application and Implementation	20
7	Specifications	4	10.1	Application Information	20
7.1	Absolute Maximum Ratings	4	10.2	Typical Application	22
7.2	ESD Ratings	4	11	Power Supply Recommendations	24
7.3	Recommended Operating Conditions	4	12	Layout	24
7.4	Thermal Information	5	12.1	Layout Guidelines	24
7.5	Driver Electrical Characteristics	6	12.2	Layout Example	26
7.6	Receiver Electrical Characteristics	6	13	デバイスおよびドキュメントのサポート	27
7.7	Driver Switching Characteristics	7	13.1	ドキュメントの更新通知を受け取る方法	27
7.8	Receiver Switching Characteristics	8	13.2	コミュニティ・リソース	27
7.9	Device Switching Characteristics	8	13.3	商標	27
7.10	Typical Characteristics	9	13.4	静電気放電に関する注意事項	27
8	Parameter Measurement Information	11	13.5	Glossary	27
			14	メカニカル、パッケージ、および注文情報	27

4 改訂履歴

2017年9月発行のものから更新

Page

•	製品ステータスを「事前情報」から「量産データ」に変更	1
---	----------------------------------	---

5 概要 (続き)


モード: SN55HVD233-SPの R_S (ピン8)を使用して、高速、勾配制御、および低消費電力スタンバイ・モードの3つの動作モードを選択できます。ピン8を直接グランドに接続して高速モードの動作を選択すると、立ち上がり/立ち下がり勾配の制限なしに、ドライバ出力トランジスタが可能な限り高速にオン/オフのスイッチングを実行できます。立ち上がり/立ち下がり勾配はピンの出力電流に比例するため、この勾配はピン8とグランドの間に抵抗を接続することにより調整できます。抵抗値 0Ω で勾配制御を実装した場合、シングルエンド・スルーレートは約 $38V/\mu s$ となり、抵抗値 $50k\Omega$ であればスルーレートは約 $4V/\mu s$ となります。勾配制御の詳細については、[アプリケーションと実装](#)セクションを参照してください。

SN55HVD233-SPは、ピン8にHIGHレベルが印加されると、低電流のスタンバイ(リッスンのみ)モードへ移行し、このモードでは、ドライバのスイッチがオフになり、レシーバはアクティブのまま保持されます。ローカル・プロトコル・コントローラがバスへメッセージを送信する必要がある場合は、この低電流スタンバイ・モードを元に戻す必要があります。ループバック・モードの詳細については、[アプリケーション情報](#)セクションを参照してください。

ループバック: SN55HVD233-SPのループバックLBKピン5がHIGHになると、バス出力とバス入力が高インピーダンス状態になります。残りの回路はアクティブに維持され、ドライバからレシーバへのループバックに利用可能なため、バスに干渉することなく自己診断ノード機能に使用できます。

CANバスの状態: デバイスの通電動作中、CANバスにはドミナントとリセッシブという2つの状態があります。ドミナント・バス状態とは、バスが差動で駆動される場合をいい、DおよびRピンがLOWになります。リセッシブ・バス状態とは、バスが $V_{CC}/2$ に、レシーバの高抵抗の内部入力抵抗 R_{IN} によりバイアスされる場合をいい、DおよびRピンがHIGHになります([バスの状態\(物理的ビット表現\)](#)および[リセッシブ同相バイアスとレシーバの概略図](#)を参照)。

6 Pin Configuration and Functions



Pin Functions

PIN		TYPE	DESCRIPTION
NAME	NO.		
D	1	I	CAN transmit data input (LOW for dominant and HIGH for recessive bus states), also called TXD, driver input.
GND	2	GND	Ground connection.
V_{CC}	3	Supply	Transceiver 3.3-V supply voltage.
R	4	O	CAN receive data output (LOW for dominant and HIGH for recessive bus states), also called RXD, receiver output.
LBK	5	I	Loopback mode input pin.
CANL	6	I/O	Low-level CAN bus line.
CANH	7	I/O	High-level CAN bus line.
RS	8	I	Mode select pin: Tie to GND = high-speed mode, Strong pullup to V_{CC} = low power mode, 0Ω to $50\text{-}k\Omega$ pulldown to GND = slope control mode.

7 Specifications

7.1 Absolute Maximum Ratings

over operating junction temperature unless otherwise noted⁽¹⁾⁽²⁾

		MIN	MAX	UNIT
V _{CC}	Supply voltage	-0.3	7	V
	Voltage at any bus pin (CANH or CANL)	-16	16	V
	Voltage input, transient pulse, CANH and CANL, through 100 Ω (see Figure 18)	-100	100	V
V _I	Input voltage, (D, RS, LBK)	-0.5	7	V
V _O	Output voltage, (R)	-0.5	7	V
I _O	Receiver output current	-10	10	mA
T _J	Operating junction temperature		150	°C
T _{stg}	Storage temperature	-65	150	°C

- Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- All voltage values, except differential I/O bus voltages, are with respect to network ground pin.

7.2 ESD Ratings

			VALUE	UNIT	
V _(ESD)	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	CANH, CANL, and GND	±14000	V
			Other pins	±4000	
		Charged-device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾		±500	

- JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

			MIN	NOM	MAX	UNIT
V _{CC}	Supply voltage		3		3.6	V
	Voltage at any bus pin (separately or common mode)		-7		12	V
V _{IH}	High-level input voltage	D, LBK	2		5.5	V
V _{IL}	Low-level input voltage	D, LBK	0		0.8	V
V _{ID}	Differential input voltage		-6		6	V
	Resistance from RS to ground for slope control		0		50	kΩ
V _{I(RS)}	Input voltage at RS for standby		0.75 V _{CC}		5.5	V
I _{OH}	High-level output current	Driver	-50			mA
		Receiver	-10			
I _{OL}	Low-level output current	Driver			50	mA
		Receiver			10	
T _J	Operating junction temperature ⁽¹⁾		-55		125	°C

- Maximum junction temperature operation is allowed as long as the device maximum junction temperature is not exceeded.

7.4 Thermal Information

THERMAL METRIC ⁽¹⁾⁽²⁾		SN55HVD233-SP	
		HKX (CFP)	
		8 PINS	
			UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	97.1	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	21.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	79.1	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	13.7	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	73.6	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	7.0	°C/W

- (1) All values except $R_{\theta JC}$ were taken on a JEDEC-51 standard High-K PCB using a nominal lead form. Differences in lead form, component density, or PCB design can affect these values.
- (2) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

7.5 Driver Electrical Characteristics

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER		TEST CONDITIONS		SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
$V_{O(D)}$	Bus output voltage (dominant)	CANH	$V_{(D)} = 0\text{ V}$, $V_{(RS)} = 0\text{ V}$, see Figure 12 and Figure 13	[1, 2, 3]	2.4		V_{CC}	V
		CANL		[1, 2, 3]	0.5	1.25		
V_O	Bus output voltage (recessive)	CANH	$V_{(D)} = 3\text{ V}$, $V_{(RS)} = 0\text{ V}$, see Figure 12 and Figure 13			2.3		V
		CANL				2.3		
$V_{OD(D)}$	Differential output voltage (dominant)		$V_{(D)} = 0\text{ V}$, $V_{(RS)} = 0\text{ V}$, see Figure 12 and Figure 13	L [1, 2, 3]	1.5	2	3	V
					1.4			
V_{OD}	Differential output voltage (recessive)		$V_{(D)} = 0\text{ V}$, $V_{(RS)} = 0\text{ V}$, see Figure 13 and Figure 14	[1, 2, 3]	1.2	2	3	V
				$V_{(D)} = 3\text{ V}$, $V_{(RS)} = 0\text{ V}$, see Figure 12 and Figure 13	[1, 2, 3]	-120		
V_{OD}	Differential output voltage (recessive)		$V_{(D)} = 3\text{ V}$, $V_{(RS)} = 0\text{ V}$, no load	[1, 2, 3]	-0.5		0.05	V
				See Figure 20			1	V
I_{IH}	High-level input current	D, LBK	$V_{(D)} = 2\text{ V}$	[1, 2, 3]	-30		30	μA
I_{IL}	Low-level input current	D, LBK	$V_{(D)} = 0.8\text{ V}$	[1, 2, 3]	-30		30	μA
I_{OS}	Short-circuit output current		$V_{(CANH)} = -7\text{ V}$, CANL open, see Figure 23	[1, 2, 3]	-250			mA
			$V_{(CANH)} = 12\text{ V}$, CANL open, see Figure 23	[1, 2, 3]			1	
			$V_{(CANL)} = -7\text{ V}$, CANH open, see Figure 23	[1, 2, 3]	-1			
			$V_{(CANL)} = 12\text{ V}$, CANH open, see Figure 23	[1, 2, 3]			250	
C_O	Output capacitance		See receiver input capacitance					
$I_{IRS(s)}$	RS input current for standby		$V_{(RS)} = 0.75 V_{CC}$	[1, 2, 3]	-10			μA
I_{CC}	Supply current	Standby	$V_{(RS)} = V_{CC}$, $V_{(D)} = V_{CC}$, $V_{(LBK)} = 0\text{ V}$	[1, 2, 3]		200	600	μA
		Dominant	$V_{(D)} = 0\text{ V}$, no load, $V_{(LBK)} = 0\text{ V}$, $RS = 0\text{ V}$	[1, 2, 3]			6	mA
		Recessive	$V_{(D)} = V_{CC}$, no load, $V_{(LBK)} = 0\text{ V}$, $V_{(RS)} = 0\text{ V}$	[1, 2, 3]			6	

(1) For subgroup definitions, please see [Table 1](#).

(2) All typical values are at 25°C and with a 3.3-V supply.

7.6 Receiver Electrical Characteristics

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER		TEST CONDITIONS		SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
V_{IT+}	Positive-going input threshold voltage		$V_{(LBK)} = 0\text{ V}$, see Table 2	[1, 2, 3]		750	900	mV
V_{IT-}	Negative-going input threshold voltage			[1, 2, 3]	500	650		mV
V_{hys}	Hysteresis voltage ($V_{IT+} - V_{IT-}$)					100		mV
V_{OH}	High-level output voltage		$I_O = -4\text{ mA}$, see Figure 17	[1, 2, 3]	2.4			V
V_{OL}	Low-level output voltage		$I_O = 4\text{ mA}$, see Figure 17	[1, 2, 3]			0.4	V

(1) For subgroup definitions, please see [Table 1](#).

(2) All typical values are at 25°C and with a 3.3-V supply.

Receiver Electrical Characteristics (continued)

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER		TEST CONDITIONS	SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
I_I	Bus input current	$V_{(\text{CANH})}$ or $V_{(\text{CANL})} = 12\text{ V}$	[1, 2, 3]	150		500	μA
		$V_{(\text{CANH})}$ or $V_{(\text{CANL})} = 12\text{ V}$, $V_{\text{CC}} = 0\text{ V}$	Other bus pin = 0 V, $V_{(\text{D})} = 3\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$, $V_{(\text{RS})} = 0\text{ V}$	[1, 2, 3]	150	600	
		CANH or CANL = -7 V		[1, 2, 3]	-610	-100	
		CANH or CANL = -7 V , $V_{\text{CC}} = 0\text{ V}$		[1, 2, 3]	-450	-100	
C_I	Input capacitance (CANH or CANL)	Pin-to-ground, $V_I = 0.4 \sin(4E6\pi t) + 0.5\text{ V}$, $V_{(\text{D})} = 3\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$			40	pF	
C_{ID}	Differential input capacitance	Pin-to-pin, $V_I = 0.4 \sin(4E6\pi t) + 0.5\text{ V}$, $V_{(\text{D})} = 3\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$			20	pF	
R_{ID}	Differential input resistance		[4, 5, 6]	40		105	$\text{k}\Omega$
R_{IN}	Input resistance (CANH or CANL)	$V_{(\text{D})} = 3\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$	[4, 5, 6]	20		55	$\text{k}\Omega$
I_{CC}	Supply current	Standby	$V_{(\text{RS})} = V_{\text{CC}}$, $V_{(\text{D})} = V_{\text{CC}}$, $V_{(\text{LBK})} = 0\text{ V}$	[1, 2, 3]	200	600	μA
		Dominant	$V_{(\text{D})} = 0\text{ V}$, no load, $V_{(\text{RS})} = 0\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$	[1, 2, 3]		6	mA
		Recessive	$V_{(\text{D})} = V_{\text{CC}}$, no load, $V_{(\text{RS})} = 0\text{ V}$, $V_{(\text{LBK})} = 0\text{ V}$	[1, 2, 3]		6	mA

7.7 Driver Switching Characteristics

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER		TEST CONDITIONS	SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
t_{PLH}	Propagation delay time, low-to-high-level output	$V_{(\text{RS})} = 0\text{ V}$, see Figure 15	[9, 10, 11]		35	85	ns
		RS with 10 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]		70	125	
		RS with 50 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]		500	870	
t_{PHL}	Propagation delay time, high-to-low-level output	$V_{(\text{RS})} = 0\text{ V}$, see Figure 15	[9, 10, 11]		70	120	ns
		RS with 10 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]		130	180	
		RS with 50 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]		870	1200	
$t_{\text{sk(p)}}$	Pulse skew ($ t_{\text{PHL}} - t_{\text{PLH}} $)	$V_{(\text{RS})} = 0\text{ V}$, see Figure 15			35		ns
		RS with 10 $\text{k}\Omega$ to ground, see Figure 15			60		
		RS with 50 $\text{k}\Omega$ to ground, see Figure 15			370		
t_r	Differential output signal rise time	$V_{(\text{RS})} = 0\text{ V}$, see Figure 15	[9, 10, 11]	20		70	ns
t_f	Differential output signal fall time		[9, 10, 11]	20		70	ns
t_r	Differential output signal rise time	RS with 10 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]	30		135	ns
t_f	Differential output signal fall time		[9, 10, 11]	30		135	ns
t_r	Differential output signal rise time	RS with 50 $\text{k}\Omega$ to ground, see Figure 15	[9, 10, 11]	350		1400	ns
t_f	Differential output signal fall time		[9, 10, 11]	350		1400	ns
$t_{\text{en(s)}}$	Enable time from standby to dominant	See Figure 19	[9, 10, 11]		0.6	1.5	μs

(1) For subgroup definitions, please see Table 1.

(2) All typical values are at 25°C and with a 3.3-V supply.

7.8 Receiver Switching Characteristics

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER	TEST CONDITIONS	SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
t_{PLH} Propagation delay time, low-to-high-level output	See Figure 17	[9, 10, 11]	35	105		ns
t_{PHL} Propagation delay time, high-to-low-level output		[9, 10, 11]	35	105		ns
$t_{\text{sk(p)}}$ Pulse skew ($t_{\text{PHL}} - t_{\text{PLH}}$)			7			ns
t_{r} Output signal rise time			2			ns
t_{f} Output signal fall time			2			ns

(1) For subgroup definitions, please see Table 1.

(2) All typical values are at 25°C and with a 3.3-V supply.

7.9 Device Switching Characteristics

The specifications shown below are valid across temperature range of -55°C to 125°C pre-radiation and 25°C post-radiation. When different, the post-radiation values are shown in a separate row specified by the corresponding RHA level (L = 50 krad).

PARAMETER	TEST CONDITIONS	SUBGROUP ⁽¹⁾	MIN	TYP ⁽²⁾	MAX	UNIT
$t_{\text{(LBK)}}$ Loopback delay, driver input to receiver output	See Figure 22		7.5			ns
$t_{\text{(loop1)}}$ Total loop delay, driver input to receiver output, recessive to dominant	$V_{\text{(RS)}}$ at 0 V, see Figure 21	[9, 10, 11]	70	150		ns
	$V_{\text{(RS)}}$ with 10 k Ω to ground, see Figure 21	[9, 10, 11]	105	225		
	$V_{\text{(RS)}}$ with 50 k Ω to ground, see Figure 21	[9, 10, 11]	500	600		
$t_{\text{(loop2)}}$ Total loop delay, driver input to receiver output, dominant to recessive	$V_{\text{(RS)}}$ at 0 V, See Figure 21	[9, 10, 11]	70	150		ns
	$V_{\text{(RS)}}$ with 10 k Ω to ground, see Figure 21	[9, 10, 11]	105	225		
	$V_{\text{(RS)}}$ with 50 k Ω to ground, see Figure 21	[9, 10, 11]	500	600		

(1) For subgroup definitions, please see Table 1.

(2) All typical values are at 25°C and with a 3.3-V supply.

Table 1. Quality Conformance Inspection⁽¹⁾

SUBGROUP	DESCRIPTION	TEMPERATURE ($^{\circ}\text{C}$)
1	Static tests at	25
2	Static tests at	125
3	Static tests at	-55
4	Dynamic tests at	25
5	Dynamic tests at	125
6	Dynamic tests at	-55
7	Functional tests at	25
8A	Functional tests at	125
8B	Functional tests at	-55
9	Switching tests at	25
10	Switching tests at	125
11	Switching tests at	-55

(1) MIL-STD-883, Method 5005 - Group A

7.10 Typical Characteristics




Figure 1. Recessive-To-Dominant Loop Time vs Temperature




Figure 2. Dominant-To-Recessive Loop Time vs Temperature




Figure 3. Supply Current vs Frequency




Figure 4. Driver Low-Level Output Current vs Low-Level Output Voltage




Figure 5. Driver High-Level Output Current vs High-Level Output Voltage




Figure 6. Differential Output Voltage vs Temperature

Typical Characteristics (continued)




Figure 7. Receiver Low-To-High Propagation Delay vs Temperature




Figure 8. Receiver High-To-Low Propagation Delay vs Temperature




Figure 9. Driver Low-To-High Propagation Delay vs Temperature




Figure 10. Driver High-To-Low Propagation Delay vs Temperature




Figure 11. Driver Output Current vs Supply Voltage

8 Parameter Measurement Information




Figure 12. Driver Voltage, Current, and Test Definition




Figure 13. Bus Logic State Voltage Definitions





Figure 14. Driver V_{OD}



- A. The input pulse is supplied by a generator having the following characteristics:
- Pulse repetition rate (PRR) ≤ 125 kHz, 50% duty cycle
 - $t_r \leq 6$ ns
 - $t_f \leq 6$ ns
 - $Z_0 = 50 \Omega$
- B. C_L includes fixture and instrumentation capacitance.

Figure 15. Driver Test Circuit and Voltage Waveforms

Parameter Measurement Information (continued)





Figure 16. Receiver Voltage and Current Definitions




- A. The input pulse is supplied by a generator having the following characteristics:
 - PRR ≤ 125 kHz, 50% duty cycle
 - $t_r \leq 6$ ns
 - $t_f \leq 6$ ns
 - $Z_o = 50 \Omega$
- B. C_L includes fixture and instrumentation capacitance.

Figure 17. Receiver Test Circuit and Voltage Waveforms


Table 2. Differential Input Voltage Threshold Test

INPUT		OUTPUT		MEASURED
V_{CANH}	V_{CANL}	R		$ V_{ID} $
-6.1 V	-7 V	L	V_{OL}	900 mV
12 V	11.1 V	L		900 mV
-1 V	-7 V	L		6 V
12 V	6 V	L		6 V
-6.5 V	-7 V	H	V_{OH}	500 mV
12 V	11.5 V	H		500 mV
-7 V	-1 V	H		6 V
6 V	12 V	H		6 V
Open	Open	H		X



NOTE: This test is conducted to test survivability only. Data stability at the R output is not specified.

Figure 18. Test Circuit, Transient Overvoltage Test




Copyright © 2017, Texas Instruments Incorporated

NOTE: All V_I input pulses are supplied by a generator having the following characteristics:

- t_r or $t_f \leq 6$ ns
- PRR = 125 kHz, 50% duty cycle

Figure 19. $T_{en(s)}$ Test Circuit and Voltage Waveforms



NOTE: All V_I input pulses are supplied by a generator having the following characteristics:

- t_r or $t_f \leq 6$ ns
- PRR = 125 kHz, 50% duty cycle

Figure 20. $V_{OC(pp)}$ Test Circuit and Voltage Waveforms





Figure 21. $T_{(loop)}$ Test Circuit and Voltage Waveforms



Copyright © 2017, Texas Instruments Incorporated

Figure 22. $T_{(LBK)}$ Test Circuit and Voltage Waveforms





Figure 23. I_{OS} Test Circuit and Waveforms



The R Output State Does Not Change During Application of the Input Waveform.

V_{ID}	R1	R2
500 mV	50 Ω	280 Ω
900 mV	50 Ω	130 Ω



NOTE: All input pulses are supplied by a generator with $f \leq 1.5$ MHz.

Figure 24. Common-Mode Voltage Rejection


9 Detailed Description

9.1 Overview

The SN55HVD233-SP is used in applications employing the CAN serial communication physical layer in accordance with the ISO 11898 standard. As a CAN transceiver, the device provides transmit and receive capability between the differential CAN bus and a CAN controller, with signaling rates up to 1 Mbps.

Designed for operation in especially harsh environments, the SN55HVD233-SP features cross-wire, overvoltage, and loss of ground protection to ± 16 V, overtemperature (thermal shutdown) protection, and common-mode transient protection of ± 100 V. This device operates over a wide -7 -V to 12-V common mode range. This transceiver is the interface between the host CAN controller on the microprocessor, FPGA, or ASIC, and the differential CAN bus used in satellite applications.

9.2 Functional Block Diagram



Copyright © 2017, Texas Instruments Incorporated

9.3 Feature Description

9.3.1 Modes

The R_S , pin 8 of the SN55HVD233-SP, provides for three modes of operation: high-speed, slope control, or low-power standby mode. The user selects the high-speed mode of operation by connecting pin 8 directly to ground, allowing the driver output transistors to switch on and off as fast as possible with no limitation on the rise and fall slope. The user can adjust the rise and fall slope by connecting a resistor to ground at pin 8, because the slope is proportional to the pin's output current. Slope control is implemented with a resistor values of 0Ω to achieve a single ended slew rate of approximately $38 \text{ V}/\mu\text{s}$ up to a value of $50 \text{ k}\Omega$ to achieve approximately $4 \text{ V}/\mu\text{s}$ slew rate. For more information about slope control, refer to [Application and Implementation](#).

The SN55HVD233-SP enters a low-current standby (listen-only) mode during which the driver is switched off and the receiver remains active if a high logic level is applied to pin 8. The local protocol controller reverses this low-current standby mode when it needs to transmit to the bus.

Feature Description (continued)

9.3.2 Loopback

A logic high on the loopback LBK pin 5 of the SN55HVD233-SP places the bus output and bus input in a high-impedance state. The remaining circuit remains active and available for driver-to-receiver loopback, self-diagnostic node functions without disturbing the bus. For more information on the loopback mode, refer to the [Application Information](#).

Feature Description (continued)

9.3.3 CAN Bus States

The CAN bus has two states during powered operation of the device: dominant and recessive. A dominant bus state is when the bus is driven differentially, corresponding to a logic low on the D and R pin. A recessive bus state is when the bus is biased to $V_{CC} / 2$ through the high-resistance internal input resistors R_{IN} of the receiver, corresponding to a logic high on the D and R pins (see Figure 25 and Figure 26).




Figure 25. Bus States (Physical Bit Representation)




Figure 26. Simplified Recessive Common Mode Bias and Receiver


9.3.4 ISO 11898 Compliance of SN55HVD233-SP

9.3.4.1 Introduction

Many users value the low-power consumption of operating their CAN transceivers from a 3.3-V supply. However, some users are concerned about the interoperability with 5-V supplied transceivers on the same bus. This report analyzes this situation to address those concerns.

9.3.4.2 Differential Signal

CAN is a differential bus where complementary signals are sent over two wires and the voltage difference between the two wires defines the logical state of the bus. The differential CAN receiver monitors this voltage difference and outputs the bus state with a single-ended output signal.

Feature Description (continued)

Figure 27. Typical SN55HVD233-SP Differential Output Voltage Waveform

The CAN driver creates the difference in voltage between CANH and CANL in the dominant state. The dominant differential output of the SN55HVD233-SP is greater than 1.5 V and less than 3 V across a 60-Ω load. The minimum required by ISO 11898 is 1.5 V and maximum is 3 V. These are the same limiting values for 5-V supplied CAN transceivers. The bus termination resistors drive the recessive bus state and not the CAN driver.

A CAN receiver is required to output a recessive state with less than 500 mV and a dominant state with more than 900 mV difference voltage on its bus inputs. The CAN receiver must do this with common-mode input voltages from –2 V to 7 V. The SN55HVD233-SP receiver meets these same input specifications as 5-V supplied receivers.

9.3.4.2.1 Common-Mode Signal

A common-mode signal is an average voltage of the two signal wires that the differential receiver rejects. The common-mode signal comes from the CAN driver, ground noise, and coupled bus noise. The supply voltage of the CAN transceiver has nothing to do with noise. The SN55HVD233-SP driver lowers the common-mode output in a dominant bit by a couple hundred millivolts from that of most 5-V drivers. While this does not fully comply with ISO 11898, this small variation in the driver common-mode output is rejected by differential receivers and does not effect data, signal noise margins, or error rates.

9.3.4.3 Interoperability of 3.3-V CAN in 5-V CAN Systems

The 3.3-V supplied CAN transceivers are electrically interchangeable with 5-V CAN transceivers. The differential output is the same. The recessive common mode output is the same. The dominant common mode output voltage is a couple hundred millivolts lower than 5 V supplied drivers, while the receivers exhibit identical specifications as 5-V devices.

To help ensure the widest interoperability possible, the SN55HVD233-SP successfully passed the internationally recognized GIFT ICT conformance and interoperability testing for CAN transceivers. Electrical interoperability does not always assure interchangeability, however. Most implementers of CAN buses recognize that ISO 11898 does not sufficiently specify the electrical layer and that strict standard compliance alone does not ensure full interchangeability. Interchangeability is ensured with thorough equipment testing.

Feature Description (continued)

9.3.5 Thermal Shutdown

If the junction temperature of the device exceeds the thermal shutdown threshold, the device turns off the CAN driver circuits thus blocking the D pin to bus transmission path. The shutdown condition is cleared when the junction temperature drops below the thermal shutdown temperature of the device. The CAN bus pins are high-impedance biased to recessive level during a thermal shutdown, and the receiver-to-R pin path remains operational.

9.4 Device Functional Modes

Table 3. Driver I/O

DRIVER ⁽¹⁾					
INPUTS			OUTPUTS		
D	LBK	RS	CANH	CANL	BUS STATE
X	X	$> 0.75 V_{CC}$	Z	Z	Recessive
L	L or open	$\leq 0.33 V_{CC}$	H	L	Dominant
H or open	X		Z	Z	Recessive
X	H	$\leq 0.33 V_{CC}$	Z	Z	Recessive

(1) H = High level; L = Low level; Z = High impedance; X = Irrelevant

Table 4. Receiver I/O

RECEIVER ⁽¹⁾			
INPUTS		OUTPUT	
BUS STATE	$V_{ID} = V_{(CANH)} - V_{(CANL)}$	D	R
Dominant	$V_{ID} \geq 0.9 V$	X	L
Recessive	$V_{ID} \leq 0.5 V$ or open	H or open	H
?	$0.5 V < V_{ID} < 0.9 V$	H or open	?
Dominant	$V_{ID} \geq 0.9 V$	X	L
Recessive	$V_{ID} \leq 0.5 V$ or open	H	H
Recessive	$V_{ID} \leq 0.5 V$ or open	L	L
?	$0.5 V < V_{ID} < 0.9 V$	L	L

(1) H = High level; L = Low level; Z = High impedance; X = Irrelevant; ? = Indeterminate

10 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.


10.1 Application Information

10.1.1 Diagnostic Loopback

The diagnostic loopback or internal loopback function of the SN55HVD233-SP is enabled with a high-level input on pin 7, LBK. This mode disables the driver output while keeping the bus pins biased to the recessive state. This mode also redirects the D data input (transmit data) through logic to the received data output (R), thus creating an internal loopback of the transmit-to-receive data path. This mimics the loopback that occurs normally with a CAN transceiver because the receiver loops back the driven output to the R (receive data) pin. This mode allows the host microprocessor to input and read back a bit sequence or CAN messages to perform diagnostic routines without disturbing the CAN bus. [Figure 33](#) shows a typical CAN bus application.

If the LBK pin is not used, it may be tied to ground (GND). However, it is pulled low internally (defaults to a low-level input) and may be left open if not in use.


Application Information (continued)



Copyright © 2017, Texas Instruments Incorporated

Figure 28. Equivalent Input and Output Schematic Diagrams

10.2 Typical Application



Copyright © 2017, Texas Instruments Incorporated

Figure 29. Typical Application Schematic

10.2.1 Design Requirements

The High-Speed ISO 11898 Standard specifications are given for a maximum signaling rate of 1 Mbps with a bus length of 40 m and a maximum of 30 nodes. It also recommends a maximum unterminated stub length of 0.3 m. The cable is specified to be a shielded or unshielded twisted-pair with a 120-Ω characteristic impedance (ZO). The standard defines a single line of twisted-pair cable with the network topology as shown in Figure 29. It is terminated at both ends with 120-Ω resistors, which match the characteristic impedance of the line to prevent signal reflections. According to ISO 11898, placing RL on a node should be avoided because the bus lines lose termination if the node is disconnected from the bus.

10.2.2 Detailed Design Procedure

Table 5. Suggested Cable Length vs Signaling Rate

BUS LENGTH (m)	SIGNALING RATE (Mbps)
40	1
100	0.5
200	0.25
500	0.1
1000	0.05

Basically, the maximum bus length is determined by, or rather is a trade-off with the selected signaling rate as listed in Table 5.

A signaling rate decreases as transmission distance increases. While steady-state losses may become a factor at the longest transmission distances, the major factors limiting signaling rate as distance is increased are time varying. Cable bandwidth limitations, which degrade the signal transition time and introduce inter-symbol interference (ISI), are primary factors reducing the achievable signaling rate when transmission distance is increased.

For a CAN bus, the signaling rate is also determined from the total system delay – down and back between the two most distant nodes of a system and the sum of the delays into and out of the nodes on a bus with the typical 5 ns/m prop delay of a twisted-pair cable. Also, consideration must be given the signal amplitude loss due to resistance of the cable and the input resistance of the transceivers. Under strict analysis, skin effects, proximity to other circuitry, dielectric loss, and radiation loss effects all act to influence the primary line parameters and degrade the signal.

A conservative rule of thumb for bus lengths over 100 m is derived from the product of the signaling rate in Mbps and the bus length in meters, which should be less than or equal to 50.

Signaling Rate (Mbps) × Bus Length (m) ≤ 50. Operation at extreme temperatures should employ additional conservatism.

10.2.2.1 Slope Control

Adjust the rise and fall slope of the SN55HVD233-SP driver output by connecting a resistor from the RS (pin 8) to ground (GND), or to a low-level input voltage as shown in Figure 30.

The slope of the driver output signal is proportional to the pin's output current. This slope control is implemented with an external resistor value ranging from 0 Ω to achieve a ≈38 V/μs single ended slew rate, and up to 50 kΩ to achieve a ≈4 V/μs slew rate as displayed in Figure 31. Figure 32 shows typical driver output waveforms with slope control.




Figure 30. Slope Control/Standby Connection to a DSP

10.2.2.2 Standby

If a high-level input (> 0.75 V_{CC}) is applied to RS (pin 8), the circuit enters a low-current, listen-only standby mode during which the driver is switched off and the receiver remains active. The local controller can reverse this low-power standby mode when the rising edge of a dominant state (bus differential voltage > 900-mV typical) occurs on the bus.

10.2.3 Application Curves




Figure 31. HVD233 Driver Output Signal Slope vs Slope Control Resistance Value




Figure 32. Typical SN55HVD233-SP 250-Kbps Output Pulse Waveforms With Slope Control

11 Power Supply Recommendations

TI recommends to have localized capacitive decoupling near device VCC pin to GND. Values of 4.7 μF at VCC pin and 10 μF , 1 μF , and 0.1 μF at supply have tested well on evaluation modules.

12 Layout

12.1 Layout Guidelines

Minimize stub length from node insertion to bus.

12.1.1 Bus Loading, Length, and Number of Nodes

The ISO11898 standard specifies up to 1-Mbps data rate, maximum bus length of 40 m, maximum drop line (stub) length of 0.3 m, and a maximum of 30 nodes. However, with careful network design, the system may have longer cables, longer stub lengths, and many more nodes to a bus. Many CAN organizations and standards have scaled the use of CAN for applications outside the original ISO11898 standard. They made system level trade-offs for data rate, cable length, and parasitic loading of the bus. Examples of some of these specifications are ARINC825, CANopen, CAN Kingdom, DeviceNet, and NMEA200.

A high number of nodes requires a transceiver with high input impedance and wide common mode range such as the SN55HVD233-SP CAN. ISO11898-2 specifies the driver differential output with a 60- Ω load (two 120- Ω termination resistors in parallel), and the differential output must be greater than 1.5 V. The SN55HVD233-SP is specified to meet the 1.5-V requirement with a 60- Ω load, and additionally specified with a differential output voltage minimum of 1.2 V across a common mode range of -2 to 7 V through a 330- Ω coupling network. This network represents the bus loading of 120 SN55HVD233-SP transceivers based on their minimum differential input resistance of 40 k Ω . Therefore, the SN55HVD233-SP supports up to 120 transceivers on a single bus segment with margin to the 1.2-V minimum differential input voltage requirement at each node. For CAN network design, margin must be given for signal loss across the system and cabling, parasitic loadings, network imbalances, ground offsets, and signal integrity; thus, a practical maximum number of nodes may be lower. Bus length may also be extended beyond the original ISO11898 standard of 40 m by careful system design and data rate tradeoffs. For example, CANopen network design guidelines allow the network to be up to 1 km with changes in the termination resistance, cabling, less than 64 nodes, and significantly lowered data rate.

This flexibility in CAN network design is one of the key strengths of the various extensions and additional standards that have been built on the original ISO11898 CAN standard. Using this flexibility requires good network design.

12.1.2 CAN Termination

The ISO11898 standard specifies the interconnect to be a twisted pair cable (shielded or unshielded) with 120- Ω characteristic impedance (Z_0). Use resistors equal to the characteristic impedance of the line to terminate both ends of the cable to prevent signal reflections. Keep unterminated drop lines (stubs) connecting nodes to the bus as short as possible to minimize signal reflections. The termination may be on the cable or in a node, but if nodes may be removed from the bus, the termination must be carefully placed so that it is not removed from the bus.

Layout Guidelines (continued)




Figure 33. Typical CAN Bus

Termination is typically a 120-Ω resistor at each end of the bus. If filtering and stabilization of the common mode voltage of the bus is desired, then the user may use split termination (see Figure 34). Split termination uses two 60-Ω resistors with a capacitor in the middle of these resistors to ground. Split termination improves the electromagnetic emissions behavior of the network by eliminating fluctuations in the bus common mode voltages at the start and end of message transmissions.

Take care with the power ratings of the termination resistors used, especially for the worst-case condition (if a system power supply is shorted across the termination resistance to ground). In most cases, under the worst-case condition, much higher current passes through the termination resistance than the CAN transceiver's current limit.




Figure 34. CAN Bus Termination Concepts

12.2 Layout Example




Figure 35. Board Layout Example

13 デバイスおよびドキュメントのサポート

13.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、ti.comのデバイス製品フォルダを開いてください。右上の隅にある「通知を受け取る」をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取れます。変更の詳細については、修正されたドキュメントに含まれている改訂履歴をご覧ください。

13.2 コミュニティ・リソース

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

TI E2E™オンライン・コミュニティ *TIのE2E (Engineer-to-Engineer) コミュニティ*。エンジニア間の共同作業を促進するために開設されたものです。e2e.ti.comでは、他のエンジニアに質問し、知識を共有し、アイデアを検討して、問題解決に役立てることができます。

設計サポート *TIの設計サポート* 役に立つE2Eフォーラムや、設計サポート・ツールをすばやく見つけることができます。技術サポート用の連絡先情報も参照できます。

13.3 商標

E2E is a trademark of Texas Instruments.
All other trademarks are the property of their respective owners.

13.4 静電気放電に関する注意事項



これらのデバイスは、限定的なESD(静電破壊)保護機能を内蔵しています。保存時または取り扱い時は、MOSゲートに対する静電破壊を防止するために、リード線同士をショートさせておくか、デバイスを導電フォームに入れる必要があります。

13.5 Glossary



SLYZ022 — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

14 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、そのデバイスについて利用可能な最新のデータです。このデータは予告なく変更されることがあり、ドキュメントが改訂される場合もあります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
5962L1420901VXC	ACTIVE	CFP	HKX	8	25	RoHS & Green	NIAU	N / A for Pkg Type	-55 to 125	L1420901VXC HVD233-SP	
HVD233HKX/EM	ACTIVE	CFP	HKX	8	25	RoHS & Green	NIAU	N / A for Pkg Type	25 to 25	HVD233HKX/EM EVAL ONLY	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBsolete: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN55HVD233-SP :

- Catalog : [SN55HVD233-SEP](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product

TUBE


*All dimensions are nominal




Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
5962L1420901VXC	HKX	CFP (HSL)	8	25	506.98	26.16	6220	NA
HVD233HKX/EM	HKX	CFP (HSL)	8	25	506.98	26.16	6220	NA

HKX0008A



PACKAGE OUTLINE
CFP - 2.785 mm max height

CERAMIC FLATPACK



4223439/C 08/2021

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a metal lid.
4. The leads are gold plated.

重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス・デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含むいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、または [ti.com](https://www.ti.com) やかかる TI 製品の関連資料などのいずれかを通じて提供する適用可能な条項の下で提供されています。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。

お客様がいかなる追加条項または代替条項を提案した場合でも、TI はそれらに異議を唱え、拒否します。

郵送先住所 : Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated