

SN74LV8T157-EP Enhanced Product, Quadruple 2-Line To 1-Line Data Selectors/ Multiplexers

1 Features

- Wide operating range of 1.65V to 5.5V
- 5.5V tolerant input pins
- Single-supply voltage translator (refer to LVxT Enhanced Input Voltage):
 - Up translation:
 - 1.2V to 1.8V
 - 1.5V to 2.5V
 - 1.8V to 3.3V
 - 3.3V to 5.0V
 - Down translation:
 - 5.0V, 3.3V, 2.5V to 1.8V
 - 5.0V, 3.3V to 2.5V
 - 5.0V to 3.3V
- Up to 150Mbps with 5V or $3.3V V_{CC}$
- Supports standard function pinout
- Latch-up performance exceeds 250mA per JESD 17
- · Supports defense and aerospace applications:
 - Controlled baseline
 - One assembly and test site
 - One fabrication site
 - Extended product life cycle
 - Product traceability

2 Applications

- Enable or disable a digital signal
- Controlling an indicator LED
- Translation between communication modules and system controllers


3 Description

The SN74LV8T157-EP contains four data selectors/ multiplexers to select one of two data sources. All channels are controlled by the same address select (\overline{A}/B) input, and strobe (\overline{G}) input. A high level at the strobe terminal forces all outputs low.

Package Information

	v							
PART NUMBER	PACKAGE ⁽¹⁾	PACKAGE SIZE ⁽²⁾	BODY SIZE ⁽³⁾					
SN74LV8T157-EP	PW (TSSOP, 16)	5mm × 6.4mm	5mm × 4.4mm					

- (1) For more information, see the orderable addendum at the end of the data sheet.
- (2) The package size (length × width) is a nominal value and includes pins, where applicable
- (3) The body size (length × width) is a nominal value and does not include pins.



Logic Diagram (Positive Logic)



Table of Contents

1 Features	1
2 Applications	1
3 Description	1
4 Pin Configuration and Functions	3
5 Specifications	4
5.1 Absolute Maximum Ratings	4
5.2 ESD Ratings	4
5.3 Recommended Operating Conditions	4
5.4 Thermal Information	<mark>5</mark>
5.5 Electrical Characteristics	<mark>5</mark>
5.6 Switching Characteristics	<mark>5</mark>
5.7 Typical Characteristics	7
6 Parameter Measurement Information	
7 Detailed Description	11
7.1 Overview	11
7.2 Functional Block Diagram	11
7.3 Feature Description	

7.4 Device Functional Modes	14
8 Application and Implementation	15
8.1 Application Information	. 15
8.2 Typical Application	
8.3 Power Supply Recommendations	18
8.4 Layout	
9 Device and Documentation Support	
9.1 Documentation Support	. 20
9.2 Receiving Notification of Documentation Updates	20
9.3 Support Resources	20
9.4 Trademarks	
9.5 Electrostatic Discharge Caution	20
9.6 Glossary	
10 Revision History	. 20
11 Mechanical, Packaging, and Orderable	
Information	. 20



4 Pin Configuration and Functions

⊼/в	10	16	
1A 🖂	2	15	G
1B 🗖	3	14	🖵 4A
1Y 🗖	4	13	4B
2A 🖂	5	12	🖵 4Y
2B 🗖	6	11	🗀 ЗА
2Y 🗖	7	10	🗔 3B
GND 🖂	8	9	💷 3Y

Table 4-1. Pin Functions

F	PIN	I/O ⁽¹⁾	DESCRIPTION			
NO.	NAME	- 1/0("/	DESCRIPTION			
1	Ā/B	I	Address select			
2	1A	I	Channel 1, data input A			
3	1B	I	Channel 1, data input B			
4	1Y	I	Channel 1, data output			
5	2A	0	hannel 2, data input A			
6	2B	0	nannel 2, data input B			
7	2Y	I	Channel 2, data output			
8	GND	_	Ground			
9	3Y	I	Channel 3, data output			
10	3B	I	Channel 3, data input B			
11	3A	I	Channel 3, data input A			
12	4Y	I	Channel 4, data output			
13	4B	I	Channel 4, data input B			
14	4A	I	Channel 4, data input A			
15	G	I	Output strobe, active low			
16	V _{CC}	_	Positive supply			



5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

			MIN	MAX	UNIT
V _{CC}	Supply voltage range		-0.5	7	V
VI	Input voltage range ⁽²⁾		-0.5	7	V
Vo	Voltage range applied to any outp	tage range applied to any output in the high-impedance or power-off state ⁽²⁾			
Vo	Output voltage range ⁽²⁾		-0.5	V _{CC} + 0.5	V
I _{IK}	Input clamp current	V _I < -0.5V		-20	mA
I _{OK}	Output clamp current	$V_{\rm O}$ < -0.5V or $V_{\rm O}$ > $V_{\rm CC}$ + 0.5V		±20	mA
I _O	Continuous output current	$V_{O} = 0$ to V_{CC}		±25	mA
	Continuous output current through V _{CC} or GND			±50	mA
T _{stg}	Storage temperature		-65	150	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If briefly operating outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.

(2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

5.2 ESD Ratings

				VALUE	UNIT	
	V	Electrostatic	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	V	
V _(ESD) discharge	Charged-device model (CDM), per ANSI/ESDA/JEDEC JS-002 ⁽²⁾	±1000	v			

(1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

Specification	Description	Condition	MIN	MAX	UNIT	
V _{cc}	Supply voltage		1.8	5.5	V	
VI	Input voltage		0	5.5	V	
Vo	Output voltage		0	V _{CC}	V	
		V _{CC} = 1.65V to 2V	1.1			
	High lovel input veltage	V _{CC} = 2.25V to 2.75V	1.28		V	
	High-level input voltage $V_{CC} = 3V \text{ to } 3.6V$ $V_{CC} = 4.5V \text{ to } 5.5V$ Low-Level input voltage $V_{CC} = 1.65V \text{ to } 2V$ $V_{CC} = 2.25V \text{ to } 2.75V$ $V_{CC} = 3V \text{ to } 3.6V$	V _{CC} = 3V to 3.6V	1.45		V	
		2				
V _I Inpu V _O Outp V _{IH} High V _{IL} Low- I _O Outp I _O Outp Δt/Δv Inpu		V _{CC} = 1.65V to 2V		0.5		
		V _{CC} = 2.25V to 2.75V		0.65	V	
	Low-Level input voltage	V _{CC} = 3V to 3.6V		0.75	v	
		$age \qquad \begin{array}{c} 1.8 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ $	0.85			
		V _{CC} = 1.6V to 2V		±3		
I _O	Output current	V _{CC} = 2.25V to 2.75V		±7	mA	
	Low-Level input voltage Output current Output Current Input transition rise or fall rate	V _{CC} = 3.3V to 5.0V		±15		
lo	Output Current	V _{CC} = 4.5V to 5.5V		±25	mA	
Δt/Δv	Input transition rise or fall rate	V _{CC} = 1.6V to 5.0V		20	ns/V	
T _A	Operating free-air temperature		-55	125	°C	



5.4 Thermal Information

PACKAGE	PINS			THERMAL	METRIC ⁽¹⁾			UNIT
	FING	R _{θJA}	R _{0JC(top)}	R _{θJB}	Ψ _{JT}	Ψ _{JB}	R _{θJC(bot)}	UNIT
PW (TSSOP)	16	117.4	52.5	75.2	4.7	74.5	-	°C/W

For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application (1) note.

5.5 Electrical Characteristics

over operating free-air temperature range; typical ratings measured at $T_A = 25^{\circ}C$ (unless otherwise noted).

PARAMETER	TEST CONDITIONS	V _{cc}	MIN	TYP	MAX	UNIT	
	Ι _{ΟΗ} = -50μΑ	1.2V to 5.5V	V _{CC} -0.2				
	I _{OH} = -1mA	1.2V	0.8				
V _{OH}	I _{OH} = -2mA	1.65V to 2V	1.21	1.7 ⁽¹⁾			
V _{OH}	I _{OH} = -3mA	2.25V to 2.75V	1.93	2.4 ⁽¹⁾		V	
	I _{OH} = -5.5mA	3V to 3.6V	2.49	3.08 ⁽¹⁾			
	I _{OH} = -8mA	4.5V to 5.5V	3.95	4.65 ⁽¹⁾			
	I _{OH} = -24mA	4.5V to 5.5V	$\begin{array}{c c} V_{CC}\text{-}0.2 \\ \hline 0.8 \\ \hline 1.21 & 1.7^{(1)} \\ \hline 1.93 & 2.4^{(1)} \\ \hline 2.49 & 3.08^{(1)} \end{array} \\ \\ \end{array} \\ V$				
	I _{OL} = 50μA	1.2V to 5.5V			0.1		
V _{OL}	I _{OL} = 1mA	1.2V			0.2	V	
	I _{OL} = 2mA	1.65V to 2V		0.1 ⁽¹⁾	0.25		
	I _{OL} = 3mA	2.25V to 2.75V		0.1 ⁽¹⁾	0.2		
	I _{OL} = 5.5mA	3V to 3.6V		0.2 ⁽¹⁾	0.25		
	I _{OL} = 8mA	4.5V to 5.5V		0.3 ⁽¹⁾	0.35		
	I _{OL} = 24mA	4.5V to 5.5V			0.75		
1	V _I = 0V or V _{CC}	0V to 5.5V		±0.1	±1	μA	
сс	$V_1 = V_{CC}$ or GND, $I_0 = 0$	1.8V to 5.5V		2	20	μA	
ΔI _{CC}	One input at 0.3V or 3.4V, other inputs at 0 or V_{CC} , $I_0 = 0$	5.5V		1.35	1.5	mA	
	One input at 0.3V or 1.1V, other inputs at 0 or V_{CC} , $I_{O} =$ 0	1.8V			68	μA	
CI	V _I = V _{CC} or GND	5V		3	5	pF	
Co	$V_{O} = V_{CC}$ or GND	5V		5	8	pF	
C _{PD} ⁽²⁾ (3)	C _L = 50pF, F = 10MHz	1.8V to 5.5V			200	pF	

Typical value at nearest nominal voltage (1.8V, 2.5V, 3.3V, and 5V) (1)

(1) Typical value at hearest hormal voltage (1:0, 2:0, 0:0, and 0.7) (2) C_{PD} is used to determine the dynamic power consumption, per channel. (3) $P_D = V_{CC} {}^2xF_Ix(C_{PD} + C_L)$ where $F_I =$ input frequency, $C_L =$ output load capacitance, $V_{CC} =$ supply voltage.

5.6 Switching Characteristics

over operating free-air temperature range; typical values measured at T_A = 25°C (unless otherwise noted)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	Lood Conseitence	V	-55°C to 125°C			UNIT
PARAWIETER		10 (001901)	Load Capacitance	V _{cc}	MIN	TYP	MAX	UNIT
t _{PHL}	A or B	Any Y	C _L = 15pF	1.8V		28.5	33.0	ns
t _{PHL}	A or B	Any Y	C _L = 50pF	1.8V		33.2	38.5	ns
t _{PLH}	A or B	Any Y	C _L = 15pF	1.8V		26.4	30.0	ns
t _{PLH}	A or B	Any Y	C _L = 50pF	1.8V		29.8	34.0	ns
t _{PHL}	G	Any Y	C _L = 15pF	1.8V		25	29.0	ns
t _{PHL}	G	Any Y	C _L = 50pF	1.8V		29.5	34.0	ns
t _{PLH}	G	Any Y	C _L = 15pF	1.8V		29.6	34.0	ns

Copyright © 2025 Texas Instruments Incorporated

Submit Document Feedback 5

SN74LV8T157-EP SCASE54 – JANUARY 2025


over operating free-air temperature range; typical values measured at T_A = 25°C (unless otherwise noted)

DADAMETER			Load Conselten	N	-55°(C to 125°	°C		
PARAMETER	FROM (INPUT)	TO (OUTPUT)	Load Capacitance	V _{cc}	MIN TYP		MAX	UNIT	
t _{PLH}	G	Any Y	C _L = 50pF	1.8V		33.3	38.0	ns	
t _{PHL}	Ā/B	Any Y	C _L = 15pF	1.8V		28.6	33.0	ns	
t _{PHL}	Ā/B	Any Y	C _L = 50pF	1.8V		32.7	38.0	ns	
t _{PLH}	Ā/B	Any Y	C _L = 15pF	1.8V		28.6	34.0	ns	
t _{PLH}	Ā/B	Any Y	C _L = 50pF	1.8V		33.3	38.0	ns	
t _{PHL}	A or B	Any Y	C _L = 15pF	2.5V		15.6	20.0	ns	
t _{PHL}	A or B	Any Y	C _L = 50pF	2.5V		18.7	23.0	ns	
t _{PLH}	A or B	Any Y	C _L = 15pF	2.5V		13.6	16.5	ns	
t _{PLH}	A or B	Any Y	C _L = 50pF	2.5V		16.1	19.5	ns	
t _{PHL}	G	Any Y	C _L = 15pF	2.5V		13.3	16.0	ns	
t _{PHL}	G	Any Y	C _L = 50pF	2.5V		16.4	19.2	ns	
t _{PLH}	G	Any Y	C _L = 15pF	2.5V		15.5	19.0	ns	
t _{PLH}	G	Any Y	C _L = 50pF	2.5V		17.8	22.0	ns	
t _{PHL}	Ā/B	Any Y	C _L = 15pF	2.5V		15.2	19.5	ns	
t _{PHL}	Ā/B	Any Y	C _L = 50pF	2.5V		18.5	23.0	ns	
t _{PLH}	Ā/B	Any Y	C _L = 15pF	2.5V		15.5	19.0	ns	
t _{PLH}	Ā/B	Any Y	C _L = 50pF	2.5V		17.8	22.0	ns	
t _{PHL}	A or B	Any Y	C _L = 15pF	3.3V		10.9	16.5	ns	
t _{PHL}	A or B	Any Y	C _L = 50pF	3.3V		13.3	16.5	ns	
t _{PLH}	A or B	Any Y	C _L = 15pF	3.3V		9.28	16.5	ns	
t _{PLH}	A or B	Any Y	C _L = 50pF	3.3V		11.2	16.5	ns	
t _{PHL}	G	Any Y	C _L = 15pF	3.3V		9.3	20.5	ns	
t _{PHL}	G	Any Y	C _L = 50pF	3.3V		11.9	20.5	ns	
t _{PLH}	G	Any Y	C _L = 15pF	3.3V		10.6	20.5	ns	
t _{PLH}	G	Any Y	C _L = 50pF	3.3V		12.5	20.5	ns	
t _{PHL}	Ā/B	Any Y	C _L = 15pF	3.3V		10.9	20	ns	
t _{PHL}	Ā/B	Any Y	C _L = 50pF	3.3V		13.5	20	ns	
t _{PLH}	Ā/B	Any Y	C _L = 15pF	3.3V		10.6	20	ns	
t _{PLH}	Ā/B	Any Y	C _L = 50pF	3.3V		12.5	20	ns	
t _{PHL}	A or B	Any Y	C _L = 15pF	5V		7.36	10.5	ns	
t _{PHL}	A or B	Any Y	C _L = 50pF	5V		9.13	11.5	ns	
t _{PLH}	A or B	Any Y	C _L = 15pF	5V		6.86	10.5	ns	
t _{PLH}	A or B	Any Y	$C_L = 50 pF$	5V		8.2	10.5	ns	
t _{PHL}	G	Any Y	C _L = 15pF	5V		6.96	13	ns	
t _{PHL}	G	Any Y	$C_L = 50 pF$	5V		8.87	13	ns	
t _{PLH}	G	Any Y	$C_L = 15 pF$	5V		7.76	13	ns	
t _{PLH}	G	Any Y	$C_L = 50 pF$	5V		9.2	13	ns	
t _{PHL}	Ā/B	Any Y	C _L = 15pF	5V		7.36	13	ns	
t _{PHL}	Ā/B	Any Y	$C_L = 50 pF$	5V		9.31	13	ns	
t _{PLH}	Ā/B	Any Y	$C_L = 15 pF$	5V		7.76	13	ns	
t _{PLH}	Ā/B	Any Y	$C_L = 50 \text{pF}$	5V 5V		9.2	13	ns	



5.7 Typical Characteristics


 $T_A = 25^{\circ}C$ (unless otherwise noted)



8 Submit Document Feedback

5.7 Typical Characteristics (continued)

 $T_A = 25^{\circ}C$ (unless otherwise noted)










5.7 Typical Characteristics (continued)

 $T_A = 25^{\circ}C$ (unless otherwise noted)





 V_{CC}

0 V

V_{OH}

 V_{OL}


VOH

 V_{OL}


6 Parameter Measurement Information

Phase relationships between waveforms were chosen arbitrarily for the examples listed in the following table. All input pulses are supplied by generators having the following characteristics: PRR \leq 1MHz, Z₀ = 50 Ω , t_t < 2.5ns.

The outputs are measured individually with one input transition per measurement.



(1) The greater between t_{PLH} and t_{PHL} is the same as t_{pd} . Figure 6-2. Voltage Waveforms Propagation Delays



(1) The greater between t_{r} and t_{f} is the same as $t_{t}. \label{eq:transform}$

Figure 6-3. Voltage Waveforms, Input and Output Transition Times



7 Detailed Description

7.1 Overview

The SN74LV8T157-EP devices contain inverters and drivers to supply full data selection to the four output gates. A separate strobe (\overline{G}) input is provided. A 4-bit word is selected from one of two sources and is routed to the four outputs. The SN74LV8T157-EP devices present true data.

7.2 Functional Block Diagram




Figure 7-1. Logic Diagram (Positive Logic)

7.3 Feature Description

7.3.1 Balanced CMOS Push-Pull Outputs

This device includes balanced CMOS push-pull outputs. The term *balanced* indicates that the device can sink and source similar currents. The drive capability of this device may create fast edges into light loads, so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important to limit the output power of the device to avoid damage due to overcurrent. The electrical and thermal limits defined in the *Absolute Maximum Ratings* must be followed at all times.

Unused push-pull CMOS outputs must be left disconnected.



7.3.2 LVxT Enhanced Input Voltage

The SN74LV8T157-EP belongs to TI's LVxT family of logic devices with integrated voltage level translation. This family of devices was designed with reduced input voltage thresholds to support up-translation, and inputs tolerant of signals with up to 5.5V levels to support down-translation. For proper functionality, input signals must remain at or above the specified $V_{IH(MIN)}$ level for a HIGH input state, and at or below the specified $V_{IL(MAX)}$ for a LOW input state. Figure 7-2 shows the typical V_{IH} and V_{IL} levels for the LVxT family of devices, as well as the voltage levels for standard CMOS devices for comparison.

The inputs are high impedance and are typically modeled as a resistor in parallel with the input capacitance given in the *Electrical Characteristics*. The worst case resistance is calculated with the maximum input voltage, given in the *Absolute Maximum Ratings*, and the maximum input leakage current, given in the *Electrical Characteristics*, using Ohm's law ($R = V \div I$).

Input signals must transition between valid logic states quickly, as defined by the input transition rate in the *Recommended Operating Conditions* table. Failing to meet this specification will result in excessive power consumption and could cause oscillations. More details can be found in the *Implications of Slow or Floating CMOS Inputs* application report.

Do not leave inputs floating at any time during operation. Unused inputs must be terminated at a valid high or low voltage level. If a system will not be actively driving an input at all times, then a pull-up or pull-down resistor can be added to provide a valid input voltage during these times. The resistor value will depend on multiple factors; however, a $10k\Omega$ resistor is recommended and will typically meet all requirements.




Figure 7-2. LVxT Input Voltage Levels



7.3.2.1 Up Translation

Input signals can be up translated using the SN74LV8T157-EP. The voltage applied at V_{CC} will determine the output voltage and the input thresholds as described in the Recommended Operating Conditions and Electrical Characteristics tables. When connected to a high-impedance input, the output voltage will be approximately V_{CC} in the HIGH state, and 0V in the LOW state.

The inputs have reduced thresholds that allow for input HIGH state levels, which are much lower than standard values. For example, standard CMOS inputs for a device operating at a 5V supply will have a V_{IH(MIN)} of 3.5V. For the SN74LV8T157-EP, VIH(MIN) with a 5V supply is only 2V, which would allow for up-translation from a typical 2.5V to 5V signals.

Ensure that the input signals in the HIGH state are above V_{IH(MIN)} and input signals in the LOW state are lower than $V_{IL(MAX)}$ as shown in Figure 7-3.

Up Translation Combinations are as follows:

- 1.8V V_{CC} Inputs from 1.2V
- 2.5V V_{CC} Inputs from 1.8V
- $3.3V~V_{CC}$ Inputs from 1.8V and 2.5V 5.0V V_{CC} Inputs from 2.5V and 3.3V




Figure 7-3. LVxT Up and Down Translation Example

7.3.2.2 Down Translation

Signals can be translated down using the SN74LV8T157-EP. The voltage applied at the V_{CC} will determine the output voltage and the input thresholds as described in the Recommended Operating Conditions and Electrical Characteristics tables.

When connected to a high-impedance input, the output voltage will be approximately V_{CC} in the HIGH state, and 0V in the LOW state. Ensure that the input signals in the HIGH state are between $V_{H(MIN)}$ and 5.5V, and input signals in the LOW state are lower than V_{IL(MAX)} as shown in Figure 7-2.

For example, standard CMOS inputs for devices operating at 5.0V, 3.3V or 2.5V can be down-translated to match 1.8V CMOS signals when operating from 1.8V V_{CC} . See Figure 7-3.

Down Translation Combinations are as follows:

- 1.8V V_{CC} Inputs from 2.5V, 3.3V, and 5.0V
- 2.5V V_{CC} Inputs from 3.3V and 5.0V
- 3.3V V_{CC} Inputs from 5.0V


7.3.3 Clamp Diode Structure

As Figure 7-4 shows, the outputs to this device have both positive and negative clamping diodes, and the inputs to this device have negative clamping diodes only.

CAUTION

Voltages beyond the values specified in the Absolute Maximum Ratings table can cause damage to the device. The input and output voltage ratings may be exceeded if the input and output clampcurrent ratings are observed.







7.4 Device Functional Modes

INPU	ITS ⁽¹⁾	DA	TA								
G	SELECT Ā/B	А	В	Ουτρυτ Υ							
н	Х	Х	Х	L							
L	L	L	Х	L							
L	L	Н	Х	Н							
L	Н	Х	L	L							
L	Н	Х	Н	Н							

Table 7-1. Function Tab

(1) H = High Voltage Level, L = Low Voltage Level, X = Do not Care, Z = High Impedance



8 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

8.1 Application Information

The SN74LV8T157-EP is a quadruple 2-to-1 data selector/multiplexer. The following application shows an example of using the device with all required connections to switch a 4-bit data bus between two source devices.

8.2 Typical Application




Figure 8-1. Typical Application Block Diagram



8.2.1 Design Requirements

8.2.1.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the *Recommended Operating Conditions*. The supply voltage sets the device's electrical characteristics of the device as described in the *Electrical Characteristics* section.

The positive voltage supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the SN74LV8T157-EP plus the maximum static supply current, I_{CC} , listed in the *Electrical Characteristics*, and any transient current required for switching. The logic device can only source as much current that is provided by the positive supply source. Ensure the maximum total current through V_{CC} listed in the *Absolute Maximum Ratings* is not exceeded.

The ground must be capable of sinking current equal to the total current to be sunk by all outputs of the SN74LV8T157-EP plus the maximum supply current, I_{CC} , listed in the *Electrical Characteristics*, and any transient current required for switching. The logic device can only sink as much current that can be sunk into its ground connection. Ensure the maximum total current through GND listed in the *Absolute Maximum Ratings* is not exceeded.

The SN74LV8T157-EP can drive a load with a total capacitance less than or equal to 50pF while still meeting all of the data sheet specifications. Larger capacitive loads can be applied; however, it is not recommended to exceed 50pF.

The SN74LV8T157-EP can drive a load with total resistance described by $R_L \ge V_O / I_O$, with the output voltage and current defined in the *Electrical Characteristics* table with V_{OH} and V_{OL} . When outputting in the HIGH state, the output voltage in the equation is defined as the difference between the measured output voltage and the supply voltage at the V_{CC} pin.

Total power consumption can be calculated using the information provided in *CMOS Power Consumption and Cpd Calculation*.

Thermal increase can be calculated using the information provided in *Thermal Characteristics of Standard Linear and Logic (SLL) Packages and Devices*.

CAUTION

The maximum junction temperature, $T_{J(max)}$ listed in the *Absolute Maximum Ratings*, is an additional limitation to prevent damage to the device. Do not violate any values listed in the *Absolute Maximum Ratings*. These limits are provided to prevent damage to the device.



8.2.1.2 Input Considerations

Input signals must cross to be considered a logic LOW, and to be considered a logic HIGH. Do not exceed the maximum input voltage range found in the *Absolute Maximum Ratings*.

Unused inputs must be terminated to either V_{CC} or ground. The unused inputs can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input will be used sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The drive current of the controller, leakage current into the SN74LV8T157-EP (as specified in the *Electrical Characteristics*), and the desired input transition rate limits the resistor size. A 10k Ω resistor value is often used due to these factors.

Refer to the *Feature Description* section for additional information regarding the inputs for this device.

8.2.1.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the V_{OH} specification in the *Electrical Characteristics*. The ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the V_{OL} specification in the *Electrical Characteristics*.

Push-pull outputs that could be in opposite states, even for a very short time period, should never be connected directly together. This can cause excessive current and damage to the device.

Two channels within the same device with the same input signals can be connected in parallel for additional output drive strength.

Unused outputs can be left floating. Do not connect outputs directly to V_{CC} or ground.

Refer to the *Feature Description* section for additional information regarding the outputs for this device.



8.2.2 Detailed Design Procedure

- Add a decoupling capacitor from V_{CC} to GND. The capacitor needs to be placed physically close to the device and electrically close to both the V_{CC} and GND pins. An example layout is shown in the *Layout* section.
- Ensure the capacitive load at the output is ≤ 50pF. This is not a hard limit; by design, however, it will
 optimize performance. This can be accomplished by providing short, appropriately sized traces from the
 SN74LV8T157-EP to one or more of the receiving devices.
- 3. Ensure the resistive load at the output is larger than $(V_{CC} / I_{O(max)})\Omega$. Doing this will prevent the maximum output current from the *Absolute Maximum Ratings* from being violated. Most CMOS inputs have a resistive load measured in M Ω ; much larger than the minimum calculated previously.
- 4. Thermal issues are rarely a concern for logic gates; the power consumption and thermal increase, however, can be calculated using the steps provided in the application report, *CMOS Power Consumption and Cpd Calculation*.

8.2.3 Application Curve




Figure 8-2. Application Timing Diagram

8.3 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Recommended Operating Conditions*. Each V_{CC} terminal should have a good bypass capacitor to prevent power disturbance. A 0.1µF capacitor is recommended for this device. It is acceptable to parallel multiple bypass capacitors to reject different frequencies of noise. The 0.1µF and 1µF capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results.

8.4 Layout

8.4.1 Layout Guidelines

- Bypass capacitor placement
 - Place near the positive supply terminal of the device
 - Provide an electrically short ground return path
 - Use wide traces to minimize impedance
 - Keep the device, capacitors, and traces on the same side of the board whenever possible
- Signal trace geometry
 - 8mil to 12mil trace width
 - Lengths less than 12cm to minimize transmission line effects
 - Avoid 90° corners for signal traces
 - Use an unbroken ground plane below signal traces
 - Flood fill areas around signal traces with ground
 - For traces longer than 12cm
 - Use impedance controlled traces
 - · Source-terminate using a series damping resistor near the output
 - · Avoid branches; buffer signals that must branch separately



8.4.2 Layout Example





Figure 8-3. Example Trace Corners for Improved Signal Integrity

GNE 0.	1 µF
2	13
3	12
4	11
5	10
6	9
GND 🗖 7	8






Figure 8-5. Example Bypass Capacitor Placement for WQFN and Similar Packages




Figure 8-6. Example Bypass Capacitor Placement for SOT, SC70 and Similar Packages




Figure 8-7. Example Damping Resistor Placement for Improved Signal Integrity



9 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

9.1 Documentation Support

9.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, CMOS Power Consumption and C_{pd} Calculation application report
- Texas Instruments, Designing With Logic application report
- Texas Instruments, Thermal Characteristics of Standard Linear and Logic (SLL) Packages and Devices application report

9.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

9.3 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

9.4 Trademarks

TI E2E[™] is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

9.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

9.6 Glossary

TI Glossary This glossary lists and explains terms, acronyms, and definitions.

10 Revision History

-		
DATE	REVISION	NOTES
January 2025	*	Initial Release

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
SN74LV8T157MPWR	EP ACTIVE	TSSOP	PW	16	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM		LV157EP	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LV8T157MPWREP	TSSOP	PW	16	3000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

16-Feb-2025



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74LV8T157MPWREP	TSSOP	PW	16	3000	353.0	353.0	32.0

PW0016A



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



PW0016A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



PW0016A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

9. Board assembly site may have different recommendations for stencil design.



^{8.} Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025, Texas Instruments Incorporated