

LM65680-Q1 70V, 8A Buck Regulator Evaluation Module



Description

The [LM65680-Q1EVM](#) evaluation module (EVM) is a synchronous, buck, DC/DC regulator that employs synchronous rectification to achieve high conversion efficiency in a small footprint. The EVM operates over a wide input voltage range of 6V to 70V, which offers outsized voltage rating and operating margin to withstand supply-rail voltage transients while providing a regulated output of 5V. The output voltage has better than 1% setpoint accuracy and is adjusted by modifying the feedback resistor values, permitting the user to customize the output voltage as needed.

The selected input and output capacitors accommodate the entire range of input voltage. Output voltage configuration must be limited to 5V since output capacitors are rated for 10V for small solution size. For output voltages higher than 5V, careful consideration of higher voltage rated capacitors is recommended.


Features

- Wide input voltage operating range of 6V to 70V
- Adjustable output down to 0.8V
- Switching frequency of 400kHz externally synchronizable up or down by 20%
- Full-load efficiency of 91.7% at 12V_{IN}, 91.5% at 24V_{IN} and 90% at 48V_{IN}

- 15μA no load operating current at 48V_{IN}
- Designed for low Electromagnetic Interference (EMI)
 - Dual-random spread spectrum EMI mitigation
 - Meets CISPR 25 Class 5 and UNECE Reg 10 EMI standards
- Peak current-mode control architecture provides fast line and load transient response
 - Integrated slope compensation adaptive with switching frequency
 - Forced pulsed width modulation (FPWM) or pulsed frequency modulation (PFM) operation
 - Optional internal or external loop compensation
- Integrated high-side and low-side power MOSFETs
- Overcurrent protection (OCP) with hiccup mode for sustained overload conditions
- SYNCOUT signal 180° out-of-phase with internal clock
- Power-Good (PG) signal with 100kΩ pullup resistor to VOUT
- Internal 5.3ms soft start (SS)
- Fully assembled, tested, and proven PCB layout

Applications

- [Advanced Driver Assistance Systems \(ADAS\)](#)
- [Automotive infotainment and cluster](#)
- [Hybrid, electric, and powertrain systems](#)



1 Evaluation Module Overview

1.1 Introduction

The LM65680-Q1EVM uses the LM65680-Q1 synchronous buck converter IC with input voltage range up to 70V and output current up to 8A. The default evaluation module (EVM) features an output voltage that is set to 5V adjustable and a switching frequency of 400kHz.

The design supports adjustable input voltage UVLO for application-specific power-up and power-down requirements, external clock synchronization to mitigate beat frequencies in noise-sensitive applications, power good (PG) indicator for sequencing and output voltage monitoring, pin-selectable dual random spread spectrum (DRSS) control for electromagnetic interference (EMI) mitigation, pin-selectable MODE control for light-load performance (pulsed frequency modulation - PFM) with AUTO mode or fixed switching frequency with forced pulsed width modulation (FPWM) mode, pin-selectable COMP feature for internal or external compensation, and soft start (SS) feature to extend the soft-start time.

The [LM65680-Q1](#) synchronous buck converter used in the EVM has the following features:

- Wide input voltage (wide V_{IN}) range of 3V to 70V
- Dual random spread spectrum (DRSS) modulation for lower EMI
- Wide duty cycle range with low $t_{ON(min)}$ and $t_{OFF(min)}$
- Ultra-low shutdown and no-load standby quiescent currents
- Multiphase capability
- Peak current-mode control loop architecture
- Integrated, high-current MOSFETs
- Cycle-by-cycle overcurrent protection with hiccup

1.2 Kit Contents

- LM65680-Q1EVM Circuit Board
- EVM Disclaimer Read Me
- Prototype EVM Disclaimer Read Me

1.3 Specification

The following figure shows the schematic of an LM65680-Q1 based synchronous buck converter.




Figure 1-1. LM65680-Q1 Synchronous Buck Regulator Simplified Schematic

1.4 Device Information

With an input operating voltage range from 3V to 70V and rated output current up to 8A, the LM65680-Q1 buck converter provides flexibility, scalability, and optimized solution size for a wide range of applications. The device enables design for high power density and low EMI solutions. Available EMI mitigation includes dual random spread spectrum (DRSS) and slew rate (SR) control to reduce peak EMI emissions.

The free-running switching frequency of the EVM is 400kHz and is synchronizable to a higher or lower frequency, if required. VCC and gate drive UVLO protects the regulator at low input voltage conditions, and EN pin supports application-specific power-up and power-down requirements. The [LM65680-Q1](#) is available in a 26-pin VQFN package with 4.5mm × 4.5mm footprint to enable DC/DC devices with high density and low component count. See the [LM65680-Q1 70V, 8A, Automotive Buck Converter Optimized for Low EMI and High Power Density data sheet](#) for more information.

2 Hardware

2.1 Test Setup and Procedure

2.1.1 EVM Connections

Referencing the EVM connections described in [Table 2-1](#), the recommended test setup to evaluate the LM65680-Q1 is shown in [Figure 2-1](#). Working at an ESD-protected workstation, make sure that any wrist straps, boot straps, or mats are connected and referencing the user to earth ground before handling and applying power to the EVM.




Figure 2-1. EVM Test Setup

Note

Refer to the [LM65680-Q1 70V, 8A, Automotive Buck Converter Optimized for Low EMI and High Power Density](#) data sheet, [LM65680-Q1 Quickstart Calculator](#), and [WEBENCH® Power Designer](#) for additional guidance pertaining to component selection and converter operation.

Table 2-1. EVM Power Connections

LABEL	DESCRIPTION
VIN+	Positive input power connection
VIN-	Negative input power connection
VOUT+	Positive output power connection
VOUT-	Negative output power connection

Table 2-2. EVM Signal Connections

LABEL	DESCRIPTION
PG	Power-Good indicator
BIAS	Input to internal voltage regulator. Connect to VOUT or optional external bias supply for higher efficiency
VOUT	Output voltage
VCC	Internal regulator output. Do not connect this pin to any external loads.
CONFIG	Loop compensation selection. Connect CONFIG to VCC for internal compensation. Floating the CONFIG pin or connecting CONFIG to GND for external compensation.
GND	GND connection
INJ	50Ω injection point for loop response
GND	GND connection
EN	ENABLE input – tie to GND to disable the device
VIN	Input voltage
VAUX	Requires functional safety IC variant. Auxiliary pull-up voltage for nFault. Connect to VIN, VCC, or optional external bias supply.
VCC	Internal regulator output. Do not connect this pin to any external loads.
VCC	Internal regulator output. Do not connect this pin to any external loads.
MODE/SYNC	PFM / FPWM selection and synchronization input. Connect MODE/SYNC to GND for AUTO mode or to VCC for FPWM mode. The MODE/SYNC pin can also be driven by an external synchronization clock signal to operate in FPWM mode.
GND	GND connection
nFAULT	Requires functional safety IC variant. Test point used to monitor if any faults has occurred in the regulator or the system. nFAULT is an active low fault signal.

2.1.2 Test Equipment

Voltage Source: The input voltage source V_{IN} must be an 80V variable DC source capable of supplying 8A.

Multimeters:

- **Voltmeter 1:** Measure the input voltage at VIN_S to PGND test point.
- **Voltmeter 2:** Measure the output voltage at VOUT+ (TP5) to VOUT– (TP6).
- **Ammeter 1:** Measure the input current. Set the ammeter to 1-second aperture time.
- **Ammeter 2:** Measure the output current. Set the ammeter to 1-second aperture time.

Electronic Load: The load must be an electronic constant-resistance (CR) or constant-current (CC) mode capable of $0A_{DC}$ to $15A_{DC}$. For a no-load input current measurement, disconnect the electronic load as the load can draw a small residual current.

Oscilloscope: With the scope set to 20MHz bandwidth and AC coupling, measure the output voltage ripple directly across an output capacitor with a short ground lead normally provided with the scope probe. Place the oscilloscope probe tip on the positive terminal of the output capacitor, holding the ground barrel of the probe through the ground lead to the negative terminal of the capacitor. TI does not recommend using a long-leaded ground connection because this can induce additional noise given a large ground loop. To measure other waveforms, adjust the oscilloscope as needed.

Safety: Always use caution when touching any circuits that can be live or energized.

2.1.3 Recommended Test Setup

2.1.3.1 Input Connections

- Prior to connecting the DC input source, set the current limit of the input supply to 0.1A maximum. Make sure the input source is initially set to 0V and connected to the VIN+ and VIN– connection points as shown in [Figure 2-1](#).
- Connect voltmeter 1 at VIN_S and PGND (TP3) connection points to measure the input voltage.
- Connect ammeter 1 to measure the input current and set the ammeter to at least a 0.1 second aperture time.

2.1.3.2 Output Connections

- Connect an electronic load to VOUT+ and VOUT– connections as shown in [Figure 2-1](#). Set the load to constant-resistance mode or constant-current mode at 0A before applying input voltage.
- Connect voltmeter 2 at VOUT+ (TP5) and VOUT– (TP6) sense points to measure the output voltage.
- Connect ammeter 2 to measure the output current.

2.1.4 Test Procedure

2.1.4.1 Line, Load Regulation, and Efficiency

- Set up the EVM as described in [EVM Connections](#).
- Set load to constant resistance or constant current mode to sink 0A.
- Increase the input source voltage from 0V to 70V; use voltmeter 1 to measure the input voltage.
- Increase the current limit of the input supply to 8A.
- Use voltmeter 2 to measure the output voltage, V_{OUT} , and vary the load current from 0A to 8A DC; V_{OUT} must remain within the load regulation specification.
- Set the load current to 4A (50% rated load) and vary the input source voltage from 6V to 70V; V_{OUT} must remain within the line regulation specification.
- Set the load current to 8A (100% rated load) and measure the efficiency at typical input voltages (12V, 24V, 36V, 48V and 65V).
- Decrease the load to 0A. Decrease the input source voltage to 0V.

CAUTION

Extended operation at high output current can raise component and EVM board temperatures above 55°C. To avoid risk of a burn injury, do not touch the components and the EVM board until cooled sufficiently after disconnecting power.

3 Implementation Results

3.1 Performance Data and Results

The typical performance curves for the LM65680-Q1EVM are shown in [Figure 3-1](#) through [Figure 3-15](#). Because actual performance data can be affected by measurement techniques and environmental variables, these curves are presented for reference and can differ from actual field measurements.

3.1.1 EVM Characteristics

The electrical characteristics for LM65680-Q1EVM are shown in [Table 3-1](#).

Table 3-1. Electrical Performance Characteristics of EVM

Parameter	Test Conditions	MIN	TYP	MAX	Unit
INPUT CHARACTERISTICS					
Input voltage range, V_{IN}	Operating	8	24	70	V
Input current, no load, I_{IN-NL}	$I_{OUT} = 0A$, MODE/SYNC pin tied to GND	$V_{IN} = 12V$	29		μA
		$V_{IN} = 24V$	18		
		$V_{IN} = 48V$	15		
		$V_{IN} = 65V$	15.5		
Input voltage turn-on, $V_{IN(ON)}$	Adjusted using EN divide resistors	5.81		V	
Input voltage turn-off, $V_{IN(OFF)}$		4.73		V	
Input voltage hysteresis, $V_{IN(HYS)}$		1.08		V	
Input current, shutdown, I_{IN-OFF}	$V_{EN} = 0V$, $V_{IN} = 48V$, with 187k Ω and 49.9k Ω EN divider	357		μA	
OUTPUT CHARACTERISTICS					
Output voltage, V_{OUT} ⁽¹⁾		4.95	5	5.05	V
Output current, I_{OUT}	$V_{IN} = 8V$ to 65V, Airflow = 100 LFM ⁽²⁾	0	8		A
Output voltage regulation, ΔV_{OUT}	Load regulation	$I_{OUT} = 0A$ to 8A		0.1%	
	Line regulation	$V_{IN} = 8V$ to 65V		1%	
Output voltage ripple, V_{OUT-AC}	$V_{IN} = 48V$, $I_{OUT} = 8A$	35		mVrms	
Output overcurrent protection, I_{OCP}	$V_{IN} = 48V$	8.5		A	
Soft-start time, t_{SS}		5.3		ms	
SYSTEM CHARACTERISTICS					
Switching frequency, F_{SW-nom}	$V_{IN} = 48V$	400		kHz	
PFM Light-load efficiency, η_{LIGHT} ⁽¹⁾	$I_{OUT} = 1A$	$V_{IN} = 12V$	94.3%		
		$V_{IN} = 24V$	90.9%		
		$V_{IN} = 48V$	85.3%		
		$V_{IN} = 65V$	79.7%		
Half-load efficiency, η_{HALF}	$I_{OUT} = 4A$	$V_{IN} = 12V$	95.2%		
		$V_{IN} = 24V$	94%		
		$V_{IN} = 48V$	91.6%		
		$V_{IN} = 65V$	89.7%		
Full load efficiency, η_{FULL}	$I_{OUT} = 8A$	$V_{IN} = 12V$	91.7%		
		$V_{IN} = 24V$	91.5%		
		$V_{IN} = 48V$	90%		
		$V_{IN} = 65V$	88.8%		
LM65680-Q1 junction temperature, T_J		-40	150		$^{\circ}C$

- (1) The default output voltage of this EVM is 5V. Efficiency and other performance metrics can change based on operating input voltage, load currents, externally-connected output capacitors, and other parameters.
- (2) The recommended airflow when operating at input voltages greater than 65V is 100 LFM.

3.1.2 Conversion Efficiency




Figure 3-1. Efficiency, $V_{IN} = V_{EN} = 8V$ to $65V$, $V_{OUT} = 5V$, PFM Mode, Linear Scale




Figure 3-2. Efficiency, $V_{IN} = V_{EN} = 8V$ to $65V$, $V_{OUT} = 5V$, PFM Mode, Logarithmic Scale




Figure 3-3. Efficiency, $V_{IN} = V_{EN} = 8V$ to $65V$, $V_{OUT} = 5V$, FPWM Mode, Linear Scale




Figure 3-4. Efficiency, $V_{IN} = V_{EN} = 8V$ to $65V$, $V_{OUT} = 5V$, FPWM Mode, Logarithmic Scale

3.1.3 Operating Waveforms

3.1.3.1 Switching




Figure 3-5. Steady State Operation, $V_{IN} = 48\text{V}$, $V_{OUT} = 5\text{V}$, $I_{OUT} = 8\text{A}$, $F_{SW} = 400\text{kHz}$




Figure 3-6. Steady State Operation in PFM Mode, $V_{IN} = 48\text{V}$, $V_{OUT} = 5\text{V}$, $I_{OUT} = \text{No Load}$

3.1.3.2 Load Transient Response




Figure 3-7. Load Transient Response, $V_{IN} = 48V$, $V_{OUT} = 5V$, $F_{SW} = 400kHz$, FPWM, 0A to 8A at 1A/ μs

3.1.3.3 Short-Circuit Recovery




Figure 3-8. Short-Circuit Recovery $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$, $F_{SW} = 400kHz$, FPWM

3.1.3.4 Start-Up and Shutdown With EN




Figure 3-9. EN ON and OFF, $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$ Resistive Load, $F_{SW} = 400kHz$, FPWM

3.1.3.5 Start-Up With VIN




Figure 3-10. Start-Up, $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$ Resistive Load, $F_{SW} = 400kHz$, FPWM

3.1.4 Bode Plot




Figure 3-11. Bode Plot, $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$ Resistive Load

3.1.5 CISPR 25 EMI Performance

The EMI performance of the LM65680-Q1 EVM at 24V and 48V input with DRSS EMI mitigation disabled are shown in Figure 3-12 and Figure 3-13. Conducted emissions are measured over a frequency range of 150kHz to 108MHz using a 5μH LISN according to the CISPR 25 specification. CISPR 25 Class 5 peak and average limit lines are denoted in red. The purple and green spectra are measured using peak and average detection, respectively.




Figure 3-12. CISPR 25 Class 5 Conducted Emissions Plot, 150kHz to 108MHz, $V_{IN} = 24V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$ Resistive Load, $F_{SW} = 400kHz$




Figure 3-13. CISPR 25 Class 5 Conducted Emissions Plot, 150kHz to 108MHz, $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$ Resistive Load, $F_{SW} = 400kHz$

3.1.6 Thermal Performance

The thermal performance images are shown in [Figure 3-14](#) and [Figure 3-15](#).




Figure 3-14. Thermal Performance, $V_{IN} = 24V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$, $T_{amb} = 25^{\circ}C$, No Airflow




Figure 3-15. Thermal Performance, $V_{IN} = 48V$, $V_{OUT} = 5V$, $I_{OUT} = 8A$, $T_{amb} = 25^{\circ}C$, No Airflow

4 Hardware Design Files

4.1 Schematic

The EVM schematic is illustrated in [Figure 4-1](#).




Figure 4-1. EVM Schematic

4.2 PCB Layout

The design of the LM65680-Q1 EVM using a four-layer 62mils standard thickness PCB with 2oz. copper on all layers is shown in Figure 4-2 through Figure 4-9.




Figure 4-2. Top 3D View




Figure 4-3. Bottom 3D View (viewed from Bottom)




Figure 4-4. Top Layer Copper (Top View)




Figure 4-5. Layer 2 Copper (Top View)




Figure 4-6. Layer 3 Copper (Top View)




Figure 4-7. Bottom Layer Copper (Inverted)

4.2.1 Component Drawings




Figure 4-8. Top Component Drawing




Figure 4-9. Bottom Component Drawing

4.2.2 Multi-Layer Stackup

#	Name	Material	Type	Weight	Thickness	Dk	Df
	Top Overlay		Overlay				
	Top Solder	Solder Resist	Solder Mask		0.4mil	3.5	
1	Top Layer		Signal	2oz	2.8mil		
	Dielectric1	FR-4 High Tg	Core		5mil	4.2	
2	Signal Layer 1		Signal	2oz	2.8mil		
	Dielectric 2	FR-4 High Tg	Prepreg		40mil	4.2	
3	Signal Layer 2		Signal	2oz	2.8mil		
	Dielectric 3	FR-4 High Tg	Core		5mil	4.2	
4	Bottom Layer		Signal	2oz	2.8mil		
	Bottom Solder	Solder Resist	Solder Mask		0.4mil	3.5	
	Bottom Overlay		Overlay				

Figure 4-10. Layer Stackup

4.3 Bill of Materials

Table 4-1. Component BOM

REF DES	QTY	VALUE	DESCRIPTION	PACKAGE	PART NUMBER	MANUFACTURER
C1, C10, C11, C24	4	0.1 μ F	CAP, CERM, 0.1 μ F, 100V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	G CJ188R72A104KA01D	MuRata
C2, C3, C4, C8, C9, C27, C28	7	4.7 μ F	CAP, CERM, 4.7 μ F, 100V, +/- 10%, X7S, AEC-Q200 Grade 1, 1210	1210	GCM32DC72A475KE02L	MuRata
C5, C6, C25, C26	4	0.1 μ F	CAP, CERM, 0.1 μ F, 100V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805	CGA4J2X7R2A104K125AA	TDK
C7	1	68 μ F	CAP, AL, 68 μ F, 80V, +/- 20%, 0.32ohm, AEC-Q200 Grade 2, SMD	SMT Radial H13	EEV-FK1K680Q	Panasonic
C12	1	1 μ F	CAP, CERM, 1 μ F, 16V, +/- 20%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71C105MA64D	MuRata
C13	1	0.47 μ F	CAP, CERM, 0.47 μ F, 50V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CGA3E3X7R1H474K080AB	TDK
C14, C17	2	0.1 μ F	CAP, CERM, 0.1 μ F, 50V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7R1H104K050BB	TDK
C15	1	2.2nF	Ceramic Capacitor Automotive 2200pF \pm 10% 50V X7R 0603	0603	UMJ107AB7222KAHT	Taiyo Yuden
C18	1	10pF	CAP, CERM, 10pF, 50V, +/- 5%, C0G/NP0, 0603	0603	CGA3E2C0G1H100D080AA	TDK
C19, C20	2	47 μ F	Ceramic Capacitor for Automotive 47 μ F \pm 10% 10VDC X7S 1210 Embossed T/R	1210	GCM32EC71A476KE02K	Murata
H1, H2, H3, H4	4		Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw	NY PMS 440 0025 PH	B&F Fastener Supply
H5, H6, H7, H8	4		Standoff, Hex, 0.5"L #4-40 Nylon	Standoff	1902C	Keystone
J1, J4	2		Terminal Block, 5mm, 2x1, Tin, TH	Terminal Block, 5mm, 2x1, TH	691 101 710 002	Wurth Elektronik
J3	1		Header, 100mil, 16x1, Gold, TH	16x1 Header	TSW-116-07-G-S	Samtec
L1	1		Coupled inductor, 7.6 μ H, 700ohm, AEC-Q200 Grade 1, SMD	12x11mm	ACM12V-701-2PL-TL00	TDK
L2, L3	2	3.3 μ H	Shielded Power Inductors 3.3uH 20% tol, 6.5mOhm 16.6A	SMT_6MM51_6M M71	XGL6060-332MEC	Coilcraft
R1, R15, R18	3	0	RES, 0, 1%, 0.1W, AEC-Q200 Grade 0, 0603	0603	RMCF0603ZT0R00	Stackpole Electronics Inc
R2	1	150k	RES, 150k, 1%, 0.063W, AEC-Q200 Grade 0, 0402	0402	CRCW0402150KFKED	Vishay-Dale
R3	1	40.2k	RES, 40.2k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	0603	CRCW060340K2FKEA	Vishay-Dale
R4	1	8.66k	RES, 8.66k, 1%, 0.1W, 0603	0603	RC0603FR-078K66L	Yageo
R5	1	187k	RES, 187k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	0603	CRCW0603187KFKEA	Vishay-Dale
R6, R8	2	49.9k	49.9kOhms \pm 1% 0.1W, 1/10W Chip Resistor 0603 (1608 Metric) Automotive AEC-Q200 Thick Film	0603	CRCW060349K9FKEA	Vishay
R7	1	150k	RES, 150k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	0603	CRCW0603150KFKEA	Vishay-Dale

Table 4-1. Component BOM (continued)

REF DES	QTY	VALUE	DESCRIPTION	PACKAGE	PART NUMBER	MANUFACTURER
R14	1	100k	RES, 100k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	0603	CRCW0603100KFKEA	Vishay-Dale
R16	1	49.9k	RES, 49.9, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060349R9FKEA	Vishay-Dale
R17	1	78.7k	78.7kOhms \pm 0.5% 0.1W, 1/10W Chip Resistor 0603 (1608 Metric) Automotive AEC-Q200 Thick Film	0603	ERJ-3RBD7872V	Panasonic
R19	1	15k	15kOhms \pm 0.1% 0.15W Chip Resistor 0603 (1608 Metric) Anti-Sulfur, Automotive AEC-Q200 Thin Film	0603	RQ73C1J15KBTD	TE Connectivity
SH-J1, SH-J2, SH-J3, SH-J4, SH-J5	5	1x2	Shunt, 100mil, Gold plated, Black	Shunt	SNT-100-BK-G	Samtec
TP1, TP2, TP3, TP5, TP6	5		Test Point, Miniature, SMT	Test Point, Miniature, SMT	5019	Keystone
VIN_S	1		Testpoint_Keystone_Miniature	Test Point, Miniature, SMT	5015	Keystone
U1	1		70V, 8A Automotive Buck Converters Optimized for Low EMI and High Power Density	VQFN-FCRLF26	LM65680RZYRQ1	Texas Instruments
C16	0	10pF	CAP, CERM, 10pF, 50V, +/- 5%, C0G/NP0, 0603	0603	GRM1885C1H100JA01D	Murata
C21, C22	0	47 μ F	Ceramic Capacitor for Automotive 47 μ F \pm 10% 10VDC X7S 1210 Embossed T/R	1210	GCM32EC71A476KE02K	Murata
C23	0	82 μ F	CAP, Aluminum Polymer, 82 μ F, 16V, +/- 20%, 0.03ohm	1210	875105344009	Wurth Elektronik
R10	0	78.7k	78.7kOhms \pm 0.5% 0.1W, 1/10W Chip Resistor 0603 (1608 Metric) Automotive AEC-Q200 Thick Film	0603	ERJ-3RBD7872V	Panasonic
R11	0	15k	15kOhms \pm 0.1% 0.15W Chip Resistor 0603 (1608 Metric) Anti-Sulfur, Automotive AEC-Q200 Thin Film	0603	RQ73C1J15KBTD	TE Connectivity
R12	0	49.9k	49.9kOhms \pm 1% 0.1W, 1/10W Chip Resistor 0603 (1608 Metric) Automotive AEC-Q200 Thick Film	0603	CRCW060349K9FKEA	Vishay

5 Compliance Information

5.1 Compliance and Certifications

[LM65680-Q1EVM EU Declaration of Conformity \(DoC\) for Restricting the use of Hazardous Substances \(RoHS\)](#)

6 Related Documentation

For related documentation, see the following:

- Texas Instruments, [LM65680-Q1 70V, 8A, Automotive Buck Converter Optimized for Low EMI and High Power Density](#) data sheet
- Texas Instruments, [Reduce Buck Converter EMI and Voltage Stress by Minimizing Inductive Parasitics](#) analog applications journal
- Texas Instruments, [AN-2162 Simple Success with Conducted EMI from DC-DC Converters](#) application report
- White papers:
 - Texas Instruments, [Valuing Wide \$V_{IN}\$, Low EMI Synchronous Buck Circuits for Cost-driven, Demanding Applications](#)
 - Texas Instruments, [An Overview of Conducted EMI Specifications for Power Supplies](#)
 - Texas Instruments, [An Overview of Radiated EMI Specifications for Power Supplies](#)

6.1 Supplemental Content

6.1.1 Development Support

For development support, see the following:

- For TI's reference design library, visit [TI reference designs](#).
- For TI's WEBENCH Design Environments, visit the [WEBENCH® Design Center](#).
- LM65680-Q1 DC/DC Converter [Quickstart Calculator](#).

6.1.2 PCB Layout Resources

- Texas Instruments, [AN-1149 Layout Guidelines for Switching Power Supplies](#) application report
- Texas Instruments, [AN-1229 Simple Switcher PCB Layout Guidelines](#) application report
- Texas Instruments, [Constructing Your Power Supply – Layout Considerations](#) Power Supply Design seminar
- Texas Instruments, [Low Radiated EMI Layout Made SIMPLE with LM4360x and LM4600x](#) application report
- Power house blogs:
 - [High-Density PCB Layout of DC-DC Converters](#)

6.1.3 Thermal Design Resources

- Texas Instruments, [AN-2020 Thermal Design by Insight, Not Hindsight](#) application report
- Texas Instruments, [AN-1520 A Guide to Board Layout for Best Thermal Resistance for Exposed Pad Packages](#) application report
- Texas Instruments, [Semiconductor and IC Package Thermal Metrics](#) application report
- Texas Instruments, [Thermal Design Made Simple with LM43603 and LM43602](#) application report
- Texas Instruments, [PowerPAD™ Thermally Enhanced Package](#) application report
- Texas Instruments, [PowerPAD™ Made Easy](#) application brief
- Texas Instruments, [Using New Thermal Metrics](#) application report

7 Additional Information

7.1 Trademarks

PowerPAD™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

8 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision * (October 2024) to Revision A (December 2024)	Page
• Updated EVM schematic to reflect changes to the updated silicon.....	16

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated