

TUSB1146 IBIS-AMI Models

User's Guide

Version 1.1
March 2020
Copyright © 2009, Texas Instruments Incorporated. All rights reserved.

The information and/or drawings set forth in this document and all rights in and to inventions disclosed herein and patents which might be granted thereon disclosing or employing the materials, methods, techniques, or apparatus described herein are the exclusive property of Texas Instruments. No disclosure of information or drawings shall be made to any other person or organization without the prior consent of Texas Instruments.

Texas Instruments Proprietary Information

Disclaimer

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI is a trademark of Texas Instruments Incorporated.

© 2020, Texas Instruments Incorporated. All rights reserved.

Table of Contents

1	Introduction	4
1.1	Formatting Conventions.....	4
1.2	Charter of the SerDes IBIS-AMI models	4
1.3	Is / Is Not Table	4
2	About This Release	6
2.1	IBIS-AMI Model Files	6
2.2	AMI model specific parameters.....	8
3	Model Simulation in ADS	9

1 Introduction

This document describes the organization, structure, and proper usage of the TI TUSB1146 IBIS-AMI models (compiled and approved for external customer release), hereafter referred to as the “model” for short. The model is intended for use by the TUSB1146 design team and by TUSB1146 customers for system-level modeling and verification. This document assumes that you are familiar with the relevant IBIS-AMI modeling specifications.

1.1 Formatting Conventions

The help readability, various formatting conventions are used throughout this document:

- Hyperlinks to material within and outside this document are marked in [blue](#).
- Courier font is used for `file names, code, variables, structures, parameters, and terminal commands`.

1.2 Charter of the SerDes IBIS-AMI models

The models are designed in accordance with the [IBIS-AMI standard](#) and attempt to model the significant characteristics of most components in the TUSB1146. The models are not intended to be an exact representation of TUSB1146 components implemented. Rather, the models seek to provide as high a degree of accuracy as is feasible outside of Spice-based models and simulations.

1.3 Is / Is Not Table

The following table describes the features and purposes of the models, as well as the limitations of the models.

Table 1: Model Is / Is Not Table

Is	Is Not
Compiled for 64 bit AMI EDA tool that run in Windows platform Compiled for 64-bit AMI EDA tool that run in Linux platform	Compiled for any other platform (i.e. 32-Linux)
Compliant to IBIS-AMI 5.0	Compliant to a more recent BIRD revisions, if they exist
Model of TUSB1146 functionality, non-idealities, and performance	Exact representation of implemented components
Model for SSTX->TX1, RX1->SSRX and DP0->RX2 paths only	Does not model other paths
Based on measured data	
Only valid for typical conditions (27C, 3.3V and nominal process)	

The TI IBIS-AMI models contain information on products that is based on high-level specifications. These may not accurately represent the product design in all cases. Please verify the accuracy of the models with TI before using the results.

2 About This Release

2.1 IBIS-AMI Model Files

[Table 2](#) shows the key IBIS-AMI model files delivered with the model release as part of the compressed archive.

Table 2: IBIS-AMI files included with the model release

File Name	Type	Description
TUSB1146_AMI_users_guide.pdf	PDF	TI TUSB1146 AMI model user's guide.
tusb1146.ibs	IBIS	Top-level IBIS wrapper for the TUSB1146 model.
RX2_TX.ami	AMI	Parameters file for the RX2 Tx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
RX2_TX_x64.dll	DLL	Windows 64-bit compiled shared library for the RX2 Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
RX2_TX_x64.so	SO	Linux 64-bit compiled shared object library for the RX2 Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
DP0_RX.ami	AMI	Parameters file for the DP0 Rx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
DP0_RX_x64.dll	DLL	Windows 64-bit compiled shared library for the DP0 Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
DP0_RX_x64.so	SO	Linux 64-bit compiled shared object library for the DP0 Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
SSRX_TX.ami	AMI	Parameters file for the SSRX Tx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
SSRX_TX_x64.dll	DLL	Windows 64-bit compiled shared library for the SSRX Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
SSRX_TX_x64.so	SO	Linux 64-bit compiled shared object library for the SSRX Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.

The TI IBIS-AMI models contain information on products that is based on high-level specifications. These may not accurately represent the product design in all cases. Please verify the accuracy of the models with TI before using the results.

RX1_RX.ami	AMI	Parameters file for the RX1 Rx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
RX1_RX_x64.dll	DLL	Windows 64-bit compiled shared library for the RX1 Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
RX1_RX_x64.so	SO	Linux 64-bit compiled shared object library for the RX1 Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
TX1_TX.ami	AMI	Parameters file for the TX1 Tx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
TX1_TX_x64.dll	DLL	Windows 64-bit compiled shared library for the TX1 Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
TX1_TX_x64.so	SO	Linux 64-bit compiled shared object library for the TX1 Tx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
SSTX_RX.ami	AMI	Parameters file for the SSTX Rx model as required by the IBIS-AMI standard. This is a text file which is common for all OS/execution platforms.
SSTX_RX_x64.dll	DLL	Windows 64-bit compiled shared library for the SSTX Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
SSTX_RX_x64.so	SO	Linux 64-bit compiled shared object library for the SSTX Rx model. This shared library includes the AMI_Init, AMI_GetWave, and AMI_Close functions defined in the IBIS-AMI standard.
TUSB1146_wrk.7zADS	ADS workspace	Sample ADS simulation workspace – includes sample testbenches (see Figure 1) for the repeater.

The TI IBIS-AMI models contain information on products that is based on high-level specifications. These may not accurately represent the product design in all cases. Please verify the accuracy of the models with TI before using the results.

2.2 AMI model specific parameters

TUSB1146 model consists of receiver and transmitter models. The EDA tool cascades the receiver and transmitter to form a redriver for signal integrity analysis.

The following table corresponds to receiver and transmitter parameter settings.

Table 3. Model Specific Parameters

Parameter	Description and Setting
EQ	0 to 15. 0 is lowest EQ and 15 is highest EQ setting. Controls the DP0, RX1 and SSTX receiver equalizer. Please refer to the datasheet for parameter values
VOD	0 to 3. 0 is highest VOD and 3 is lowest VOD setting. Controls the TX1, SSRX and RX2 transmitter VOD linearity setting. Please refer to the datasheet for parameter values
EN_LIMIT	0 or 1. 0 is linear enabled. 1 is limited enabled. Controls the SSRX transmitter – linear (0) or limiting (1) mode
EN_DE	0 or 1. 0 is de-emphasis disabled. 1 is de-emphasis enabled. Enables the SSRX transmitter de-emphasis when in limiting mode
EN_PRE	0 or 1. 0 is pre-shoot disabled. 1 is pre-shoot enabled. Enables the SSRX transmitter pre-shoot when in limiting mode
DE	0 to 3. 0 is lowest de-emphasis level and 3 is highest de-emphasis level. Sets the SSRX transmitter de-emphasis level Please refer to the datasheet for parameter values
PRE	0 to 3. 0 is lowest pre-shoot level and highest pre-shoot level. Sets the SSRX transmitter pre-shoot level Please refer to the datasheet for parameter values
Corner	Typical corner only.

The TI IBIS-AMI models contain information on products that is based on high-level specifications. These may not accurately represent the product design in all cases. Please verify the accuracy of the models with TI before using the results.

3 Model Simulation in ADS




Figure 1: ADS schematic of a simulation testbench for the RX1 to SSRX channel. The testbench includes an ideal transmitter, TUSB1146 redriver (RX1_RX and SSRX_TX) and ideal termination (receiver). The channel between the transmitter and the repeater inserts ~12dB loss at 5GHz.

Note: The SamplesPerBit should be set to 100 for correct behavior (SampleRate 100e10 for 10Gbps).




Figure 2: Simulation results using the following settings : EQ=4, VOD=0, EN_LIMIT=1, EN_DE=EN_PRE=1 and DE=PRE=0. Eye diagrams are at the input to the repeater, within the repeater after equalization and at the output of the repeater. The waveform is at the output of the repeater.

The TI IBIS-AMI models contain information on products that is based on high-level specifications. These may not accurately represent the product design in all cases. Please verify the accuracy of the models with TI before using the results.